

**SMF7N60**


600V N-Channel MOSFET

**●Features:**

- 7.0A, 600V,  $R_{DS(on)(Typ)} = 1.0\Omega$  @  $V_{GS} = 10V$
- Low Gate Charge
- Low  $C_{rss}$
- 100% Avalanche Tested
- Fast Switching
- Improved dv/dt Capability

**●Application:**

- High Frequency Switching Mode Power Supply
- Active Power Factor Correction

**Absolute Maximum Ratings( $T_c=25^\circ C$  unless otherwise noted)**

Symbol	Parameter	Value	Unit
$V_{DSS}$	Drain-Source Voltage	600	V
$I_D$	Drain Current - Continuous( $T_c=25^\circ C$ )	7.0*	A
	- Continuous( $T_c=100^\circ C$ )	4.5*	A
$I_{DM}$	Drain Current -Pulsed (Note1)	28*	A
$V_{GSS}$	Gate-Source Voltage	$\pm 30$	V
$E_{AS}$	Single Pulsed Avalanche Energy (Note2)	590	mJ
$I_{AR}$	Avalanche Current (Note1)	7.0	A
$E_{AR}$	Repetitive Avalanche Energy (Note1)	14.0	mJ
$dv/dt$	Peak Diode Recovery $dv/dt$ (Note3)	4.5	V/ns
$P_D$	Power Dissipation( $T_c = 25^\circ C$ )	48	W
	-Derate above $25^\circ C$	0.38	W/ $^\circ C$
$T_j$	Operating Junction Temperature	150	$^\circ C$
$T_{stg}$	Storage Temperature Range	-55 to +150	$^\circ C$

\* Drain Current Limited by Maximum Junction Temperature.

**Thermal Characteristics**

Symbol	Parameter	Max	Unit
$R_{\theta JC}$	Thermal Resistance,Junction to Case	2.6	$^\circ C/W$
$R_{\theta JA}$	Thermal Resistance,Junction to Ambient	62.5	$^\circ C/W$

	<b>SMF7N60</b>
	600V N-Channel MOSFET

### Electrical Characteristics( $T_c=25^\circ C$ unless otherwise noted)

Symbol	Parameter	Test Conditions	Min	Typ	Max	Unit
<b>Off Characteristics</b>						
$BV_{DSS}$	Drain-source Breakdown Voltage	$V_{GS}=0V, I_D=250\mu A$	600	--	--	V
$\Delta BV_{DSS} / \Delta T_J$	Breakdown Voltage Temperature Coefficient	$I_D=250\mu A$ (Referenced to $25^\circ C$ )	--	0.7	--	$V/^\circ C$
$I_{DSS}$	Zero Gate Voltage Drain Current	$V_{DS}=600V, V_{GS}=0V$	--	--	1	$\mu A$
		$V_{DS}=480V, T_c=125^\circ C$	--	--	10	$\mu A$
$I_{GSSF}$	Gate-Body Leakage Current,Forward	$V_{GS}=+30V, V_{DS}=0V$	--	--	100	nA
$I_{GSSR}$	Gate-Body Leakage Current,Reverse	$V_{GS}=-30V, V_{DS}=0V$	--	--	-100	nA

### On Characteristics

$V_{GS(th)}$	Gate Threshold Voltage	$V_{DS}=V_{GS}, I_D=250\mu A$	2.0	--	4.0	V
$R_{DS(on)}$	Static Drain-Source On-Resistance	$V_{GS}=10 V, I_D=3.5A$	--	1.0	1.2	$\Omega$
$g_{FS}$	Forward Transconductance	$V_{DS}=40 V, I_D=3.5A$ (Note4)	--	6.5	--	S

### Dynamic Characteristics

$C_{iss}$	Input Capacitance	$V_{DS}=25V, V_{GS}=0V, f=1.0MHz$	--	1380	--	pF
$C_{oss}$	Output Capacitance		--	170	--	pF
$C_{rss}$	Reverse Transfer Capacitance		--	15	--	pF

### Switching Characteristics

$t_{d(on)}$	Turn-On Delay Time	$V_{DD} = 300 V, I_D = 7.0 A, R_G = 25 \Omega$ (Note4,5)	--	13	--	ns
$t_r$	Turn-On Rise Time		--	100	--	ns
$t_{d(off)}$	Turn-Off Delay Time		--	126	--	ns
$t_f$	Turn-Off Fall Time		--	48	--	ns
$Q_g$	Total Gate Charge	$V_{DS} = 480 V, I_D = 7.0 A, V_{GS} = 10 V$ (Note4,5)	--	30	--	nC
$Q_{gs}$	Gate-Source Charge		--	6	--	nC
$Q_{gd}$	Gate-Drain Charge		--	14	--	nC

### Drain-Source Diode Characteristics and Maximum Ratings

$I_s$	Maximum Continuous Drain-Source Diode Forward Current	--	--	7.0	A	
$I_{SM}$	Maximum Pulsed Drain-Source Diode Forward Current	--	--	28	A	
$V_{SD}$	Drain-Source Diode Forward Voltage	$V_{GS}=0V, I_s=7.0A$	--	--	1.4	V
$t_{rr}$	Reverse Recovery Time	$V_{GS}=0V, I_s=7.0A,$ $dI_F/dt=100A/\mu s$ (Note4)	--	315	--	ns
$Q_{rr}$	Reverse Recovery Charge		--	2.6	--	$\mu C$

Notes:


1. Repetitive Rating:Pulse Width Limited by Maximum Junction Temperature.
2.  $L = 19.5mH, I_{AS} = 7.0A, V_{DD} = 50V, R_G = 25 \Omega$ , Starting  $T_J = 25^\circ C$ .
3.  $I_{SD} \leq 7.0A, di/dt \leq 200A/\mu s, V_{DD} \leq BV_{DSS}$ , Starting  $T_J = 25^\circ C$ .
4. Pulse Test : Pulse Width  $\leq 300 \mu s$ , Duty Cycle  $\leq 2\%$ .
5. Essentially Independent of Operating Temperature.




**SMF7N60**

600V N-Channel MOSFET


### On-Region Characteristics




### Transfer Characteristics




### On-Resistance Variation vs. Drain Current and Gate Voltage




### Body Diode Forward Voltage Variation vs. Source Current and Temperature



### Capacitance Characteristics



### Gate Charge Characteristics







**SMF7N60**

600V N-Channel MOSFET


### Breakdown Voltage Variation vs. Temperature




### On-Resistance Variation vs. Temperature



### Maximum Safe Operating Area



### Maximum Drain Current Vs. Case Temperature





**SMF7N60**

600V N-Channel MOSFET

## TO-220F Package Dimensions

UNIT: mm

SYMBOL	min	nom	max	SYMBOL	min	nom	max
A	9.80		10.60	D		2.54	
A1		7.00		D1	1.15		1.55
A2	2.90		3.40	D2	0.60		1.00
A3	9.10		9.90	D3	0.20		0.50
B1	15.40		16.40	E	2.24		2.84
B2	4.35		4.95	E1		0.70	
B3	6.00		7.40	E2		1.0×45°	
C	3.00		3.70	E3	0.35		0.65
C1	15.00		17.00	E4	2.30		3.30
C2	8.80		10.80	α (度)		30°	

