

## N-Channel Enhancement Mode Power MOSFET

### Description


IRF20N65 is an N-channel enhancement mode power MOS field effect transistor. The improved planar stripe cell and the improved guard ring terminal have been especially tailored to minimize on-state resistance, provide superior switching performance, and withstand high energy pulse in the avalanche and commutation mode.

These devices are widely used in AC-DC power suppliers, DCDC converters and H-bridge PWM motor drivers.

### General Features

- 20A, 650V,  $R_{DS(on)(typ.)} = 0.38\text{ohm}$  @  $V_{GS}=10\text{V}$
- Low Gate charge
- Low Crss
- Fast Switching
- Improved dv/dt Capability

$I_D$	20A
$V_{DSS}$	650V
$R_{ds(on) (\max)}$	$0.5\Omega(V_{GS}=10\text{V}, I_D=10\text{A})$
$Q_g$	60nC



1.Gate 2.Drain 3.Source


### Application

- Power switching application
- Hard switched and high frequency circuits
- Uninterruptible power supply



TO-220

TO-220F



TO-247

## Order Information

Order Information	Marking ID	Package	Packing Type Supplied As
SMIRF20N65T2TL	IRF20N65	TO220F-3L	1000 units on Box, 5000 units on Carton
SMIRF20N65T1TL	IRF20N65	TO220-3L	1000 units on Box, 5000 units on Carton
SMIRF20N65T8TL	IRF20N65	TO247-3L	450 units on Box, 2250 units on Carton

## Absolute Maximum Ratings Ta=25 °C unless otherwise noted

Parameter	Symbol	Value	Unit
Drain-source Voltage	V <sub>DS</sub>	650	V
Gate-source Voltage	V <sub>GS</sub>	±30	V
Continuous Drain Current(Ta=25°C)	I <sub>D</sub>	20	A
Drain Current-Pulsed	I <sub>DM</sub>	80	A
Total Dissipation(Ta=25°C)	TO247	365	W
	TO220	239	
	TO220F	80	
Junction Temperature	T <sub>J</sub>	150	°C
Storage Temperature	T <sub>STG</sub>	-55 to 150	°C
Single Pulse Avalanche Energy	E <sub>AS</sub>	1200	mJ
ESD HBM(Human Body Mode)		≥2000	V
ESD MM(Machine Mode)		≥200	V

## Electrical Characteristics Ta = 25°C

PARAMETER	Symbol	Test Condition	MIN	TYP	MAX	UNIT
Drain-source Breakdown Voltage	BV <sub>DSS</sub>	V <sub>GS</sub> =0V, I <sub>D</sub> =250µA	650			V
Gate Threshold Voltage	V <sub>GS(TH)</sub>	V <sub>GS</sub> =V <sub>DS</sub> , I <sub>D</sub> =250µA	2.0	3.0	4.0	V
Drain-source Leakage Current	I <sub>DSS</sub>	V <sub>DS</sub> =650V, V <sub>GS</sub> =0V			1	uA
Drain-Source Diode Forward Voltage	V <sub>SD</sub>	V <sub>GS</sub> =0V, I <sub>S</sub> =20A			1.5	V
Gate-body Leakage Current (V <sub>DS</sub> = 0)	I <sub>GSS</sub>	V <sub>GS</sub> =±30V, V <sub>DS</sub> =0V			±100	nA
Static Drain-source On Resistance	R <sub>DS(ON)</sub>	V <sub>GS</sub> =10V, I <sub>D</sub> =10A		0.38	0.5	Ω

**Note:** Using continuously under heavy loads (e.g. the application of high temperature/current/voltage and the significant in temperature etc.) may cause this product to decrease in the reliability significantly even if the operating conditions (i.e. operating temperature/current/voltage, etc.) are within the absolute maximum ratings

## Thermal Characteristics Ta=25 °C

PARAMETER		Symbol	TYP	MAX	UNIT
Maximum Junction-to-case	TO220F,TO220	$R_{QJC}$		1.56	°C/W
	TO-247			0.3	
Maximum Junction-to-Ambient	TO220F,TO220	$R_{QJA}$		80	°C/W
	TO247			40	

**Note1:** Ensure that the channel temperature does not exceed 150°C

**Note2:**  $V_{DD}=50V$ ,  $T_{ch}=25$  °C(initial),  $I_{AS}=20A$ ,  $R_g=25\Omega$

**Note3:** This transistor is sensitive to electrostatic and should be handled with care

## Dynamic Characteristics Ta = 25 °C

PARAMETER	Symbol	Test Condition	MIN	TYP	MAX	UNIT
Input Capacitance	$C_{iss}$	$V_{DS}=25V, V_{GS}=0V, f=1.0MHz$		3060		pF
output Capacitance	$C_{oss}$			250		pF
Reverse Transfer Capacitance	$C_{rss}$			18		pF
Gate Resistance	$R_g$	$V_{DS}=0V, V_{GS}=0V, f=1.0MHz$		2.2		Ω

## Switching Characteristics Ta=25 °C


PARAMETER	Symbol	Test Condition	MIN	TYP	MAX	UNIT
Turn-On Delay Time	$T_{d(on)}$	$V_{DS}=325V, I_D=20A, V_{GS}=10V, R_G=25\Omega$		36		nS
Turn-On Rise Time	$T_r$			80		nS
Turn-Off Delay Time	$T_{d(off)}$			170		nS
Turn-Off Rise Time	$T_f$			80		nS
Total Gate Charge	$Q_g$	$V_{DS}=520V, I_D=20A, V_{GS}=10V$		60		nC
Gate-Source Charge	$Q_{gs}$			11		nC
Gate-Drain Charge	$Q_{gd}$			26		nC

## Drain-Source Diode Maximum Ratings and Characteristics Ta=25 °C


PARAMETER	Symbol	Test Condition	MIN	TYP	MAX	UNIT
Max. Diode Forward Current	$I_s$	Integral Reverse P-N Junction Diode in the MOSFET			20	A
Pulsed Source Current	$I_{sm}$				80	A
Diode Forward Voltage	$V_{SD}$	$V_{GS}=0V, I_s=20A$		0.88	1.5	V
Reverse Recovery Time	$t_{rr}$	$V_{GS}=0V, I_s=20A, dI/dt=100A/\mu s$		400		nS
Reverse Recovery Charge	$Q_{rr}$			3.5		μC

## Test Circuit


Gate Charge Test Circuit & Waveform



Resistive Switching Test Circuit & Waveform



Unclamped Inductive Switching Test Circuit & Waveform



## Typical Characteristics Curve





Figure 1: Output Characteristics

Figure 2: Transfer Characteristics





Figure 3: On Resistance Vs Drain Current

Source Voltage

Figure 4: On Resistance Vs Gate





Figure 5: On Resistance Vs Junction Temperature Characteristics

Figure 6: Capacitance

## Typical Characteristics Curve




Figure 7: Gate Charge Waveform  
Forward Voltage




Figure 8: Source-Drain Diode





Figure 9: Breakdown Voltage Vs Junction Temperature


**Note:** The above characteristics curves are presented for reference only and not guaranteed by production test unless otherwise noted

## Outline Information (TO220F-3L)



SYMBOL	MIN	NOM	MAX
A	4.42	4.70	5.02
A1	2.30	2.54	2.80
A3	2.50	2.76	3.10
b	0.70	0.80	0.90
b2	—	—	1.47
c	0.35	0.50	0.65
D	15.25	15.87	16.25
D1	15.30	15.75	16.30
D2	9.30	9.80	10.30
E	9.73	10.16	10.36
e	2.54BCS		
H1	6.40	6.68	7.00
L	12.48	12.98	13.48
L1	/	/	3.50
$\phi P$	3.00	3.18	3.40
Q	3.05	3.30	3.55

## Outline Information (TO220-3L)



SYMBOL	MIN	NOM	MAX
A	4.30	4.50	4.70
A1	1.00	1.30	1.50
A2	1.80	2.40	2.80
b	0.60	0.80	1.00
b1	1.00	—	1.60
c	0.30	—	0.70
D	15.10	15.70	16.10
D1	8.10	9.20	10.00
E	9.60	9.90	10.40
e	2.54BSC		
H1	6.10	6.50	7.00
L	12.60	13.08	13.60
L1	—	—	3.95
ΦP	3.40	3.70	3.90
Q	2.60	—	3.20

## Outline Information (TO247-3L)

UNIT: mm							
SYMBOL	MIN	NOM	MAX	SYMBOL	MIN	NOM	MAX
A	4.60		5.15	A1	1.30		1.60
b	2.86		3.26	b1	1.86		2.26
b2		1.20		c		0.50	
D	19.00		21.00	E	15.45		15.75
E1	12.00		13.06	e		5.45	
L	14.00		14.60	L1	5.20		5.88
L2	24.00		24.40	L3	10.00		10.60
P		3.50		Q	2.30		2.70

