






Specifications :

- Voltage rating: 250V AC / DC
- Current rating: 3A AC / DC
- Withstanding voltage: 800V AC/minute
- Temperature range: -25°C~+85°C
- Insulation resistance:≥1000MΩ
- Contact resistance: ≤10mΩ
- After environmental testing: ≤20mΩ

X2530 W R XX- XX X-PTSN XX

- ① Series No.
② Category: W-wafer
③ Welding Board Angle: R-Right Angle 90°
④ Welding Way: Blank-DIP
⑤ Row No.-Pin No.: XX-Single row (02~22P)
⑥ Special NO.:
⑦ Material: PT-PBT 94V-0
⑧ Planting Category:
V01:All Gold-Flash ; SN-Bright tin plating
⑨ Color: Blank-natural color

Poles	Dimensions(mm)		Poles	Dimensions(mm)	
	A	B		A	B
02	2.54	7.70	12	27.94	33.10
03	5.08	10.20	13	30.48	35.60
04	7.62	12.70	14	33.02	38.10
05	10.16	15.20	15	35.56	40.70
06	12.70	17.80	16	38.10	43.20
07	15.24	20.30	17	40.64	45.70
08	17.78	22.90	18	43.18	48.20
09	20.32	25.40	19	45.72	50.70
10	22.86	28.00	20	48.26	53.20
11	25.40	30.50	22	53.34	58.50



Recommended P.C.B Layout
General Tolerance±0.05

X2530WR-XX-PTSN	PBT UL 94V-0	Brass	Tin-Plated	X2530H
PART NO	Material	Material(Pin)	Finish(Pin)	Suitable XKB Terminal

For and on behalf of
XKB INDUSTRIAL PRECISION CO., LIMITED
香港星坤工業精密有限公司

					DSND		DATE		SCALE: N/A	MODEL TYPE: X2530WR-XX-PTSN				
		KKB INDUSTRIAL PRECISION CO., LIMITED			ANGULAR	± 5°	DWN		DATE	VIEW: 	PART NO.:			
△ X		香港星坤工業精密有限公司			L ≤ 4	± 0.2	CHKD		DATE	UNIT: mm	2.54mm Crimp Style Connectors			
△ X					4 < L ≤ 16	± 0.3			DATE		DWG NO.:			
△ X					16 < L ≤ 63	± 0.4	APPD		DATE	SIZE: A4				
MARK		DESCRIPTION	DATE	REVISED	APPROVED	L > 63		± 0.5		DATE				
					REVISION				AUTHORIZED SIGNATURE(S)		UNSPECIFIED TOLERANCES			
										KKB INDUSTRIAL PRECISION CO., LIMITED		WEIGHT 1.0g	SHEET 1/1	REVISION A0