


**SOD-523****Marking:****Features**

- Low Forward Voltage Drop
- Flat Lead SOD-523 Small Outline Plastic Package
- Extremely Small SOD-523 Package
- Surface Device Type Mounting
- RoHS Compliant
- Green EMC
- Matte Tin(Sn) Lead Finish
- Band Indicates Cathode

Maximum Ratings & Thermal Characteristics

(Ratings at 25°C ambient temperature unless otherwise specified.)

Symbol	Parameter	Value	Units
P _D	Power Dissipation	200	mW
T _{STG}	Storage Temperature Range	-55 to +125	°C
T _J	Operating Junction Temperature	+125	°C
V _R	Reverse Voltage	30	V
I _{F(AV)}	Average Forward Current	200	mA
I _{FSM}	Peak Forward Surge Current (At 8.3ms single half sine-wave)	1	A

These ratings are limiting values above which the serviceability of the diode may be impaired.

Electrical Characteristics

(Ratings at 25°C ambient temperature unless otherwise specified.)

Symbol	Parameter	Test Condition	Limits		Unit
			Min	Max	
B _V	Breakdown Voltage	I _R =500μA	30		Volts
I _R	Reverse Leakage Current	V _R =10V		30	μA
V _F	Forward Voltage	I _F =200mA		0.5	Volts



RATING AND CHARACTERISTIC CURVES




Figure 1. Forward Characteristics





Figure 2. Reverse Characteristics



REVERSE VOLTAGE : V_R (V)

Figure 3. Total Capacitance

SOD-523 PACKAGE OUTLINE Plastic surface mounted package

