


**SOD-123FL**

MARKING: F7

**Features**

- Low reverse leakage
- High Forward surge capability
- High reliability
- High temperature soldering guaranteed: 260°C/10 秒
- Lead and body according with Rohs standard

**Mechanical Data**

- SOD 123FL small outline plastic package
- Polarity: Color band denotes cathode end
- Epoxy UL: 94V-0
- Mounting Position: Any

**Maximum Ratings & Thermal Characteristics**





(Ratings at 25°C ambient temperature unless otherwise specified.)

Parameters	Symbol	FR107	Unit
Maximum repetitive peak reverse voltage	V <sub>RRM</sub>	1000	V
Maximum RMS voltage	V <sub>RMS</sub>	700	V
Maximum DC blocking voltage	V <sub>DC</sub>	1000	V
Maximum average forward rectified current	I <sub>F(AV)</sub>	1.0	A
Non-repetitive Peak forward surge current 8.3 ms single half sine-wave	I <sub>FSM</sub>	30	A
Typical thermal resistance	R <sub>θJA</sub>	45	°C/W
Operation junction and Storage temperature range	T <sub>j,TSTG</sub>	-55~+150	°C

**Electrical Characteristics**

(Ratings at 25°C ambient temperature unless otherwise specified.)

Parameters	Symbol	RF107	Unit
@IF=1.0A Max. forward voltage	V <sub>F</sub>	1.3	V
@VDC TA=25°C Max. reverse current TA=100°C	I <sub>R</sub>	5 100	uA
Max. reverse recover time IF=0.5A,IR=1.0A,I <sub>RR</sub> =0.25A	T <sub>rr</sub>	500	nS
VR=4.0V, f=1MHz Type junction capacitance	C <sub>j</sub>	15	pF

**Characteristic Curves****SOD-123FL PACKAGE OUTLINE** Plastic surface mounted package

SYMBOL	DIMENSIONS	
	MIN.	MAX.
A	1.20	1.40
b	0.80	1.10
c	0.15	0.25
D	1.75	1.95
E	2.70	2.90
E1	3.50	3.90
L	0.35	0.85