


MH5 系列
SERIES

105°C 高5mm品
105°C 5mm Height

·105°C 1000小时品。
Load Life : 105°C 1000 hours.

RoHS
compliance



◆规格表／SPECIFICATIONS

项目 Items	特性 Characteristics						
工作温度范围 Category Temperature Range	-40~+105°C						
额定电压范围 Rated Voltage Range	6.3~50Vdc						
静电容量允许差 Capacitance Tolerance	±20% (20°C, 120Hz)						
漏电流 Leakage Current(MAX)	小于I=0.01CV和3μA中的较大值 (施加额定电压2分钟后) I=0.01CV or 3μA whichever is greater. (After 2 minutes application of rated voltage) I=漏电流(μA) C=静电容量(μF) V=额定电压(Vdc) Leakage Current Capacitance Rated Voltage						
损失角正切值 (tanδ) Dissipation Factor(MAX)	额定电压(Vdc) Rated Voltage	6.3	10	16	25	35	50
	tanδ	0.28	0.24	0.20	0.16	0.13	0.12
耐久性 Endurance	在105°C环境中, 不超过额定电压的范围内叠加额定纹波电流, 连续加载1000小时后, 满足以下各项要求。 After applying rated voltage with rated ripple current for 1000 hours at 105°C, the capacitors shall meet the following requirements. 静态容量变化率 Capacitance Change 初期值的±25%以内 Within ±25% of the initial value. 损失角正切值 Dissipation Factor 规格值的200%以下 Not more than 200% of the specified value. 漏电电流 Leakage Current 规格值以下 Not more than the specified value.						
低温特性 Low Temperature Stability (阻抗比) Impedance Ratio(MAX)	额定电压(Vdc) Rated Voltage	6.3	10	16	25	35	50
	Z(-25°C)/Z(20°C)	3	3	2	2	2	2
	Z(-40°C)/Z(20°C)	8	5	4	3	3	3

◆标准品一览表／STANDARD SIZE Size φD×L(mm), Rated Ripple Current (mA r.m.s./105°C, 120Hz)

Vdc	Cap (μF)	Size (φDxL)	Rated Ripple Current	Vdc	Cap (μF)	Size (φDxL)	Rated Ripple Current	Vdc	Cap (μF)	Size (φDxL)	Rated Ripple Current
6.3	22	4×5	23	16	10	4×5	20	35	4.7	4×5	17
	33	5×5	30		22	5×5	31		10	5×5	24
	47	5×5	37		33	6.3×5	48		22	6.3×5	48
	100	6.3×5	57		47	6.3×5	56		0.47	4×5	4
10	22	5×5	28		100	6.3×5	62		1	4×5	8
	33	5×5	34		10	5×5	22		2.2	4×5	13
	47	6.3×5	52		22	6.3×5	44		3.3	4×5	14
	100	6.3×5	62		33	6.3×5	48		4.7	5×5	18
					47	6.3×5	56		10	6.3×5	28

◆副记号／OPTION

记号 Code	
PET套管 PET Sleeve	EFC

◆产品型号体系／PART NUMBER

□□□	MH5	□□□□□	M	□□□	□□	D×L
额定电压 Rated Voltage	系列名称 Series	静电容量 Capacitance	静电容量允许差 Capacitance Tolerance	副记号 Option	引线加工记号 Lead Forming	铝壳尺寸 Case Size