










Recommended P.C.B Layout
General Tolerance±0.05



2P-4P
SCALE 1:0.8



5P-8P
SCALE 1:0.8



9P-16P
SCALE 1:0.8

Specifications :

- Voltage rating: 250V AC / DC
- Current rating: 3A AC / DC
- Withstanding voltage: 800V AC/minute
- Temperature range: -25°C~+85°C
- Insulation resistance: ≥1000MΩ
- Contact resistance: ≤10mΩ
- After environmental testing: ≤20mΩ

X2000 W R S-XX X -9T XX XX
① ② ③ ④ ⑤ ⑥ ⑦ ⑧ ⑨

- ① Series No.
- ② Category: W-WAFER
- ③ Welding Board Angle: R-Right Angle 90°
- ④ Welding Way: S-SMT
- ⑤ Row No.-Pin No.: XX-02P~16P
- ⑥ Plug the Pin & Special No.
- ⑦ Material: 9T -PA9T 94V-0
- ⑧ Plating Category: SN-Bright Tin Plating ;SW- Matte Tin
- ⑨ Color : Blank-Natural Color

Poles	Dimensions (mm)			Poles	Dimensions (mm)		
	A	B	C		A	B	C
02	2.00	8.00	4.50	10	18.00	24.00	20.50
03	4.00	10.00	6.50	11	20.00	26.00	22.50
04	6.00	12.00	8.50	12	22.00	28.00	24.50
05	8.00	14.00	10.50	13	24.00	30.00	26.50
06	10.00	16.00	12.50	14	26.00	32.00	28.50
07	12.00	18.00	14.50	15	28.00	34.00	30.50
08	14.00	20.00	16.50	16	30.00	36.00	32.50
09	16.00	22.00	18.50				

X2000WRS-XX-9TSW	PA9T UL 94V-0	Brass	Matte Tin	Brass	Matte Tin	X2000H
X2000WRS-XX-9TSN			Tin Plating		Tin Plating	
PART NO	Material	Material(Pln)	Finish(Pln)	Material (Solder Tabs)	Finish (Solder Tabs)	Mates With Housing

DSND		DATE		SCALE: N/A	MODEL TYPE: 2000WRS-XX-9TXX
DWN		DATE		VIEW:	PART NO.:
CHKD		DATE		UNIT: mm	2.00mm Crimp Style Connector
APPD		DATE		SIZE: A4	DWG NO.:
XKB INDUSTRIAL PRECISION CO.,LIMITED					WEIGHT 1.0g
					SHEET 1/1
					REVISION A0

For and on behalf of
XKB INDUSTRIAL PRECISION CO., LIMITED
香港星坤工業精密有限公司

Authorized Signature(s)

REVISIONS

UNSPECIFIED TOLERANCES