

SLV 系列  
SERIES

105°C 5000小时品  
Load Life : 105°C 5000 hours

RoHS  
compliance



## ◆规格表／SPECIFICATIONS

项目 Items	特性 Characteristics						
工作温度范围 Category Temperature Range	-40~+105°C						
额定电压范围 Rated Voltage Range	6.3~50Vdc						
静电容量允许差 Capacitance Tolerance	$\pm 20\%$ (20°C, 120Hz)						
漏电流 Leakage Current(MAX)	小于 $I=0.01CV$ 和 $3\mu A$ 中的较大值 (施加额定电压2分钟后) $I=0.01CV$ or $3\mu A$ whichever is greater. (After 2 minutes application of rated voltage) $I$ =漏电流( $\mu A$ ) C=静电容量( $\mu F$ ) V=额定电压(Vdc) Leakage Current Capacitance Rated Voltage						
损失角正切值 (tanδ) Dissipation Factor(MAX)	额定电压(Vdc) Rated Voltage	6.3	10	16	25	35	50
	$\tan\delta$	0.30	0.24	0.20	0.16	0.14	0.14
耐久性 Endurance	在105°C环境中, 不超过额定电压的范围内叠加额定纹波电流, 连续加载5000小时后, 满足以下各项要求。 After applying rated voltage with rated ripple current for 5000 hours at 105°C, the capacitors shall meet the following requirements. 静态容量变化率 Capacitance Change 损失角正切值 Dissipation Factor 漏电电流 Leakage Current						
低温特性 Low Temperature Stability (阻抗比) Impedance Ratio(MAX)	额定电压(Vdc) Rated Voltage	6.3	10	16	25	35	50
	$Z(-25^\circ C)/Z(20^\circ C)$	4	3	2	2	2	2
	$Z(-40^\circ C)/Z(20^\circ C)$	14	12	8	6	4	3

## ◆标准品一览表／STANDARD SIZE

Vdc	Cap ( $\mu F$ )	Size ( $\phi D \times L$ )	Rated Ripple Current
6.3	22	4×6.1	22
	47	5×6.1	38
	100	6.3×6.1	69
10	33	5×6.1	35
16	10	4×6.1	18
	22	5×6.1	30
	47	6.3×6.1	50


Vdc	Cap ( $\mu F$ )	Size ( $\phi D \times L$ )	Rated Ripple Current
35	25	33	6.3×6.1
	4.7	4×6.1	50
	10	5×6.1	16
	22	6.3×6.1	27

## ◆尺寸图／DIMENSIONS

(mm)

$\phi D$	L	A1	B1	C	W1	P
4	6.1	4.3	4.3	1.8	0.5~0.8	1.0
5	6.1	5.3	5.3	2.2	0.5~0.8	1.3
6.3	6.1	6.6	6.6	2.7	0.5~0.8	1.8

## ◆标识／MARKING

◆纹波电流补正系数／  
MULTIPLIER FOR RIPPLE CURRENT

频率(Hz) Frequency	60 (50)	120	500	1k	10k
系数 Coefficient	0.47~1 $\mu F$	0.50	1.00	1.20	1.30
	2.2~4.7 $\mu F$	0.65	1.00	1.20	1.30
	10~47 $\mu F$	0.80	1.00	1.20	1.30
	100 $\mu F$	0.80	1.00	1.10	1.15

Size  $\phi D \times L$ (mm), Rated Ripple Current (mA r.m.s./105°C, 120Hz)

Vdc	Cap ( $\mu F$ )	Size ( $\phi D \times L$ )	Rated Ripple Current
50	0.47	4×6.1	4
	1	4×6.1	8
	2.2	4×6.1	11
	3.3	4×6.1	14
	4.7	5×6.1	19
	10	6.3×6.1	32

## ◆产品型号体系／PART NUMBER

□□□ SLV □□□□  
额定电压 系列名称 静电容量 M  
Rated Voltage Series Capacitance

□□□ DXL  
静电容量允许差 副记号 铝壳尺寸  
Capacitance Tolerance Option Case Size