




NOTE:
Rating: DC 12V 50mA
Operating Force:200±100gf
Lifetime:10,000 Cycles

PAPT NO	L
SK-3260D-01-L1	2.0
SK-3260D-01-L2	2.5
SK-3260D-01-L3	3.0
SK-3260D-01-L4	4.0

ITEM	PAPT NAME	TER,NO	QTY	MATERIAL	FINISHING	REMARK
⑤	Terminal	3	3	Brass (0.30t)	ag Plated	
④	Contact spring	1	1	Phosphor branze	ag Plated	
③	Base	1	1	Pa46	Black	
②	Cover	1	1	Sus	Natural	
①	Keystake	1	1	Pa46	Black	

						DSND		DATE		SCALE: N/A	MODEL TYPE: SLIDE SWITCH			
△ X					ANGLAR	±5°	DWN		DATE		VIEW: 	PART NO.:		
△ X					X.X	±0.2mm	CHKD		DATE		UNIT: mm	DWG NO.: SK-3260D-01-X		
△ X					X.XX	±0.1mm								
△ X					X.XXX	±0.05mm	APPD		DATE		SIZE: A4			
MARK	DESCRIPTION		DATE	REVISED	APPROVED		XKB INDUSTRIAL PRECISION CO.,LIMITED					WEIGHT	SHEET	REVISION
REVISIONS						UNSPECIFIED TOLERANCES						1.0g	1/1	A0
www.xk-dg.cn www.helloxkb.com www.helloxkb.cn														