

N- and P-Channel 60-V (D-S) MOSFET

PRODUCT SUMMARY

	V _{DS} (V)	R _{DS(on)} (Ω)	I _D (A) ^a	Q _g (Typ.)
N-Channel	60	0.028 at V _{GS} = 10 V	5.3	6 nC
		0.031 at V _{GS} = 4.5 V	4.7	
P-Channel	- 60	0.050 at V _{GS} = - 10 V	- 4.9	8 nC
		0.060 at V _{GS} = - 4.5 V	- 4.5	

FEATURES



- Halogen-free According to IEC 61249-2-21 Available
- TrenchFET® Power MOSFET
- 100 % R_g and UIS Tested

APPLICATIONS

- CCFL Inverter



RoHS
COMPLIANT
HALOGEN
FREE
Available



N-Channel MOSFET

P-Channel MOSFET

ABSOLUTE MAXIMUM RATINGS T_A = 25 °C, unless otherwise noted

Parameter		Symbol	N-Channel	P-Channel	Unit
Drain-Source Voltage		V _{DS}	60	- 60	V
Gate-Source Voltage		V _{GS}	± 20		
Continuous Drain Current (T _J = 150 °C)	T _C = 25 °C	I _D	5.3	- 4.9	A
	T _C = 70 °C		4.3	- 4.2	
	T _A = 25 °C		4.3 ^{b, c}	- 4.0 ^{b, c}	
	T _A = 70 °C		3.4 ^{b, c}	- 3.4 ^{b, c}	
Pulsed Drain Current (10 μs Pulse Width)		I _{DM}	20	- 25	
Source Drain Current Diode Current	T _C = 25 °C	I _S	2.6	- 2.8	
	T _A = 25 °C		1.7 ^{b, c}	- 1.7 ^{b, c}	
Pulsed Source-Drain Current		I _{SM}	20	- 25	
Single Pulse Avalanche Current	L = 0.1 mH	I _{AS}	11	15	mJ
Single Pulse Avalanche Energy		E _{AS}	6.1	11	
Maximum Power Dissipation	T _C = 25 °C	P _D	3.1	3.4	W
	T _C = 70 °C		2	2.2	
	T _A = 25 °C		2 ^{b, c}	2 ^{b, c}	
	T _A = 70 °C		1.3 ^{b, c}	1.3 ^{b, c}	
Operating Junction and Storage Temperature Range		T _J , T _{stg}	- 55 to 150		°C

THERMAL RESISTANCE RATINGS

Parameter		Symbol	N-Channel		P-Channel		Unit
			Typ.	Max.	Typ.	Max.	
Maximum Junction-to-Ambient ^{b, d}	t ≤ 10 s	R _{thJA}	55	62.5	53	62.5	°C/W
Maximum Junction-to-Foot (Drain)	Steady State	R _{thJF}	33	40	30	37	

Notes:

a. Based on T_C = 25 °C.

b. Surface Mounted on 1" x 1" FR4 board.

c. t = 10 s.

d. Maximum under Steady State conditions is 110 °C/W for N-Channel and P-Channel.

SPECIFICATIONS T _J = 25 °C, unless otherwise noted								
Parameter	Symbol	Test Conditions		Min.	Typ. ^a	Max.	Unit	
Static								
Drain-Source Breakdown Voltage	V _{DS}	V _{GS} = 0 V, I _D = 250 μA	N-Ch	60			V	
		V _{GS} = 0 V, I _D = - 250 μA	P-Ch	- 60				
V _{DS} Temperature Coefficient	ΔV _{DS} /T _J	I _D = 250 μA	N-Ch		55		mV	
		I _D = - 250 μA	P-Ch		- 50			
V _{GS(th)} Temperature Coefficient	ΔV _{GS(th)} /T _J	I _D = 250 μA	N-Ch		- 6			
		I _D = - 250 μA	P-Ch		4			
Gate Threshold Voltage	V _{GS(th)}	V _{DS} = V _{GS} , I _D = 250 μA	N-Ch	1		3	V	
		V _{DS} = V _{GS} , I _D = - 250 μA	P-Ch	- 1		- 3		
Gate-Body Leakage	I _{GSS}	V _{DS} = 0 V, V _{GS} = ± 20 V	N-Ch			100	nA	
			P-Ch			- 100		
Zero Gate Voltage Drain Current	I _{DSS}	V _{DS} = 60 V, V _{GS} = 0 V	N-Ch			1	μA	
		V _{DS} = - 60 V, V _{GS} = 0 V	P-Ch			- 1		
		V _{DS} = 60 V, V _{GS} = 0 V, T _J = 55 °C	N-Ch			10		
		V _{DS} = - 60 V, V _{GS} = 0 V, T _J = 55 °C	P-Ch			- 10		
On-State Drain Current ^b	I _{D(on)}	V _{DS} ≥ 5 V, V _{GS} = 10 V	N-Ch	20			A	
		V _{DS} ≤ - 5 V, V _{GS} = - 10 V	P-Ch	- 25				
Drain-Source On-State Resistance ^b	R _{DS(on)}	V _{GS} = 10 V, I _D = 4.3 A	N-Ch		0.026	0.028	Ω	
		V _{GS} = - 10 V, I _D = - 3.1 A	P-Ch		0.055	0.060		
		V _{GS} = 4.5 V, I _D = 3.9 A	N-Ch		0.029	0.035		
		V _{GS} = - 4.5 V, I _D = - 0.2 A	P-Ch		0.060	0.070		
Forward Transconductance ^b	g _{fs}	V _{DS} = 15 V, I _D = 4.3 A	N-Ch		15		S	
		V _{DS} = - 15 V, I _D = - 3.1 A	P-Ch		8.5			
Dynamic ^a								
Input Capacitance	C _{iss}	N-Channel V _{DS} = 15 V, V _{GS} = 0 V, f = 1 MHz	N-Ch		665		pF	
			P-Ch		650			
Output Capacitance	C _{oss}	P-Channel V _{DS} = - 15 V, V _{GS} = 0 V, f = 1 MHz	N-Ch		75			
			P-Ch		95			
Reverse Transfer Capacitance	C _{rss}		N-Ch		40			
			P-Ch		60			
Total Gate Charge	Q _g	V _{DS} = 30 V, V _{GS} = 10 V, I _D = 4.3 A	N-Ch		13	20	nC	
		V _{DS} = - 30 V, V _{GS} = - 10 V, I _D = - 3.1 A	P-Ch		14.5	22		
	N-Channel V _{DS} = 30 V, V _{GS} = 4.5 V, I _D = 4.3 A	N-Ch		6	9			
		P-Ch		8	12			
Gate-Source Charge	Q _{gs}		N-Ch		2.3			
			P-Ch		2.2			
Gate-Drain Charge	Q _{gd}	P-Channel V _{DS} = - 30 V, V _{GS} = - 4.5 V, I _D = - 3.1 A	N-Ch		2.6			
			P-Ch		3.7			
Gate Resistance	R _g	f = 1 MHz	N-Ch		2	3	Ω	
			P-Ch		14	20		


SPECIFICATIONS T _J = 25 °C, unless otherwise noted								
Parameter	Symbol	Test Conditions		Min.	Typ. ^a	Max.	Unit	
Dynamic ^a								
Turn-On Delay Time	t _{d(on)}	N-Channel V _{DD} = 30 V, R _L = 8.8 Ω I _D ≅ 3.4 A, V _{GEN} = 4.5 V, R _g = 1 Ω	N-Ch		15	25	ns	
			P-Ch		30	45		
Rise Time	t _r		N-Ch		65	100		
			P-Ch		70	105		
Turn-Off Delay Time	t _{d(off)}	P-Channel V _{DD} = - 30 V, R _L = 12.5 Ω I _D ≅ - 2.4 A, V _{GEN} = - 4.5 V, R _g = 1 Ω	N-Ch		15	25		
			P-Ch		40	60		
Fall Time	t _f		N-Ch		10	15		
			P-Ch		30	45		
Turn-On Delay Time	t _{d(on)}	N-Channel V _{DD} = 30 V, R _L = 8.8 Ω I _D ≅ 3.4 A, V _{GEN} = 10 V, R _g = 1 Ω	N-Ch		10	15		
			P-Ch		10	15		
Rise Time	t _r		N-Ch		15	25		
			P-Ch		13	20		
Turn-Off Delay Time	t _{d(off)}	P-Channel V _{DD} = - 30 V, R _L = 12.5 Ω I _D ≅ - 2.4 A, V _{GEN} = - 10 V, R _g = 1 Ω	N-Ch		20	30		
			P-Ch		35	55		
Fall Time	t _f		N-Ch		10	15		
			P-Ch		30	45		
Drain-Source Body Diode Characteristics								
Continuous Source-Drain Diode Current	I _S	T _C = 25 °C	N-Ch			2.6	A	
			P-Ch			- 2.8		
Pulse Diode Forward Current ^a	I _{SM}		N-Ch			20		
			P-Ch			- 25		
Body Diode Voltage	V _{SD}	I _S = 1.7 A	N-Ch		0.8	1.2	V	
		I _S = - 2 A	P-Ch		- 0.8	- 1.2		
Body Diode Reverse Recovery Time	t _{rr}	N-Channel I _F = 1.7 A, dI/dt = 100 A/μs, T _J = 25 °C	N-Ch		30	60	ns	
			P-Ch		30	50		
Body Diode Reverse Recovery Charge	Q _{rr}		P-Channel I _F = - 2 A, dI/dt = - 100 A/μs, T _J = 25 °C	N-Ch		32	50	nC
				P-Ch		35	60	
Reverse Recovery Fall Time	t _a			N-Ch		25		ns
				P-Ch		16		
Reverse Recovery Rise Time	t _b		N-Ch		5			
			P-Ch		14			

Notes:


a. Guaranteed by design, not subject to production testing.

b. Pulse test; pulse width $\leq 300\text{ }\mu\text{s}$, duty cycle $\leq 2\%$.


Stresses beyond those listed under "Absolute Maximum Ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated in the operational sections of the specifications is not implied. Exposure to absolute maximum rating conditions for extended periods may affect device reliability.

N-CHANNEL TYPICAL CHARACTERISTICS 25 °C, unless otherwise noted



Output Characteristics





Transfer Characteristics








On-Resistance vs. Drain Current and Gate Voltage




Capacitance





N-CHANNEL TYPICAL CHARACTERISTICS 25 °C, unless otherwise noted

Source-Drain Diode Forward Voltage

On-Resistance vs. Gate-to-Source Voltage

Threshold Voltage

Single Pulse Power, Junction-to-Ambient


* $V_{GS} >$ minimum V_{GS} at which $R_{DS(on)}$ is specified



Safe Operating Area


N-CHANNEL TYPICAL CHARACTERISTICS 25 °C, unless otherwise noted

 T_C - Case Temperature (°C)

Current Derating*

 T_C - Case Temperature (°C)


Power Derating

Single Pulse Avalanche Capability

* The power dissipation P_D is based on $T_{J(max)} = 150$ °C, using junction-to-case thermal resistance, and is more useful in settling the upper dissipation limit for cases where additional heatsinking is used. It is used to determine the current rating, when this rating falls below the package limit.


N-CHANNEL TYPICAL CHARACTERISTICS 25 °C, unless otherwise noted


P-CHANNEL TYPICAL CHARACTERISTICS 25 °C, unless otherwise noted



Output Characteristics





Transfer Characteristics








On-Resistance vs. Drain Current




Capacitance




P-CHANNEL TYPICAL CHARACTERISTICS 25 °C, unless otherwise noted

Source-Drain Diode Forward Voltage

On-Resistance vs. Gate-to-Source Voltage

Threshold Voltage

Single Pulse Power


* $V_{GS} >$ minimum V_{GS} at which $R_{DS(on)}$ is specified


Safe Operating Area, Junction-to-Case

P-CHANNEL TYPICAL CHARACTERISTICS 25 °C, unless otherwise noted


T_C - Case Temperature (°C)
Current Derating*





T_C - Case Temperature (°C)
Power Derating, Junction-to-Foot




Single Pulse Avalanche Capability

* The power dissipation P_D is based on $T_{J(max)} = 150$ °C, using junction-to-case thermal resistance, and is more useful in settling the upper dissipation limit for cases where additional heatsinking is used. It is used to determine the current rating, when this rating falls below the package limit.

P-CHANNEL TYPICAL CHARACTERISTICS 25 °C, unless otherwise noted

Normalized Thermal Transient Impedance, Junction-to-Ambient

Normalized Thermal Transient Impedance, Junction-to-Foot

SOIC (NARROW): 8-LEAD


JEDEC Part Number: MS-012



DIM	MILLIMETERS		INCHES	
	Min	Max	Min	Max
A	1.35	1.75	0.053	0.069
A ₁	0.10	0.20	0.004	0.008
B	0.35	0.51	0.014	0.020
C	0.19	0.25	0.0075	0.010
D	4.80	5.00	0.189	0.196
E	3.80	4.00	0.150	0.157
e	1.27 BSC		0.050 BSC	
H	5.80	6.20	0.228	0.244
h	0.25	0.50	0.010	0.020
L	0.50	0.93	0.020	0.037
q	0°	8°	0°	8°
S	0.44	0.64	0.018	0.026

ECN: C-06527-Rev. I, 11-Sep-06
DWG: 5498

RECOMMENDED MINIMUM PADS FOR SO-8



Recommended Minimum Pads
Dimensions in Inches/(mm)

Disclaimer

All products due to improve reliability, function or design or for other reasons, product specifications and data are subject to change without notice.

Taiwan VBsemi Electronics Co., Ltd., branches, agents, employees, and all persons acting on its or their representatives (collectively, the "Taiwan VBsemi"), assumes no responsibility for any errors, inaccuracies or incomplete data contained in the table or any other any disclosure of any information related to the product.(www.VBsemi.tw)

Taiwan VBsemi makes no guarantee, representation or warranty on the product for any particular purpose of any goods or continuous production. To the maximum extent permitted by applicable law on Taiwan VBsemi relinquished: (1) any application and all liability arising out of or use of any products; (2) any and all liability, including but not limited to special, consequential damages or incidental ; (3) any and all implied warranties, including a particular purpose, non-infringement and merchantability guarantee.

Statement on certain types of applications are based on knowledge of the product is often used in a typical application of the general product VBsemi Taiwan demand that the Taiwan VBsemi of. Statement on whether the product is suitable for a particular application is non-binding. It is the customer's responsibility to verify specific product features in the products described in the specification is appropriate for use in a particular application. Parameter data sheets and technical specifications can be provided may vary depending on the application and performance over time. All operating parameters, including typical parameters must be made by customer's technical experts validated for each customer application. Product specifications do not expand or modify Taiwan VBsemi purchasing terms and conditions, including but not limited to warranty herein.

Unless expressly stated in writing, Taiwan VBsemi products are not intended for use in medical, life saving, or life sustaining applications or any other application. Wherein VBsemi product failure could lead to personal injury or death, use or sale of products used in Taiwan VBsemi such applications using client did not express their own risk. Contact your authorized Taiwan VBsemi people who are related to product design applications and other terms and conditions in writing.

The information provided in this document and the company's products without a license, express or implied, by estoppel or otherwise, to any intellectual property rights granted to the VBsemi act or document. Product names and trademarks referred to herein are trademarks of their respective representatives will be all.

Material Category Policy

Taiwan VBsemi Electronics Co., Ltd., hereby certify that all of the products are determined to be RoHS compliant and meets the definition of restrictions under Directive of the European Parliament 2011/65 / EU, 2011 Nian. 6. 8 Ri Yue restrict the use of certain hazardous substances in electrical and electronic equipment (EEE) - modification, unless otherwise specified as inconsistent.(www.VBsemi.tw)

Please note that some documents may still refer to Taiwan VBsemi RoHS Directive 2002/95 / EC. We confirm that all products identified as consistent with the Directive 2002/95 / EC European Directive 2011/65 /.

Taiwan VBsemi Electronics Co., Ltd. hereby certify that all of its products comply identified as halogen-free halogen-free standards required by the JEDEC JS709A. Please note that some Taiwanese VBsemi documents still refer to the definition of IEC 61249-2-21, and we are sure that all products conform to confirm compliance with IEC 61249-2-21 standard level JS709A.