

■ Features

- Low-profile type with low RDC and large current.
- The magnetic shielded type is suitable and high density mounting.
- Available on tape and reel for auto-insertion.
- Ideal for variety of DC-DC converter inductor applications..
- Operating temperature:-40°C ~ +125°C.

■ Applications

- Portable communication equipment.
- Notebook PC,digital camera,LCD television set.
- Power supply for VTR,OA equipment.
- DC/DC converters.

■ Product Identification

YSLF □□□□ - □□□ □
 (1) (2) (3) (4)


(1) : Type

(2) : Dimensions

(3) : Inductance value

(4) : Inductance Tolerance; N=±30%,M=±20%, K=±10%

■ Shapes and Dimensions (Unit: mm)




TYPE	A	B	C	D	E	F Ref.	G Ref.	H Ref.
YSLF1045	10.1±0.3	4.5±0.3	6.0±0.2	3.0±0.2	2.0	2.5	5.6	3.2

■ YSLF1045 Series

Part Number	Inductance (uH)	Test Freq.(KHz)	DCR Max.(Ω)	Rated Current Max. (A)
YSLF1045-3R3□	3.3	100	0.020	4.90
YSLF1045-4R7□	4.7	100	0.024	4.50
YSLF1045-5R6□	5.6	100	0.027	3.80
YSLF1045-100□	10	100	0.044	2.50
YSLF1045-150□	15	100	0.057	2.20
YSLF1045-220□	22	100	0.071	1.90
YSLF1045-330□	33	100	0.099	1.60
YSLF1045-470□	47	100	0.120	1.40
YSLF1045-680□	68	100	0.168	1.20
YSLF1045-101□	100	100	0.240	1.00
YSLF1045-151□	150	100	0.420	0.79
YSLF1045-221□	220	100	0.564	0.65
YSLF1045-331□	330	100	0.816	0.54
YSLF1045-471□	470	100	1.236	0.47
YSLF1045-681□	680	100	1.920	0.38
YSLF1045-102□	1000	100	3.360	0.29
YSLF1045-152□	1500	100	4.080	0.22


- ※ The saturation current value is the DC current value having inductance decrease down to 30%.(at 20°C)
- ※ The temperature rise current value is the DC current value having temperature increase up to 40°C. (at 20°C)
- ※ The rated current is the DC current value that satisfies both of current value saturation current value and temperature rise current value.

■ Taping Dimensions(Unit:mm)




TYPE	W	A	B	C	D	E	P	K Ref	T	MPQ
YSLF1045	24±0.3	10.8±0.1	10.8±0.1	10.75	11.5±0.1	4.75±0.1	16±0.1	4.95	0.35±0.05	800

■ Reel Dimensions(Unit:mm)




TYPE	W	W1	W2	W3	A	B	C	D
YSLF1045	330±2.0	24.4±1.50	30.4MAX	23.9 Min	13.0±0.50	21.0±0.80	2.0±0.50	100 Min

■ Direction of rolling



■ Cover tape peel off condition



Cover tape peel force shall be 0.1N to 1.3N.

Reference peel speed $300 \pm 10 \text{ mm/min.}$