

**SPECIFICATION OF QUARTZ CRYSTAL UNITS****1.HOLDER TYPE:** SMD SEAM SEALING X'TAL 3.2\*2.5

8.000000 MHz

**2. ELECTRICAL SPECIFICATIONS**

Standard atmospheric conditions

Unless otherwise specified, the standard range of atmospheric conditions for making measurement

Ambient temperature :  $25 \pm 3^\circ\text{C}$ 

Relative humidity : 40% ~ 70%

If there is any doubt about the results ,measurement shall be made within the following limits .

Ambient temperature :  $25 \pm 3^\circ\text{C}$ 

Relative humidity : 40% ~ 70%

Electriacal characteristics measured by S&amp;A250B or equivalent .

The crystal is using AT CUT (thinkness shear mode).

**3.ELECTRICAL CHARACTERISTICS**

	Parameters	SYM	Electrical Spec				Notes
			MIN	TYP	MAX	UNITS	
1	Nominal Frequency	FL	8.000000			MHz	
2	Oscillation mode	-	Fundamental			-	
3	Load Capacitance	CL	20			pF	
4	Frequency Tolerance	-	$\pm 10$			ppm	at $25 \pm 3^\circ\text{C}$
5	Operating Temperature	-	-20	~	70	°C	
6	Temperature drift (TC)	-	$\pm 30$			ppm	-20°C ~ +70°C
	Temperature drift (TC)	-					
	Temperature drift (TC)	-					
7	Equivalent Resistance Rr	Rr	-	-	300	Ω	
8	Drive Level	DL	-	100	300	uW	
9	Shunt Capacitance C0	C0	-	-	2.00	pF	
10	Insulation Resistance	-	500	-	-	MΩ	at DC 100V
11	Aging	-	$\pm 2$			ppm	Year
12	Storage Temperature Range	-	-55	~	125	°C	

