


600V N-Channel MOSFET

FEATURES

- Fast switching
- Integrate fast recovery diode
- Fast switching speed
- 100% avalanche tested
- Improved dv/dt capability

APPLICATIONS

- Switch Mode Power Supply (SMPS)
- Motor Controls
- Power Factor Correction (PFC)



Device Marking and Package Information

Device	Package	Marking
CSFR7N60F	TO-220F	CSFR7N60F
CSFR7N60K	TO-262	CSFR7N60K
CSFR7N60D	TO-252	CSFR7N60D
CSFR7N60U	TO-251	CSFR7N60U

Absolute Maximum Ratings $T_C = 25^\circ\text{C}$, unless otherwise noted

Parameter	Symbol	Value				Unit
		TO-220F	TO-262	TO-252	TO-251	
Drain-Source Voltage (V _{GS} = 0V)	V _{DSS}	600				V
Continuous Drain Current	I _D	7				A
Pulsed Drain Current (note1)	I _{DM}	28				A
Gate-Source Voltage	V _{GSS}	± 30				V
Single Pulse Avalanche Energy (note2)	E _{AS}	224.5				mJ
Avalanche Current (note1)	I _{AS}	6.7				A
Repetitive Avalanche Energy (note1)	E _{AR}	134.7				mJ
Power Dissipation (T _C = 25°C)	P _D	63	97			W
Operating Junction and Storage Temperature Range	T _J , T _{stg}	-55~+150				°C

Thermal Resistance

Parameter	Symbol	Value				Unit
		TO-220F	TO-262	TO-252	TO-251	
Thermal Resistance, Junction-to-Case	R _{thJC}	1.98	1.29			°C/W
Thermal Resistance, Junction-to-Ambient	R _{thJA}	62.5	60			

Specifications $T_J = 25^{\circ}\text{C}$, unless otherwise noted

Parameter	Symbol	Test Conditions	Value			Unit
			Min.	Typ.	Max.	
Static						
Drain-Source Breakdown Voltage	V _{(BR)DSS}	V _{GS} = 0V, I _D = 250μA	600	--	--	V
Zero Gate Voltage Drain Current	I _{DSS}	V _{DS} = 600V, V _{GS} = 0V, T _J = 25°C	--	--	1	μA
Gate-Source Leakage	I _{GSS}	V _{GS} = ±30V	--	--	±100	nA
Gate-Source Threshold Voltage	V _{GS(th)}	V _{DS} = V _{GS} , I _D = 250μA	3.0	--	4.0	V
Drain-Source On-Resistance (Note3)	R _{DS(on)}	V _{GS} = 10V, I _D = 3.5A	--	1.1	1.3	Ω
Dynamic						
Input Capacitance	C _{iss}	V _{GS} = 0V, V _{DS} = 25V, f = 1.0MHz	--	912	--	pF
Output Capacitance	C _{oss}		--	92	--	
Reverse Transfer Capacitance	C _{rss}		--	11	--	
Total Gate Charge	Q _g	V _{DD} = 480V, I _D = 7.0A, V _{GS} = 10V	--	28	--	nC
Gate-Source Charge	Q _{gs}		--	4.3	--	
Gate-Drain Charge	Q _{gd}		--	14	--	
Turn-on Delay Time	t _{d(on)}	V _{DD} 300V, I _D =7A, R _G =25Ω	--	38.5	--	ns
Turn-on Rise Time	t _r		--	14	--	
Turn-off Delay Time	t _{d(off)}		--	119	--	
Turn-off Fall Time	t _f		--	54	--	
Drain-Source Body Diode Characteristics						
Continuous Body Diode Current	I _S	T _C = 25 °C	--	--	7.0	A
Pulsed Diode Forward Current	I _{SM}		--	--	28	
Body Diode Voltage	V _{SD}	T _J = 25°C, I _{SD} = 3.5A, V _{GS} = 0V	--	--	1.4	V
Reverse Recovery Time	t _{rr}	V _{GS} = 0V, I _S = 7A, diF/dt = 100A/μs	--	82	--	ns
Reverse Recovery Charge	Q _{rr}		--	0.12	--	μC

Notes

1. Repetitive Rating: Pulse width limited by maximum junction temperature
2. $L=10mH, V_{DD} = 50V, R_G = 25\Omega$, Starting $T_J = 25^{\circ}\text{C}$
3. Pulse Test: Pulse width $\leq 300\mu s$, Duty Cycle $\leq 1\%$

Typical Characteristics $T_J = 25^\circ\text{C}$, unless otherwise noted

Figure 1. Output Characteristics ($T_J = 25^\circ\text{C}$)




Figure 2. Body Diode Forward Voltage




Figure 3. Drain Current vs. Temperature




Figure 4. BV_{DSS} Variation vs. Temperature




Figure 5. Transfer Characteristics





Figure 6. On-Resistance vs. Temperature



Typical Characteristics $T_J = 25^\circ\text{C}$, unless otherwise noted

Figure 7. Capacitance




Figure 8. Gate Charge




Figure 9. Transient Thermal Impedance
TO-262, TO-251, TO-252




Figure 10. Transient Thermal Impedance
TO-220F









Figure A: Gate Charge Test Circuit and Waveform

Figure B: Resistive Switching Test Circuit and Waveform

Figure C: Unclamped Inductive Switching Test Circuit and Waveform



TO-220F




TO-251



TO-252



TO-262



Disclaimer

All product specifications and data are subject to change without notice.

For documents and material available from this datasheet, Suzhou Convert does not warrant or assume any legal liability or responsibility for the accuracy, completeness of any product or technology disclosed hereunder.

No license, express or implied, by estoppels or otherwise, to any intellectual property rights is granted by this document or by any conduct of Suzhou Convert.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications unless. Customers using or selling Suzhou Convert products not expressly indicated for use in such applications do so entirely at their own risk and agree to fully indemnify Suzhou Convert for any damages arising or resulting from such use or sale.

Suzhou Convert disclaims any and all liability arising out of the use or application of any product described herein or of any information provided herein to the maximum extent permitted by law. The product specifications do not expand or otherwise modify Suzhou Convert's terms and conditions of purchase, including but not limited to the warranty expressed therein, which apply to these products.

Suzhou Convert Semiconductor CO., Ltd. strives to supply high-quality high-reliability products. However, any and all semiconductor products fail with some probability. It is possible that these probabilistic failures could give rise to accidents or events that could endanger human lives that could give rise to smoke or fire, or that could cause damage to other property. When designing equipment, adopt safety measures so that these kinds of accidents or events cannot occur. Such measures include but are not limited to protective circuits and error prevention circuits for safe design, redundant design, and structural design.

In the event that any or all Suzhou Convert products(including technical data, services) described or contained herein are controlled under any of applicable local export control laws and regulations, such products must not be exported without obtaining the export license from the authorities concerned in accordance with the above law.

Information (including circuit diagrams and circuit parameters) herein is for example only; it is not guaranteed for volume production. Suzhou Convert believes information herein is accurate and reliable, but no guarantees are made or implied regarding its use or any infringements of intellectual property rights or other rights of third parties.