規格承認書

PECIFICATION FOR APPROVAL

客 戶					
CUSTOME	R :				
項目					
ITEM	:_	电磁无源一体蜂鸣器(外部驱动)			
型號					
TYPE	:	GMC0955YB-6.5-140R2730 通用型(电阻 6.5-140 欧)			
描述	_				
DESCRIP	TION :	φ9.0 x H5.5 mm 2700Hz 6.5-140 Ω/1.5-15V ≥80dB PBT 材质			
客戶料號					
CUSTOMER NO.:					
規格書	號				
SPECIFICATION NO.:					
版本					
EDITION	NO. :	V1.0			
日 期	•				
DATE	:	20			

客戶承認

CUSTOMER CONFIRM AND SIGN

檢查	審核	承認
TESTED BY	CHECKED BY	APPROVED BY

東莞市赢海電子有限公司

DONGUAN INGHAI ELECTRONICS CO.,LTD

製作	審查	確認
ISSUED BY	CHECKED BY	APPROVED BY
周明	刘承成	


地址: 廣東省東莞市長安鎮上沙第五工业区新春科技园

網址: HTTP://WWW.INGHAI.COM

DONGGUAN INGHAI ELECTRONICS CO.,LTD

Model NO: GMC0955YB-6.5140R2700

A: DIMEMSIONS: Unit:mm Tolerance: ± 0.5



B: SPECIFICATIONS

Model NO	GMC0955YB
*Rated Voltage	1.5-15Vo-p
Operating Voltage	1.5~15.0Vo-p
*Max.Rated Current	Max.80mA
*Sound Pressure level(dB)at10cm	Min.80dB
*Resonant Frequency	2700 Hz
Coil Resistance	$6.5 - 140 \pm 15\%$
Operating Temperature	-20 °C∼+70 °C
Storage Temperature	-30 ℃~+80 ℃
Case material and color	PBT / Black

^{*}Value applying rated voltage


Measuring condition

Part shall be measured under a condition (Temperature: $5\sim35^{\circ}$ C, Humidity: $45\%\sim85\%$ R.H., Atmospheric


pressure: 860 \sim 1060hPa) unless the standard condition (Temperature: 25±3°C, Humidity: 60±10%R.H. Atmospheric pressure: 860 \sim 1060hPa) is regulated to measure.

C: Acoustic Characteristics:


The oscillation frequency, current consumption and sound pressure are measured by the measuring instruments shown below



In the measuring test, buzzer is placed as follows:



D: Typical Frequency Response Curve



E: Reliability Test

After any following tests the part shall meet specifications without any degradation in appearance and performance except SPL. SPL shall not deviate more than -10 dB from the initial value

1. Ordinary Temperature Life Test

The part shall be subjected to 96 hours at $25\pm10^{\circ}$ C. Input rated voltage Resonant frequency, 1/2 duty Square wave.

2. High Temperature Test

The part shall be capable of with standing a storage temperature of +80 ℃ for 96 hours.

3. Low Temperature Test

The part shall be capable of with standing a storage temperature of -30°C for 96 hours.

4. Humidity Test

Temperature:+40 $^{\circ}$ C \pm 3 $^{\circ}$ C Relative Humidity:90% \sim 95% Duration: 48 hours and expose to room temperature for 6 hours

5. Temperature Shock Test

Temperature:70°C /1hour \rightarrow 25°C/3hours \rightarrow -30°C/1hour \rightarrow 25°C/3hours (1cycle)

Total cycle: 10 cycles

6. Drop Test

Standard Packaging From 120mm(Drop on hard wood or board of 5cm thick, three sides, six plain.)

7. Vibration Test

Vibration: 1000cycles /min. Amplitude: 1.5mm, Duration: 1 hour in each 3 axes

Note:

As this product is not protected from foreign material entering, please make sure that any foreign materials (e.g. magnetic powder, washing solvent, flux, corrosive gas) do not enter this product in your production processes. The functional degradation (e.g. SPL down) may occur if foreign material enter it.