規格承認書

PECIFICATION FOR APPROVAL

客戶

CUSTOMER : 电压可以做到 1.5V 3V 5V 12V

項目

ITEM: 电磁有源一体蜂鸣器(内含驱动电路)

型號

TYPE : GMD0942YB-1.5-12V2700 通用型(电压分 1.5-12V)

描述

DESCRIPTION: 9.0 x 4.2 MM 2700Hz DC1.5-12V >=75DB PPS 材质 P=5 MM

客戶料號

CUSTOMER NO.:

規格書號

SPECIFICATION NO.:

版本

EDITION NO. : V1.

日 期

DATE : 20

客戶承認

CUSTOMER CONFIRM AND SIGN

檢查	審核	承認
TESTED BY	CHECKED BY	APPROVED BY

東莞市赢海電子有限公司

DONGUAN INGHAI ELECTRONICS CO.,LTD

製作	審查	確認
ISSUED BY	CHECKED BY	APPROVED BY
周明	李林	


地址: 廣東省東莞市長安鎮上沙管理區北橫路8號

網址: HTTP://WWW.INGHAI.COM

DONGGUAN INGHAI ELECTRONICS CO.,LTD

Model NO: GMD0942YB-1.5-12V2700

DIMEMSIONS Unit:mm Tolerance: ± 0.5



SPECIFICATIONS

Model NO	GMD0942YB
Rated Voltage	1.5-12VDC
Operating Voltage	1.5~15VDC
Max.Rated Current	Max.50mA
Sound Pressure level(dB)at10cm	Min.75dB
Resonant Frequency	2700±300Hz
Operating Temperature	-20 °C∼+75 °C
Storage Temperature	-30 °C∼+80 °C
Case material and color	PPS / Black

Measuring condition

Part shall be measured under a condition (Temperature: $5\sim35^{\circ}$ C, Humidity: $45\%\sim85\%$ R.H., Atmospheric pressure: $860\sim1060$ hPa) unless the standard condition (Temperature: $25\pm3^{\circ}$ C, Humidity: $60\pm10\%$ R.H. Atmospheric pressure: $860\sim1060$ hPa) is regulated to measure.

Reliability Test

After any following tests the part shall meet specifications without any degradation in appearance and performance except SPL. SPL shall not deviate more than -10 dB from the initial value

1. Ordinary Temperature Life Test

2. High Temperature Test

The part shall be capable of with standing a storage temperature of +80 ℃ for 96 hours.

3. Low Temperature Test

The part shall be capable of with standing a storage temperature of -30℃ for 96 hours.

4. Humidity Test

Temperature:+40 $^{\circ}$ C \pm 3 $^{\circ}$ C Relative Humidity:90% \sim 95% Duration: 48 hours and expose to room temperature for 6 hours

5. Temperature Shock Test

Temperature:75 $^{\circ}$ /1hour \rightarrow 25 $^{\circ}$ C/3hours \rightarrow -30 $^{\circ}$ C/1hour \rightarrow 25 $^{\circ}$ C/3hours (1cycle)

Total cycle: 10 cycles 6. **Drop Test**

Standard Packaging From 120mm(Drop on hard wood or board of 5cm thick, three sides, six plain.)

7. Vibration Test

Vibration: 1000cycles /min. Amplitude: 1.5mm, Duration: 1 hour in each 3 axes

Note:

As this product is not protected from foreign material entering, please make sure that any foreign materials (e.g. magnetic powder, washing solvent, flux, corrosive gas) do not enter this product in your production processes. The functional degradation (e.g. SPL down) may occur if foreign material enter it.