




Specifications :

- Voltage rating: 250V AC / DC
- Current rating: 3A AC / DC
- Withstanding voltage: 800V AC/minute
- Temperature range: -25°C~+85°C
- Insulation resistance:≥1000MΩ
- Contact resistance: ≤10mΩ
- After environmental testing: ≤20mΩ

X2530 H X-2*XX X-PT XX

- ① Series No.
② Category: H-HSG
③ Welding Board Angle: Blank-ordinary
④ Row No.-Pin No.: 2*XX-2*02~2*32P
⑤ Plug the Pin & special No.
⑥ Material: PT-PBT 94V-0
⑦ Color: Blank-Natural Color Black

Poles	Dimensions(mm)			Poles	Dimensions(mm)			Poles	Dimensions(mm)		
	A	B	C		A	B	C		A	B	C
2*02	2.54	5.52	7.12	2*13	30.48	33.46	35.06	2*24	58.42	61.40	63.00
2*03	5.08	8.06	9.66	2*14	33.02	36.00	37.60	2*25	60.96	63.94	65.54
2*04	7.62	10.60	12.20	2*15	35.56	38.54	40.14	2*26	63.50	66.48	68.08
2*05	10.16	13.14	14.74	2*16	38.10	41.08	42.68	2*27	66.04	69.02	70.62
2*06	12.70	15.68	17.28	2*17	40.64	43.62	45.22	2*28	68.58	71.56	73.16
2*07	15.24	18.22	19.82	2*18	43.18	46.16	47.76	2*29	71.12	74.10	75.70
2*08	17.78	20.76	22.36	2*19	45.72	48.70	50.30	2*30	73.66	76.64	78.24
2*09	20.32	23.30	24.90	2*20	48.26	51.24	52.84	2*31	76.20	79.18	80.78
2*10	22.86	25.84	27.44	2*21	50.80	53.78	55.38	2*32	78.74	81.72	83.32
2*11	25.40	28.38	29.98	2*22	53.34	56.32	57.92				
2*12	27.94	30.92	32.52	2*23	55.88	58.86	60.46				

X2530H-2*XX-PT	PBT UL 94V-0	X2530T	X2530W
PART NO	Material	Suitable XKB Terminal	Suitable XKB Terminal

For and on behalf of
XKB INDUSTRIAL PRECISION CO., LIMITED
香港星坤工業精密有限公司

MARK	DESCRIPTION	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES
△ X					ANGULAR ±5°
△ X					L ≤ 4 ±0.2
△ X					4 < L ≤ 16 ±0.3
					16 < L ≤ 63 ±0.4
					L > 63 ±0.5

DSND		DATE		SCALE: N/A	MODEL TYPE: X2530H-2*XX-PT
DWN		DATE		VIEW:	PART NO.: 2.54 mm Crimp Style Connectors
CHKD		DATE		UNIT: mm	DWG NO.:
APPD		DATE		SIZE: A4	
XKB INDUSTRIAL PRECISION CO.,LIMITED					WEIGHT 1.0g
					SHEET 1/1
					REVISION A0