




■ Specifications :

- Voltage rating: 250V AC / DC
- Current rating: 3A AC / DC
- Withstanding voltage: 1000V AC/minute
- Temperature range: -25°C~+85°C
- Insulation resistance:≥1000MΩ
- Contact resistance: ≤10mΩ
- After environmental testing: ≤20mΩ

X8826 W R X- 2*XX- N0 SN-XX
① ② ③ ④ ⑤ ⑥ ⑦ ⑧

- ① Series No.
- ② Category: W-WAFER
- ③ Welding Board Angle: R-Right Angle 90°
- ④ Welding Way: Blank-DIP ;
- ⑤ Row No.-Pin No.:2*XX-Double Row
- ⑥ Material: N0 -PA66 94V-0
- ⑦ Plating Category: SN-Bright Tin Plating
- ⑧ Color : Blank-Natural Color

Poles	Dimensions(mm)		Poles	Dimensions(mm)	
	A	B		A	B
02	2.50	7.50	12	27.50	32.50
03	5.00	10.00	13	30.00	35.00
04	7.50	12.50	14	32.50	37.50
05	10.00	15.00	15	35.00	40.00
06	12.50	17.50	16	37.50	42.50
07	15.00	20.00	17	40.00	45.00
08	17.50	22.50	18	42.50	47.50
09	20.00	25.00	19	45.00	50.00
10	22.50	27.50	20	47.50	52.50
11	25.00	30.00			

X8826WR-2*XX-N0SN	Nylon 66 UL 94V-0	Brass	Tin-Plated	X8826H
PART N0	Material	Material(Pin)	Finish(Pin)	Suitable XKB Terminal
DSND	DATE	SCALE: N/A	MODEL TYPE: X8826WR-2*XX-N0SN	
DWN	DATE	VIEW:	PART NO.: 2.50mm Crimp style Connector	
CHKD	DATE	UNIT: mm	DWG NO.:	
APPD	DATE	SIZE: A4		
			WEIGHT	SHEET
			1.0g	1/1
			REVISION	
			A0	

△ X					ANGULAR	± 5°
△ X					L ≤ 4	± 0.2
△ X					4 < L ≤ 16	± 0.3
△ X					16 < L ≤ 63	± 0.4
MARK					L > 63	± 0.5

DESCRIPTION	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES
-------------	------	---------	----------	------------------------

For and on behalf of
XKB INDUSTRIAL PRECISION CO., LIMITED
香港星坤工業精密有限公司

Authorized Signature(s)

XKB INDUSTRIAL PRECISION CO.,LIMITED