



SMF14N65


650V N-Channel MOSFET

● Features:

- 14A, 650V, $R_{DS(on)(Typ)} = 0.6\Omega$ @ $V_{GS} = 10V$
- Low Gate Charge
- Low C_{rss}
- 100% Avalanche Tested
- Fast Switching
- Improved dv/dt Capability

● Application:

- High Frequency Switching Mode Power Supply
- Active Power Factor Correction



Absolute Maximum Ratings ($T_c = 25^\circ C$ unless otherwise noted)

Symbol	Parameter	Value	Unit	
V_{DSS}	Drain-Source Voltage	650	V	
I_D	Drain Current - Continuous ($T_c = 25^\circ C$)	14*	A	
	- Continuous ($T_c = 100^\circ C$)	8.6*	A	
I_{DM}	Drain Current -Pulsed	56*	A	
V_{GSS}	Gate-Source Voltage	± 30	V	
E_{AS}	Single Pulsed Avalanche Energy	(Note 2)	940	mJ
I_{AR}	Avalanche Current	(Note 1)	14.0	A
E_{AR}	Repetitive Avalanche Energy	(Note 1)	28	mJ
dv/dt	Peak Diode Recovery dv/dt	(Note 3)	4.5	V/ns
P_D	Power Dissipation ($T_c = 25^\circ C$)	54	W	
	-Derate above $25^\circ C$	0.43	W/ $^\circ C$	
T_j	Operating Junction Temperature	150	$^\circ C$	
T_{stg}	Storage Temperature Range	-55 to +150	$^\circ C$	

* Drain Current Limited by Maximum Junction Temperature.

Thermal Characteristics

Symbol	Parameter	Max	Unit
$R_{\theta JC}$	Thermal Resistance, Junction to Case	2.31	$^\circ C / W$
$R_{\theta JA}$	Thermal Resistance, Junction to Ambient	62.5	$^\circ C / W$

**SMF14N65**

650V N-Channel MOSFET


Electrical Characteristics(Tc=25°C unless otherwise noted)

Symbol	Parameter	Test Conditions	Min	Typ	Max	Unit
Off Characteristics						
BV _{DSS}	Drain-source Breakdown Voltage	V _{GS} =0V, I _D =250μA	650	--	--	V
△BV _{DSS} /△T _J	Breakdown Voltage Temperature Coefficient	I _D =250μA (Referenced to 25°C)	--	0.65	--	V/°C
I _{DSS}	Zero Gate Voltage Drain Current	V _{DS} =650V, V _{GS} =0V	--	--	1	μA
		V _{DS} =520V, T _c =125°C	--	--	10	μA
I _{GSSF}	Gate-Body Leakage Current,Forward	V _{GS} =+30V, V _{DS} =0V	--	--	100	nA
I _{GSSR}	Gate-Body Leakage Current,Reverse	V _{GS} =-30V, V _{DS} =0V	--	--	-100	nA
On Characteristics						
V _{GS(th)}	Gate Threshold Voltage	V _{DS} = V _{GS} , I _D =250μA	2.0	--	4.0	V
R _{DS(on)}	Static Drain-Source On-Resistance	V _{GS} =10 V, I _D =7.0A	--	0.6	0.75	Ω
g _{FS}	Forward Transconductance	V _{DS} =40 V, I _D =7.0A (Note4)	--	9.0	--	S
Dynamic Characteristics						
C _{iss}	Input Capacitance	V _{DS} =25V, V _{GS} =0V, f=1.0MHz	--	2150	--	pF
C _{oss}	Output Capacitance		--	255	--	pF
C _{rss}	Reverse Transfer Capacitance		--	22.5	--	pF
Switching Characteristics						
t _{d(on)}	Turn-On Delay Time	V _{DD} = 325 V, I _D = 14 A, R _G = 25 Ω (Note4,5)	--	55	--	ns
t _r	Turn-On Rise Time		--	100	--	ns
t _{d(off)}	Turn-Off Delay Time		--	115	--	ns
t _f	Turn-Off Fall Time		--	75.0	--	ns
Q _g	Total Gate Charge	V _{DS} = 520 V, I _D = 14.0 A, V _{GS} = 10 V (Note4,5)	--	49	--	nC
Q _{gs}	Gate-Source Charge		--	12	--	nC
Q _{gd}	Gate-Drain Charge		--	22	--	nC
Drain-Source Diode Characteristics and Maximum Ratings						
I _S	Maximum Continuous Drain-Source Diode Forward Current	--	--	14	--	A
I _{SM}	Maximum Pulsed Drain-Source Diode Forward Current	--	--	56	--	A
V _{SD}	Drain-Source Diode Forward Voltage	V _{GS} =0V, I _S =14.0A	--	--	1.3	V
t _{rr}	Reverse Recovery Time	V _{GS} =0V, I _S =14.0A, d I _F /dt=100A/μs (Note4)	--	480	--	ns
Q _{rr}	Reverse Recovery Charge		--	5.25	--	μC


Notes:

1. Repetitive Rating:Pulse Width Limited by Maximum Junction Temperature.
2. L = 10mH, I_{AS} =14.0A, V_{DD} = 50V, R_G = 25 Ω, Starting T_J = 25°C.
3. I_{SD}≤14.0A, di/dt≤200A/μs, V_{DD}≤BV_{DSS}, Starting T_J = 25°C.
4. Pulse Test : Pulse Width ≤300 μ s, Duty Cycles≤2%.
5. Essentially Independent of Operating Temperature.


On-Region Characteristics




**On-Resistance Variation vs.
Drain Current and Gate Voltage**




Capacitance Characteristics




Transfer Characteristics



**Body Diode Forward Voltage Variation
vs. Source Current and Temperature**



Gate Charge Characteristics







SMF14N65

650V N-Channel MOSFET


Breakdown Voltage Variation vs. Temperature




On-Resistance Variation vs. Temperature



Maximum Safe Operating Area



Maximum Drain Current Vs. Case Temperature



**SMF14N65**

650V N-Channel MOSFET

TO-220F Package Dimensions

UNIT: mm

SYMBOL	min	nom	max	SYMBOL	min	nom	max
A	9.80		10.60	D			2.54
A1		7.00		D1	1.15		1.55
A2	2.90		3.40	D2	0.60		1.00
A3	9.10		9.90	D3	0.20		0.50
B1	15.40		16.40	E	2.24		2.84
B2	4.35		4.95	E1		0.70	
B3	6.00		7.40	E2		1.0×45°	
C	3.00		3.70	E3	0.35		0.65
C1	15.00		17.00	E4	2.30		3.30
C2	8.80		10.80	α (度)		30°	

