

**SMT8N60**


600V N-Channel MOSFET

● Features:

- 8.0A, 600V, $R_{DS(on)(Typ)} = 1.0\Omega$ @ $V_{GS} = 10V$
- Low Gate Charge
- Low C_{rss}
- 100% Avalanche Tested
- Fast Switching
- Improved dv/dt Capability

● Application:

- High Frequency Switching Mode Power Supply
- Active Power Factor Correction

**Absolute Maximum Ratings (Tc=25°C unless otherwise noted)**

Symbol	Parameter		Value	Unit	
V_{DSS}	Drain-Source Voltage		600	V	
I_D	Drain Current	- Continuous ($T_c = 25^\circ C$)	8.0*	A	
		- Continuous ($T_c = 100^\circ C$)	5.1*	A	
I_{DM}	Drain Current	-Pulsed	(Note 1)	32*	A
V_{GSS}	Gate-Source Voltage		± 30	V	
E_{AS}	Single Pulsed Avalanche Energy		600	mJ	
I_{AR}	Avalanche Current		8.0	A	
E_{AR}	Repetitive Avalanche Energy		15.0	mJ	
dv/dt	Peak Diode Recovery dv/dt		4.5	V/ns	
P_D	Power Dissipation ($T_c = 25^\circ C$)		116	W	
	-Derate above $25^\circ C$		0.93	W/ $^\circ C$	
T_j	Operating Junction Temperature		150	$^\circ C$	
T_{stg}	Storage Temperature Range		-55 to +150	$^\circ C$	

* Drain Current Limited by Maximum Junction Temperature.

Thermal Characteristics

Symbol	Parameter	Max	Unit
$R_{\theta JC}$	Thermal Resistance, Junction to Case	1.07	$^\circ C / W$
$R_{\theta JA}$	Thermal Resistance, Junction to Ambient	62.5	$^\circ C / W$

	SMT8N60
	600V N-Channel MOSFET

Electrical Characteristics($T_c=25^\circ\text{C}$ unless otherwise noted)

Symbol	Parameter	Test Conditions	Min	Typ	Max	Unit
Off Characteristics						
BV_{DSS}	Drain-source Breakdown Voltage	$V_{\text{GS}}=0\text{V}, I_{\text{D}}=250\mu\text{A}$	600	--	--	V
$\Delta \text{BV}_{\text{DSS}} / \Delta T_J$	Breakdown Voltage Temperature Coefficient	$I_{\text{D}}=250\mu\text{A}$ (Referenced to 25°C)	--	0.7	--	$\text{V}/^\circ\text{C}$
$I_{\text{DS}}^{\text{SS}}$	Zero Gate Voltage Drain Current	$V_{\text{DS}}=600\text{V}, V_{\text{GS}}=0\text{V}$	--	--	1	μA
		$V_{\text{DS}}=480\text{V}, T_c=125^\circ\text{C}$	--	--	10	μA
I_{GSSF}	Gate-Body Leakage Current,Forward	$V_{\text{GS}}=+30\text{V}, V_{\text{DS}}=0\text{V}$	--	--	100	nA
I_{GSSR}	Gate-Body Leakage Current,Reverse	$V_{\text{GS}}=-30\text{V}, V_{\text{DS}}=0\text{V}$	--	--	-100	nA
On Characteristics						
$V_{\text{GS(th)}}$	Gate Threshold Voltage	$V_{\text{DS}}=V_{\text{GS}}, I_{\text{D}}=250\mu\text{A}$	2.0	--	4.0	V
$R_{\text{DS(on)}}$	Static Drain-Source On-Resistance	$V_{\text{GS}}=10\text{ V}, I_{\text{D}}=4.0\text{ A}$	--	1.0	1.2	Ω
g_{FS}	Forward Transconductance	$V_{\text{DS}}=40\text{ V}, I_{\text{D}}=4.0\text{ A}$ (Note4)	--	7	--	S
Dynamic Characteristics						
C_{iss}	Input Capacitance	$V_{\text{DS}}=25\text{V}, V_{\text{GS}}=0\text{V}, f=1.0\text{MHz}$	--	1400	--	pF
C_{oss}	Output Capacitance		--	175	--	pF
C_{rss}	Reverse Transfer Capacitance		--	16	--	pF
Switching Characteristics						
$t_{\text{d(on)}}$	Turn-On Delay Time	$V_{\text{DD}} = 300\text{ V}, I_{\text{D}} = 8.0\text{ A}, R_{\text{G}} = 25\Omega$ (Note4,5)	--	13.5	--	ns
t_r	Turn-On Rise Time		--	105	--	ns
$t_{\text{d(off)}}$	Turn-Off Delay Time		--	128	--	ns
t_f	Turn-Off Fall Time		--	49	--	ns
Q_g	Total Gate Charge	$V_{\text{DS}} = 480\text{ V}, I_{\text{D}} = 8.0\text{ A}, V_{\text{GS}} = 10\text{ V}$ (Note4,5)	--	31	--	nC
Q_{gs}	Gate-Source Charge		--	6.5	--	nC
Q_{gd}	Gate-Drain Charge		--	14.7	--	nC
Drain-Source Diode Characteristics and Maximum Ratings						
I_s	Maximum Continuous Drain-Source Diode Forward Current	--	--	8.0	A	
I_{SM}	Maximum Pulsed Drain-Source Diode Forward Current	--	--	32	A	
V_{SD}	Drain-Source Diode Forward Voltage	$V_{\text{GS}} = 0\text{V}, I_s = 8.0\text{A}$	--	--	1.4	V
t_{rr}	Reverse Recovery Time	$V_{\text{GS}} = 0\text{V}, I_s = 8.0\text{A}, dI_F/dt = 100\text{A}/\mu\text{s}$ (Note4)	--	325	--	ns
Q_{rr}	Reverse Recovery Charge		--	2.7	--	μC

Notes:


- Repetitive Rating:Pulse Width Limited by Maximum Junction Temperature.
- $L = 18.5\text{mH}, I_{\text{AS}} = 8.0\text{A}, V_{\text{DD}} = 50\text{V}, R_{\text{G}} = 25\Omega$, Starting $T_J = 25^\circ\text{C}$.
- $I_{\text{SD}} \leq 8.0\text{A}, di/dt \leq 200\text{A}/\mu\text{s}, V_{\text{DD}} \leq \text{BV}_{\text{DSS}}$, Starting $T_J = 25^\circ\text{C}$.
- Pulse Test : Pulse Width $\leq 300\text{ }\mu\text{s}$, Duty Cycles $\leq 2\%$.
- Essentially Independent of Operating Temperature.




SMT8N60

600V N-Channel MOSFET


On-Region Characteristics




On-Resistance Variation vs. Drain Current and Gate Voltage




Capacitance Characteristics




Transfer Characteristics



Body Diode Forward Voltage Variation vs. Source Current and Temperature



Gate Charge Characteristics







SMT8N60

600V N-Channel MOSFET


Breakdown Voltage Variation vs. Temperature




On-Resistance Variation vs. Temperature



Maximum Safe Operating Area



Maximum Drain Current Vs. Case Temperature





SMT8N60

600V N-Channel MOSFET

TO-220 MECHANICAL DATA

UNIT: mm

SYMBOL	min	nom	max	SYMBOL	min	nom	max
A	4.00		4.80	E	9.50		10.50
B	1.25		1.55	e		2.54	
B1	0.55		1.05	F	1.15		1.45
b1	0.65		0.95	L	12.00		14.00
c	0.40		0.60	L1	2.50	3.00	3.50
D	14.80		16.80	Q	2.50		3.50
D1	6.00		7.00	Q1	1.80		2.80
				φ P	3.40		3.90

