

RoHS

Parts Drawing

REVISIONS

SYM	ECN No.	MODIFICATION	DATE	ISSUED

Note:

1.Material:

1.1,Housing: BLUE G/F,UL94v-0

1.2,Contact: copper alloy,t=0.25mm

1.3,Shell: copper/Ferroalloy alloy,t=0.30mm

2.Specification:

2.1,Current rating:5.0A Max.

2.2,Dielectric withstanding

voltage: 100 V(ac) for 1 min.

2.3,Contact resistance: 30 mΩ Max.

2.4,Insulation resistance: 100 MΩ Min.

2.5,Total mating force: 3.57 Kgf Max.

2.6,Total unmating force: 1.0 Kgf Min.

3.Finish:

3.1,Contact: Plated Golt in Mating Area:

Tin On Solder Talls

Shell: Nickel Plating

4.Environmental:

4.1,Temperature range: -55°C~85°C

PART ON:

907-222AXXX1Y1XX

电镀规格: 02, 镀金1u" 04, 镀金3u"
07, 镀金15u" 08, 镀金30u"

端子材质: 1, 青铜 2, 磷铜

端子规格: D, 90度 Y, 180度 S, SMT贴板

塑胶形态: 1, 双层壳体 2, 双层半包

塑胶颜色: 01, 白色 02, 黑色 03, 本色

塑胶材质: 1, PBT 2, LCP 3, PA6T 4, PPA 5, PA6T



对接方向: A, 正向 B, 反向

外壳材质: 1, 铁壳 2, 铜壳




接口类型: 1, 有边平脚 2, 无边平脚


外壳脚型: 1, 弯脚 2, 直脚 3, 无脚

类别: 双层系列



RBCOMMENDBD P.C.B
PATTBRN LAY OUT



DRAWN	深圳市精拓金电子有限公司			
CHECKED	TITLE	PART NO.		
APPROVED	USB AF 10.5短体双层无脚 无边	SEE PART ON		
	UNIT	TOLERANCE	SCALE	SHEET
	mm	.XXX±.10, .XX±.25, X±.38, ANG±15°	1:1	1 OF 1
		SIZE	REV.	
		A4	X1	
		DRAWING NO. R907322A1021Y102		