







### Specifications :


- Voltage rating: 50V AC / DC
- Current rating: 1A AC / DC
- Withstanding voltage: 500V AC/minute
- Temperature range: -25°C~+85°C
- Insulation resistance:  $\geq 100M\Omega$
- Contact resistance:  $\leq 20m\Omega$
- After environmental testing:  $\leq 40m\Omega$



X1011 W R S-2\*XX X-9T V01 XX

(1) (2) (3) (4) (5) (6) (7) (8) (9)

- (1) Series No.  
(2) Category: W-wafer  
(3) Welding Board Angle: R-90°  
(4) Welding Way: S-SMT  
(5) Row No.-Pin No.: 2\*XX-Double Row  
(6) Plug the Pin & Special No.:  
(7) Material: 9T-PA9T 94V-0  
(8) Planting Category: V01-0All Gold Flash  
(9) Color: Blank-natural color ; GR-Green



| Poles | Dimenslons (mm) |       | Poles | Dimenslons (mm) |       |
|-------|-----------------|-------|-------|-----------------|-------|
|       | A               | B     |       | A               | B     |
| 20    | 9.00            | 13.00 | 40    | 19.00           | 23.00 |
| 30    | 14.00           | 18.00 | 50    | 24.00           | 28.00 |

|                     |               |               |             |        |
|---------------------|---------------|---------------|-------------|--------|
| X1011WRS-2*XX-9TV01 | PA9T UL 94V-0 | Brass         | Gold-Flash  | X1011H |
| PART N0             | Material      | Material(Pin) | Finish(Pin) |        |

For and on behalf of  
**XKB INDUSTRIAL PRECISION CO., LIMITED**  
**香港星坤工業精密有限公司**

| MARK | DESCRIPTION | DATE | REVISED | APPROVED | UNSPECIFIED TOLERANCES |
|------|-------------|------|---------|----------|------------------------|
| △ X  |             |      |         |          | ANGULAR ±5°            |
| △ X  |             |      |         |          | L ≤ 4 ±0.2             |
| △ X  |             |      |         |          | 4 < L ≤ 16 ±0.3        |
| △ X  |             |      |         |          | 16 < L ≤ 63 ±0.4       |
| △ X  |             |      |         |          | L > 63 ±0.5            |

|                                       |  |      |  |                |                                            |
|---------------------------------------|--|------|--|----------------|--------------------------------------------|
| DSND                                  |  | DATE |  | SCALE: N/A     | MODEL TYPE:<br>X1011WRS-2*XX-9TV01         |
| DWN                                   |  | DATE |  | VIEW:          | PART NO.:<br>1.00mm Crimp Style Connectors |
| CHKD                                  |  | DATE |  | UNIT: mm       | DWG NO.:                                   |
| APPD                                  |  | DATE |  | SIZE: A4       |                                            |
| XKB INDUSTRIAL PRECISION CO., LIMITED |  |      |  | WEIGHT<br>1.0g | SHEET<br>1/1                               |
|                                       |  |      |  | REVISION<br>A0 |                                            |