


Board Layout



- Specifications :**
- Voltage rating: 350V AC / DC
 - Current rating: 4 A AC / DC
 - Withstanding voltage: 1700V AC/minute
 - Temperature range: -25°C~+85°C
 - Insulation resistance: ≥1000MΩ
 - Contact resistance: ≤30mΩ
 - After environmental testing: ≤20mΩ

X1800 W R S-02 A -LP SN
 ① ② ③ ④ ⑤ ⑥ ⑦ ⑧

- ① Series No.
- ② Category: W-WAFER
- ③ Welding Board Angle: R-Right Angle 90°
- ④ Welding Way: S-SMT
- ⑤ Row No.-Pin No.: 02-02P
- ⑥ Plug the Pin & Special No.: A- NO Lock
- ⑦ Material: LP -LCP 94V-0
- ⑧ Planting Category: SN-Bright tin plating

X1800WRS-02A-LPSN	LCP UL 94V-0	Brass	Matte Tin	X1800H-A
PART NO	Material	Material (Pin&Solder tab)	Finish(Pin)	Suitable XKB Terminal

△ X	For and on behalf of XKB INDUSTRIAL PRECISION CO., LIMITED 香港星坤工業精密有限公司	ANGULAR	±5°			
△ X		L ≤ 4	±0.2			
△ X		4 < L ≤ 16	±0.3			
△ X		16 < L ≤ 63	±0.4			
MARK	DESCRIPTION	DATE	REVISED	APPROVED	L > 63	±0.5
REVISIONS				UNSPECIFIED TOLERANCES		

DSND	DATE	SCALE: N/A	MODEL TYPE: X1800WRS-02A-LPSN
DWN	DATE	VIEW:	PART NO.:
CHKD	DATE	UNIT: mm	1.80mm Crimp Style Connectors
APPD	DATE	SIZE: A4	DWG NO.:
XKB INDUSTRIAL PRECISION CO., LIMITED			WEIGHT 1.0g
			SHEET 1/1
			REVISION A0

Authorized Signature(s)