


Three Phase Bridge, 130 A to 160 A (Power Modules)



MTK

FEATURES

- Package fully compatible with the industry standard INT-A-PAK power modules series
- High thermal conductivity package, electrically insulated case
- Excellent power volume ratio
- 4000 V_{RMS} isolating voltage
- UL E78996 approved 
- Designed and qualified for industrial level
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912


RoHS
COMPLIANT

PRIMARY CHARACTERISTICS	
I _O	130 A to 160 A
V _{RRM}	800 V to 1600 V
Package	MTK
Circuit configuration	Three phase bridge

DESCRIPTION

A range of extremely compact, encapsulated three phase bridge rectifiers offering efficient and reliable operation. They are intended for use in general purpose and heavy duty applications.

MAJOR RATINGS AND CHARACTERISTICS				
SYMBOL	CHARACTERISTICS	VALUES 130MT.K	VALUES 160MT.K	UNITS
I _O		130 (160)	160 (200)	A
	T _C	85 (62)	85 (60)	°C
I _{FSM}	50 Hz	1130	1430	A
	60 Hz	1180	1500	
I ² t	50 Hz	6400	10 200	A ² s
	60 Hz	5800	9300	
I ² √t		64 000	102 000	A ² √s
V _{RRM}	Range	800 to 1600		V
T _{Stg}	Range	-40 to 150		°C
T _J		-40 to 150		

ELECTRICAL SPECIFICATIONS

VOLTAGE RATINGS				
TYPE NUMBER	VOLTAGE CODE	V _{RRM} , MAXIMUM REPETITIVE PEAK REVERSE VOLTAGE V	V _{RSM} , MAXIMUM NON-REPETITIVE PEAK REVERSE VOLTAGE V	I _{RRM} MAXIMUM AT T _J = MAXIMUM mA
VS-130MT.K VS-160MT.K	80	800	900	10
	100	1000	1100	
	120	1200	1300	
	140	1400	1500	
	160	1600	1700	

**FORWARD CONDUCTION**

PARAMETER	SYMBOL	TEST CONDITIONS			VALUES 130MT.K	VALUES 160MT.K	UNITS
Maximum DC output current at case temperature	I _O	120° rect. conduction angle			130 (160)	160 (200)	A
					85 (62)	85 (60)	°C
Maximum peak, one-cycle forward, non-repetitive surge current	I _{FSM}	t = 10 ms	No voltage reapplid	Initial T _J = T _J maximum	1130	1430	A
		t = 8.3 ms			1180	1500	
		t = 10 ms	100 % V _{RRM} reapplid		950	1200	
		t = 8.3 ms			1000	1260	
Maximum I ² t for fusing	I ² t	t = 10 ms	No voltage reapplid		6400	10 200	A ² s
		t = 8.3 ms			5800	9300	
		t = 10 ms	100 % V _{RRM} reapplid		4500	7200	
		t = 8.3 ms			4100	6600	
Maximum I ² √t for fusing	I ² √t	t = 0.1 ms to 10 ms, no voltage reapplid			64 000	102 000	A ² √s
Low level value of threshold voltage	V _{T(TO)1}	(16.7 % x π x I _{T(AV)}) < I < π x I _{T(AV)}), T _J maximum			0.78	0.81	V
High level value of threshold voltage	V _{T(TO)2}	(I > π x I _{T(AV)}), T _J maximum			0.99	1.04	
Low level value of forward slope resistance	r _{f1}	16.7 % x π x I _{T(AV)}) < I < π x I _{T(AV)}), T _J maximum			4.59	3.52	mΩ
High level of forward slope resistance	r _{f2}	(I > π x I _{T(AV)}), T _J maximum			4.17	3.13	
Maximum forward voltage drop	V _{FM}	I _{pk} = 200 A, T _J = 25 °C, t _p = 400 μs single junction			1.63	1.49	V
RMS isolation voltage	V _{ISOL}	T _J = 25 °C, all terminal shorted f = 50 Hz, t = 1 s			4000		

THERMAL AND MECHANICAL SPECIFICATIONS

PARAMETER	SYMBOL	TEST CONDITIONS	VALUES 130MT.K	VALUES 160MT.K	UNITS
Maximum junction operating and storage temperature range	T _J , T _{Stg}		-40 to 150		°C
Maximum thermal resistance, junction to case	R _{thJC}	DC operation per module	0.16	0.12	K/W
		DC operation per junction	0.93	0.73	
		120° rect. conduction angle per module	0.18	0.15	
		120° rect. conduction angle per junction	1.08	0.88	
Maximum thermal resistance, case to heatsink	R _{thCS}	Per module Mounting surface smooth, flat and greased	0.03		
Mounting torque ± 10 %	to heatsink to terminal	A mounting compound is recommended and the torque should be rechecked after a period of 3 hours to allow for the spread of the compound. Lubricated threads.	4 to 6		Nm
			3 to 4		
Approximate weight			176		g




Fig. 1 - Current Rating Characteristics




Fig. 2 - Forward Voltage Drop Characteristics





Fig. 3 - Total Power Loss Characteristics




Fig. 4 - Maximum Non-Repetitive Surge Current




Fig. 5 - Maximum Non-Repetitive Surge Current




Fig. 6 - Current Ratings Characteristic




Fig. 7 - Forward Voltage Drop Characteristics





Fig. 8 - Total Power Loss Characteristics




Fig. 9 - Maximum Non-Repetitive Surge Current





Fig. 10 - Maximum Non-Repetitive Surge Current


Fig. 11 - Thermal Impedance Z_{thJC} Characteristics


ORDERING INFORMATION TABLE

Device code	VS-	16	0	MT	160	K	PbF
	1	2	3	4	5		6
1	-	Vishay Semiconductors product					
2	-	Current rating code: 13 = 130 A (average) 16 = 160 A (average)					
3	-	Three phase diodes bridge					
4	-	Essential part number					
5	-	Voltage code x 10 = V_{RRM} (see Voltage Ratings table)					
6	-	PbF = Lead (Pb)-free					

Note

- To order the optional hardware go to: www.vishay.com/doc?95172

CIRCUIT CONFIGURATION




LINKS TO RELATED DOCUMENTS

Dimensions

www.vishay.com/doc?95004

MTK (with and without optional barrier)

DIMENSIONS WITH OPTIONAL BARRIERS in millimeters (inches)




Technical drawing of the 1000mAh Li-ion battery, showing front and side views with dimensions in millimeters (mm) and inches (in).

Front View Dimensions:

- Overall Height: 28 ± 1 mm (1.11 ± 0.04 in)
- Top Section Height: 25.5 ± 0.5 mm (1.004 ± 0.02 in)
- Fast-on tab: 2.8×0.8 (type 110)
- Screws: M5 x 0.8 length 10

Side View Dimensions:

- Overall Width: 35 ± 0.3 mm (1.38 ± 0.01 in)
- Top Section Width: 24 ± 0.5 mm (0.94 ± 0.02 in)
- Bottom Section Height: 8.5 ± 0.5 mm (0.34 ± 0.02 in)
- Overall Side Height: 30 ± 0.5 mm (1.17 ± 0.02 in)





Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.