


HSF

Current Rating: 5.0AMP
Contact Resistance: 20mΩ Max
Withstand Voltage: 1500V AC/DC
Insulation Resistance: 1000MΩ Min
Operation Temperature: -25℃ to +85℃




Current Rating: 5.0AMP
Contact Resistance: 20mΩ Max
Withstand Voltage: 1500V AC/DC
Insulation Resistance: 1000MΩ Min
Operation Temperature: -25℃ to +85℃



Ordering Information

WF 3001 - T X SN 0 1

Material	Contact Plating
P=Phosphor bronze	SN=Tin
B=Brass	



Specification & Ordering Information:

Part No.	Thickness	Material	Finish	Wire Range	Insulation O.D	Q'ty/Reel
WF3001-TPSN01	0.20	Phosphor bronze	Tin-Plated	AWG#20~#24	1.85mm Max.	10,000PCS
WF3001-TBSN01	0.20	Brass	Tin-Plated	AWG#20~#24	1.85mm Max.	10,000PCS

				OPERATION		DRAW JYHuang	DATE 2012/09/28	SCALE	FIT	PART NO. SEE TABLE	WCON Http: www.wcon.com WCON-Dongguan Tel: +86 769 85358920 Fax: +86 769 85358915 E-mail: sales@wcon.com WCON-Kunshan Tel: +86 512 57468408 Fax: +86 512 57468468 E-mail: salesks@wcon.com
				X.X	±0.40		CHECK	DATE	UNIT		
				X.XX	±0.25	APPROVE	DATE	SIZE	A4		
A0	2012/09/28	NEW	-----	X.XXX	±0.15			SHEET	1/1		
REV	DATE	MODIFICATION DESCRIPTION	CHANGE	Angle	± 3°	DIM	TOL	PROJ.		Customer NO.	