



P-Channel Enhancement MOSFET

SI2303 (KI2303)

■ Features

- $V_{DS} (V) = -30V$
- $R_{DS(ON)} < 200m\Omega$ ($V_{GS} = -10V$)
- $R_{DS(ON)} < 380m\Omega$ ($V_{GS} = -4.5V$)



■ Absolute Maximum Ratings $T_a = 25^\circ C$

Parameter	Symbol	Rating	Unit
Drain-Source Voltage	V_{DS}	-30	V
Gate-Source Voltage	V_{GS}	± 20	
Continuous Drain Current $(T_j = 150^\circ C)$ *1	I_D	-1.7	A
$T_a = 70^\circ C$		-1.4	
Pulsed Drain Current	I_{DM}	-10	
Power Dissipation $T_a = 25^\circ C$	P_D	1.25	W
$T_a = 70^\circ C$		0.8	
Thermal Resistance.Junction- to-Ambient (surface mounted on FR4 board)	R_{thJA}	100	$^\circ C/W$
		166	
Junction Temperature	T_J	150	$^\circ C$
Storage Temperature Range	T_{stg}	-55 to 150	

*1 Surface Mounted on 1" x 1" FR4 Board.

P-Channel Enhancement MOSFET

SI2303 (KI2303)

■ Electrical Characteristics Ta = 25°C

Parameter	Symbol	Test Conditions	Min	Typ	Max	Unit	
Drain-Source Breakdown Voltage	V _{DSS}	I _D =-250 μ A, V _{GS} =0V	-30			V	
Zero Gate Voltage Drain Current	I _{DSS}	V _{Ds} =-30V, V _{GS} =0V			-1	μ A	
		V _{Ds} =-30V, V _{GS} =0V, T _J =55°C			-10		
Gate-Body leakage current	I _{GSS}	V _{Ds} =0V, V _{GS} =±20V			±100	nA	
Gate Threshold Voltage	V _{GS(th)}	V _{Ds} =V _{GS} I _D =-250 μ A	-1.0		-3.0	V	
Static Drain-Source On-Resistance *1	R _{D(on)}	V _{GS} =-10V, I _D =-1.7A			200	mΩ	
		V _{GS} =-4.5V, I _D =-1.3A			380		
On state drain current *1	I _{D(on)}	V _{GS} =-10V, V _{Ds} ≥-5V	-6			A	
Forward Transconductance *1	g _{FS}	V _{Ds} =-10V, I _D =-1.7A		2.4		S	
Input Capacitance *2	C _{iss}	V _{GS} =0V, V _{Ds} =-15V, f=1MHz		226		pF	
Output Capacitance *2	C _{oss}			87			
Reverse Transfer Capacitance *2	C _{rss}			19			
Total Gate Charge *2	Q _g	V _{GS} =-10V, V _{Ds} =-4.5V, I _D =-1.7A		5.8	10	nC	
Gate Source Charge *2	Q _{gs}			0.8			
Gate Drain Charge *2	Q _{gd}			1.5			
Turn-On DelayTime *3	t _{d(on)}	V _{GS} =-10V, V _{Ds} =-15V, R _L =15 Ω ,R _{GEN} =6 Ω I _D =-1.0A		9.0	20	ns	
Turn-On Rise Time *3	t _r			9.0	20		
Turn-Off DelayTime *3	t _{d(off)}			18	35		
Turn-Off Fall Time *3	t _f			6.0	20		
Maximum Body-Diode Continuous Current	I _S				-1.25	A	
Diode Forward Voltage	V _{SD}	I _S =-1.25A, V _{GS} =0V			-0.8	-1.2	V

*1 Pulse test: PW ≤ 300us duty cycle≤ 2%.

*2 For DESIGN AID ONLY, not subject to production testing.

*3 Switching time is essentially independent of operating temperature.

■ Marking


Marking	A3*
---------	-----

P-Channel Enhancement MOSFET


SI2303 (KI2303)

■ Typical Characteristics


Output Characteristics




Transfer Characteristics




On-Resistance vs. Drain Current




Capacitance



Gate Charge



On-Resistance vs. Junction Temperature



P-Channel Enhancement MOSFET

SI2303 (K12303)

■ Typical Characteristics

