


## SOT-23 Plastic-Encapsulated MOSFETs

P-Channel Enhancement Mode Field Effect Transistor


### General Description

The AO3407 uses advanced trench technology to provide excellent  $R_{DS(on)}$  with low gate charge. This device is suitable for use as a load switch or in PWM applications.


### MARKING



### Equivalent Circuit



### SOT-23



### Maximum ratings ( $T_a=25^\circ\text{C}$ unless otherwise noted)

Parameter	Symbol	Value	Unit
Drain-Source Voltage	$V_{DS}$	-30	V
Gate-Source Voltage	$V_{GS}$	$\pm 20$	V
Continuous Drain Current	$I_D$	-4.1	A
Power Dissipation	$P_D$	350	mW
Thermal Resistance from Junction to Ambient	$R_{\theta JA}$	357	$^\circ\text{C}/\text{W}$
Junction Temperature	$T_J$	150	$^\circ\text{C}$
Storage Temperature	$T_{stg}$	-55~+150	$^\circ\text{C}$

**Electrical characteristics ( $T_a=25^\circ\text{C}$  unless otherwise noted)**


Parameter	Symbol	Test Condition	Min	Typ	Max	Units
<b>Static characteristics</b>						
Drain-source breakdown voltage	$\text{BV}_{\text{DSS}}$	$\text{V}_{\text{GS}} = 0\text{V}, \text{I}_D = -250\mu\text{A}$	-30			V
Zero gate voltage drain current	$\text{I}_{\text{DSS}}$	$\text{V}_{\text{DS}} = -24\text{V}, \text{V}_{\text{GS}} = 0\text{V}$			-1	$\mu\text{A}$
Gate-source leakage current	$\text{I}_{\text{GSS}}$	$\text{V}_{\text{GS}} = \pm 20\text{V}, \text{V}_{\text{DS}} = 0\text{V}$			$\pm 100$	nA
Drain-source on-resistance (note 1)	$\text{R}_{\text{DS}(\text{on})}$	$\text{V}_{\text{GS}} = -10\text{V}, \text{I}_D = -4.1\text{A}$			60	$\text{m}\Omega$
		$\text{V}_{\text{GS}} = -4.5\text{V}, \text{I}_D = -3\text{A}$			87	$\text{m}\Omega$
Forward transconductance (note 1)	$\text{g}_{\text{FS}}$	$\text{V}_{\text{DS}} = -5\text{V}, \text{I}_D = -4\text{A}$	5.5			S
Gate threshold voltage	$\text{V}_{\text{GS}(\text{th})}$	$\text{V}_{\text{DS}} = \text{V}_{\text{GS}}, \text{I}_D = -250\mu\text{A}$	-1		-3	V
Diode forward voltage (note 1)	$\text{V}_{\text{SD}}$	$\text{I}_S = -1\text{A}, \text{V}_{\text{GS}} = 0\text{V}$			-1	V
<b>Dynamic characteristics (note 2)</b>						
Input capacitance	$\text{C}_{\text{iss}}$	$\text{V}_{\text{DS}} = -15\text{V}, \text{V}_{\text{GS}} = 0\text{V}, f = 1\text{MHz}$		700		pF
Output capacitance	$\text{C}_{\text{oss}}$			120		pF
Reverse transfer capacitance	$\text{C}_{\text{rss}}$			75		pF
<b>Switching Characteristics (note 2)</b>						
Turn-on delay time	$t_{\text{d}(\text{on})}$	$\text{V}_{\text{GS}} = -10\text{V}, \text{V}_{\text{DS}} = -15\text{V}, \text{R}_L = 3.6\Omega, \text{R}_{\text{GEN}} = 3\Omega$		8.6		ns
Turn-on rise time	$t_r$			5.0		ns
Turn-off delay time	$t_{\text{d}(\text{off})}$			28.2		ns
Turn-off fall time	$t_f$			13.5		ns

**Notes:**





1. Pulse test: Pulse width  $\leq 300\mu\text{s}$ , duty cycle  $\leq 2\%$ .
2. These parameters have no way to verify.

## Typical Characteristics

**Output Characteristics**



**Transfer Characteristics**



## PACKAGE OUTLINE

Plastic surface mounted package; 3 leads

SOT-23

