nexperia



### **1** General description

The 74LV17A is a hex buffer with Schmitt-trigger inputs, capable of transforming slowly changing input signals into sharply defined, jitter-free output signals.

Inputs are overvoltage tolerant. This feature allows the use of these devices as translators in mixed voltage environments.

This device is fully specified for partial power down applications using  $I_{OFF}$ . The  $I_{OFF}$  circuitry disables the output, preventing the potentially damaging backflow current through the device when it is powered down.

### 2 Features and benefits


- Wide supply voltage range from 2.0 V to 5.5 V
- Maximum t<sub>pd</sub> of 10 ns at 5 V
- Typical V<sub>OL(p)</sub> < 0.8 V at V<sub>CC</sub> = 3.3 V, T<sub>amb</sub> = 25  $^{\circ}$ C
- Typical  $V_{OH(v)}$  > 2.3 V at  $V_{CC}$  = 3.3 V,  $T_{amb}$  = 25 °C
- · Supports mixed-mode voltage operation on all ports
- I<sub>OFF</sub> circuitry provides partial Power-down mode operation
- Latch-up performance exceeds 250 mA per JESD 78 Class II
- · ESD protection:
  - HBM ANSI/ESDA/JEDEC JS-001 Class 2 exceeds 3 kV
  - MM JESD22-A115-A exceeds 150 V
  - CDM JESD22-C101E exceeds 2 kV
- Specified from -40 °C to +85 °C and from -40 °C to +125 °C

### **3** Ordering information

Table	1.	Orderi	ng int	formation
-------	----	--------	--------	-----------


Туре	Package			
number	Temperature range	Name	Description	Version
74LV17APW	-40 °C to +125 °C	TSSOP14	plastic thin shrink small outline package; 14 leads; body width 4.4 mm	SOT402-1

# 4 Functional diagram



# **5 Pinning information**

### 5.1 Pinning



### 5.2 Pin description

Symbol	Pin	Description
1A, 2A, 3A, 4A, 5A, 6A	1, 3, 5, 9, 11, 13	data input
1Y, 2Y, 3Y, 4Y, 5Y, 6Y	2, 4, 6, 8, 10, 12	data output
GND	7	ground (0 V)
V <sub>CC</sub>	14	supply voltage

74LV17A Product data sheet

#### **Functional description** 6

#### Table 3. Function table <sup>[1]</sup>

Input	Output
nA	nY
L	L
Н	Н

[1] H = HIGH voltage level; L = LOW voltage level.

#### **Limiting values** 7

#### Table 4. Limiting values

In accordance with the Absolute Maximum Rating System (IEC 60134). Voltages are referenced to GND (ground = 0 V).

Symbol	Parameter	Conditions	Min	Мах	Unit
V <sub>CC</sub>	supply voltage		-0.5	+7.0	V
VI	input voltage	[1]	-0.5	+7.0	V
Vo	output voltage	output HIGH or LOW state [2] [3]	-0.5	V <sub>CC</sub> + 0.5	V
		output power-down [2]	-0.5	+7.0	V
I <sub>IK</sub>	input clamping current	V <sub>1</sub> < 0 V	-20	-	mA
Ι <sub>ΟΚ</sub>	output clamping current	V <sub>O</sub> < 0 V	-50	-	mA
I <sub>O</sub>	output current	$V_{O}$ = 0 V to $V_{CC}$	-	±35	mA
I <sub>CC</sub>	supply current		-	70	mA
I <sub>GND</sub>	ground current		-70	-	mA
T <sub>stg</sub>	storage temperature		-65	+150	°C
P <sub>tot</sub>	total power dissipation	T <sub>amb</sub> = -40 °C to +125 °C <sup>[4]</sup>	-	500	mW

If the input current ratings are observed, the minimum input voltage ratings may be exceeded.

[1] [2] [3] [4]

If the output current ratings are observed, the minimum input voltage ratings may be exceeded. If the output current ratings are observed, the output voltage ratings may be exceeded. This value is limited to 7 V maximum. For TSSOP14 packages: above 75 °C, the value of P<sub>tot</sub> derates linearly at 7 mW/K.

# 8 Recommended operating conditions

#### Table 5. Recommended operating conditions

Voltages are referenced to GND (ground = 0 V).

Symbol	Parameter	Conditions	Min	Тур	Max	Unit
V <sub>CC</sub>	supply voltage		2.0	5.0	5.5	V
VI	input voltage		0	-	5.5	V
Vo	output voltage	output HIGH or LOW state	0	-	V <sub>CC</sub>	V
		output power-down	0	-	5.5	V
T <sub>amb</sub>	ambient temperature		-40	+25	+125	°C
Δt/ΔV	input transition rise and fall rate	$V_{CC}$ = 2.3 V to 2.7 V	-	-	50	ms/V
		V <sub>CC</sub> = 3.0 V to 3.6 V	-	-	20	ms/V
		V <sub>CC</sub> = 4.5 V to 5.5 V	-	-	1	ms/V

# 9 Static characteristics

#### **Table 6. Static characteristics**

Voltages are referenced to GND (ground = 0 V).

Symbol	Parameter	Parameter Conditions		25 °C		-40 ° +85		-40 ° +12		Unit
			Min	Тур	Max	Min	Мах	Min	Max	
V <sub>T+</sub>	positive-going	V <sub>CC</sub> = 2.5 V	-	-	1.75	-	1.75	-	1.75	V
	threshold	V <sub>CC</sub> = 3.3 V	-	-	2.31	-	2.31	-	2.31	V
	voltage	V <sub>CC</sub> = 5.0 V	-	-	3.5	-	3.5	-	3.5	V
V <sub>T-</sub>	negative-going	V <sub>CC</sub> = 2.5 V	0.75	-	-	0.75	-	0.75	-	V
	threshold	V <sub>CC</sub> = 3.3 V	0.99	-	-	0.99	-	0.99	-	V
	voltage	V <sub>CC</sub> = 5.0 V	1.5	-	-	1.5	-	1.5	-	V
V <sub>H</sub>	hysteresis	V <sub>CC</sub> = 2.5 V	0.25	-	-	0.25	-	0.25	-	V
	voltage	V <sub>CC</sub> = 3.3 V	0.33	-	-	0.33	-	0.33	-	V
		V <sub>CC</sub> = 5.0 V	0.5	-	-	0.5	-	0.5	-	V
V <sub>OH</sub>	HIGH-level	V <sub>I</sub> = V <sub>IH</sub> or V <sub>IL</sub>								
	output voltage	$V_{CC}$ = 2.0 V to 5.5 V; $I_{O}$ = -50 µA	V <sub>CC</sub> -0.1	-	-	V <sub>CC</sub> -0.1	-	V <sub>CC</sub> -0.1	-	V
		V <sub>CC</sub> = 2.3 V; I <sub>O</sub> = -2 mA	2	-	-	2	-	2	-	V
		V <sub>CC</sub> = 3.0 V; I <sub>O</sub> = -6 mA	2.48	-	-	2.48	-	2.48	-	V
		V <sub>CC</sub> = 4.5 V; I <sub>O</sub> = -12 mA	3.8	-	-	3.8	-	3.8	-	V
V <sub>OL</sub>	LOW-level	V <sub>I</sub> = V <sub>IH</sub> or V <sub>IL</sub>				,				
	output voltage	$V_{CC}$ = 2.0 V to 5.5 V; I <sub>O</sub> = 50 µA	-	-	0.1	-	0.1	-	0.1	V


### Nexperia

# 74LV17A

### Hex buffer Schmitt trigger


Symbol	Parameter	Conditions		25 °C			°C to 5 °C	-40 ° +12	°C to 5 °C	Unit
			Min	Тур	Max	Min	Мах	Min	Max	
		V <sub>CC</sub> = 2.3 V; I <sub>O</sub> = 2 mA	-	-	0.4	-	0.4	-	0.4	V
		V <sub>CC</sub> = 3.0 V; I <sub>O</sub> = 6 mA	-	-	0.44	-	0.44	-	0.44	V
		V <sub>CC</sub> = 4.5 V; I <sub>O</sub> = 12 mA	-	-	0.55	-	0.55	-	0.55	V
I <sub>OFF</sub>	power-off leakage current	$V_1 \text{ or } V_0 = \text{GND to } 5.5 \text{ V};$ $V_{CC} = 0 \text{ V}$	-	-	0.5	-	5	-	5	μA
I	input leakage current	$V_I = V_{CC}$ or GND; $V_{CC} = 0 V$ to 5.5 V	-	-	±0.1	-	±1	-	±1	μA
I <sub>CC</sub>	supply current	$V_{I} = V_{CC} \text{ or GND}; I_{O} = 0 \text{ A};$ $V_{CC} = 5.5 \text{ V}$	-	-	2	-	20	-	20	μA

# 9.1 Transfer characteristics waveforms



### Nexperia

74LV17A Hex buffer Schmitt trigger



© Nexperia B.V. 2017. All rights reserved.

# **10** Dynamic characteristics

#### Table 7. Dynamic characteristics

GND = 0 V	For test	circuit,	see	Figure 9.
-----------	----------	----------	-----	-----------

Symbol	Parameter	Conditions		25 °C		-40 °C to	o +85 °C	-40 °C to	+125 °C	Unit
			Min	Typ <sup>[1]</sup>	Max	Min	Max	Min	Мах	
t <sub>pd</sub>	propagation	nA to nY; see Figure 8 <sup>[2]</sup>		J		I	I			
	delay	V <sub>CC</sub> = 2.3 V to 2.7 V								
		C <sub>L</sub> = 15 pF	-	5.5	19	1	22	1	23	ns
		C <sub>L</sub> = 50 pF	-	8.6	24	1	27	1	28	ns
		V <sub>CC</sub> = 3.0 V to 3.6 V								
		C <sub>L</sub> = 15 pF	-	4.3	12	1	14	1	16	ns
		C <sub>L</sub> = 50 pF	-	6.7	16	1	18	1	19	ns
		$V_{CC}$ = 4.5 V to 5.5 V								
		C <sub>L</sub> = 15 pF	-	3.4	8	1	10	1	11	ns
		C <sub>L</sub> = 50 pF	-	5.1	10	1	12	1	13	ns
Cı	input capacitance	V <sub>I</sub> = V <sub>CC</sub> or GND; V <sub>CC</sub> = 3.3 V	-	2	6	-	6	-	6	pF
C <sub>O</sub>	output capacitance	$V_{O} = V_{CC} \text{ or GND};$ $V_{CC} = 3.3 \text{ V}$	-	5	-	-	-	-	-	pF
C <sub>PD</sub>	power dissipation capacitance	per buffer; f = 10 MHz; <sup>[3]</sup> C <sub>L</sub> = 50 pF; V <sub>I</sub> = GND to V <sub>CC</sub>		1		-	1	I	1	
		V <sub>CC</sub> = 3.3 V	-	8.7	-	-	-	-	-	pF
		V <sub>CC</sub> = 5.0 V	-	9.8	-	-	-	-	-	pF

[1] Typical values are measured at T<sub>amb</sub> = 25 °C and V<sub>CC</sub> = 2.5 V, 3.3 V, and 5 V respectively, unless otherwise specified.

[2] [3]

 $t_{pa}$  is the same as  $t_{PLH}$  and  $t_{PHL}$ . C<sub>PD</sub> is used to determine the dynamic power dissipation (P<sub>D</sub> in µW).

 $P_D = C_{PD} \times V_{CC}^2 \times f_i \times N + \sum (C_L \times V_{CC}^2 \times f_o)$  where:

- f<sub>i</sub> = input frequency in MHz;
- f<sub>o</sub> = output frequency in MHz;

 $C_{L}$  = output load capacitance in pF;

 $V_{CC}$  = supply voltage in V;

N = number of inputs switching;

 $\Sigma(C_L \times V_{CC}^2 \times f_0)$  = sum of the outputs.

# 74LV17A


Hex buffer Schmitt trigger

#### Table 8. Noise characteristics

GND = 0 V. For test circuit, see Figure 9.

Symbol	Parameter	Conditions	Ta	Unit		
			Min	Тур	Мах	
$V_{\rm CC} = 3.3$	3 V; C <sub>L</sub> = 50 pF					
V <sub>OL(p)</sub>	LOW-level output voltage (peak)		-	0.2	0.8	V
V <sub>OL(v)</sub>	LOW-level output voltage (valley)		-0.8	-0.1	-	V
V <sub>OH(v)</sub>	HIGH-level output voltage (valley)		-	3.1	-	V
V <sub>IH(AC)</sub>	AC HIGH-level input voltage		2.31	-	-	V
V <sub>IL(AC)</sub>	AC LOW-level input voltage		-	-	0.99	V

### 10.1 Waveforms and test circuit



Measurement points are given in Table 9.

 $V_{\text{OL}}$  and  $V_{\text{OH}}$  are typical voltage output levels that occur with the output load.


Figure 8. Propagation delay input (nA) to output (nY)

#### Table 9. Measurement points

Input	Output
V <sub>M</sub>	V <sub>M</sub>
0.5V <sub>CC</sub>	0.5V <sub>CC</sub>

### Nexperia

### Hex buffer Schmitt trigger



Input		Load	Test	
VI	t <sub>r</sub> , t <sub>f</sub>	CL		
GND to V <sub>CC</sub>	3.0 ns	15 pF, 50 pF	t <sub>PLH</sub> , t <sub>PHL</sub>	

# 11 Package outline

						Juum		haye,	14 168	ads; b	oay v	vidth 4	4.4 M	m			50	OT40
		Ţ			- D				c			E · 				X	A	
							8				×1 ( ↓ (			Q I Lp	(A <sub>3</sub> ) ↓ ↓	Α 		
				∎ ∎ e	ΨU -	b						C	detail X	]				
	IONS (n		the orig	jinal din		s)	0		2.5 scale		5 mm			_			7(1)	-
UNIT	A max.	A <sub>1</sub>	the orig	jinal din	bp	s)	0 	E <sup>(2)</sup>	scale e	Н <sub>Е</sub> 6.6		Lp	Q	v	w	у	<b>Z</b> <sup>(1)</sup> 0.72	θ 8°
UNIT mm	A		the orig	jinal din		s)	0		scale	<b>H</b> <sub>E</sub> 6.6 6.2				_	<b>w</b> 0.13	<b>y</b> 0.1	<b>Z</b> (1) 0.72 0.38	θ 8° 0°
UNIT mm lotes . Plastic	A max. 1.1	<b>A</b> <sub>1</sub> 0.15 0.05	the orig A <sub>2</sub> 0.95 0.80	<b>inal din</b> <b>A</b> <sub>3</sub> 0.25	<b>b</b> p 0.30 0.19 m maxin	s) c 0.2 0.1	0 <b>D</b> (1) 5.1 4.9 side ard	<b>E</b> <sup>(2)</sup> 4.5 4.3 e not inc	e 0.65	6.6		<b>L</b> р 0.75	<b>Q</b> 0.4	v			0.72	8°
UNIT mm Iotes . Plastic . Plastic	A max. 1.1 c or meta c interlea	<b>A</b> <sub>1</sub> 0.15 0.05	the orig A <sub>2</sub> 0.95 0.80	<b>inal din</b> <b>A</b> <sub>3</sub> 0.25	<b>b</b> p 0.30 0.19 m maxin	s) c 0.2 0.1	0 <b>D</b> (1) 5.1 4.9 side are	<b>E</b> <sup>(2)</sup> 4.5 4.3 e not inc	e 0.65 cluded.	6.6		<b>L</b> р 0.75	<b>Q</b> 0.4	v 0.2 EURO	0.13	0.1	0.72 0.38	8° 0°
UNIT mm lotes . Plastic . Plastic Ol VE	A max. 1.1	A1 0.15 0.05	the orig A <sub>2</sub> 0.95 0.80 sions of	<b>inal din</b> <b>A</b> <sub>3</sub> 0.25	<b>b</b> p 0.30 0.19 m maxin	s) c 0.2 0.1	0 D (1) 5.1 4.9 side are r side ar <b>REFEI</b>	E (2) 4.5 4.3 e not inc re not inc	e 0.65 cluded.	6.6		<b>L</b> р 0.75	<b>Q</b> 0.4	<b>v</b> 0.2	0.13	0.1	0.72	8° 0°

### Hex buffer Schmitt trigger

# **12** Abbreviations

Table 11. Abbreviations					
Acronym	Description				
CDM	Charge Device Model				
DUT	Device Under Test				
ESD	ElectroStatic Discharge				
НВМ	Human Body Model				
MM	Machine Model				

# 13 Revision history

Table 12. Revision history							
Document ID	Release date	Data sheet status	Change notice	Supersedes			
74LV17A v.1	20170518	Product data sheet	-	-			

# 14 Legal information

### 14.1 Data sheet status

Document status <sup>[1][2]</sup>	Product status <sup>[3]</sup>	Definition
Objective [short] data sheet	Development	This document contains data from the objective specification for product development.
Preliminary [short] data sheet	Qualification	This document contains data from the preliminary specification.
Product [short] data sheet	Production	This document contains the product specification.

Please consult the most recently issued document before initiating or completing a design. [1]

The term 'short data sheet' is explained in section "Definitions".

[2] [3] The product status of device(s) described in this document may have changed since this document was published and may differ in case of multiple devices. The latest product status information is available on the Internet at URL http://www.nexperia.com.

### 14.2 Definitions

Draft — The document is a draft version only. The content is still under internal review and subject to formal approval, which may result in modifications or additions. Nexperia does not give any representations or warranties as to the accuracy or completeness of information included herein and shall have no liability for the consequences of use of such information.

Short data sheet — A short data sheet is an extract from a full data sheet with the same product type number(s) and title. A short data sheet is intended for quick reference only and should not be relied upon to contain detailed and full information. For detailed and full information see the relevant full data sheet, which is available on request via the local Nexperia sales office. In case of any inconsistency or conflict with the short data sheet, the full data sheet shall prevail.

Product specification — The information and data provided in a Product data sheet shall define the specification of the product as agreed between Nexperia and its customer, unless Nexperia and customer have explicitly agreed otherwise in writing. In no event however, shall an agreement be valid in which the Nexperia product is deemed to offer functions and qualities beyond those described in the Product data sheet.

### 14.3 Disclaimers

Limited warranty and liability - Information in this document is believed to be accurate and reliable. However, Nexperia does not give any representations or warranties, expressed or implied, as to the accuracy or completeness of such information and shall have no liability for the consequences of use of such information. Nexperia takes no responsibility for the content in this document if provided by an information source outside of Nexperia. In no event shall Nexperia be liable for any indirect, incidental, punitive, special or consequential damages (including - without limitation lost profits, lost savings, business interruption, costs related to the removal or replacement of any products or rework charges) whether or not such damages are based on tort (including negligence), warranty, breach of contract or any other legal theory. Notwithstanding any damages that customer might incur for any reason whatsoever, Nexperia's aggregate and cumulative liability towards customer for the products described herein shall be limited in accordance with the Terms and conditions of commercial sale of Nexperia

Right to make changes - Nexperia reserves the right to make changes to information published in this document, including without limitation specifications and product descriptions, at any time and without notice. This document supersedes and replaces all information supplied prior to the publication hereof.

Suitability for use - Nexperia products are not designed, authorized or warranted to be suitable for use in life support, life-critical or safety-critical systems or equipment, nor in applications where failure or malfunction of an Nexperia product can reasonably be expected to result in personal injury, death or severe property or environmental damage. Nexperia and its suppliers accept no liability for inclusion and/or use of Nexperia products in such equipment or applications and therefore such inclusion and/or use is at the customer's own risk.

Applications — Applications that are described herein for any of these products are for illustrative purposes only. Nexperia makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification. Customers are responsible for the design and operation of their applications and products using Nexperia products, and Nexperia accepts no liability for any assistance with applications or customer product design. It is customer's sole responsibility to determine whether the Nexperia product is suitable and fit for the customer's applications and products planned, as well as for the planned application and use of customer's third party customer(s). Customers should provide appropriate design and operating safeguards to minimize the risks associated with their applications and products. Nexperia does not accept any liability related to any default, damage, costs or problem which is based on any weakness or default in the customer's applications or products, or the application or use by customer's third party customer(s). Customer is responsible for doing all necessary testing for the customer's applications and products using Nexperia products in order to avoid a default of the applications and the products or of the application or use by customer's third party customer(s). Nexperia does not accept any liability in this respect.

Limiting values — Stress above one or more limiting values (as defined in the Absolute Maximum Ratings System of IEC 60134) will cause permanent damage to the device. Limiting values are stress ratings only and (proper) operation of the device at these or any other conditions above those given in the Recommended operating conditions section (if present) or the Characteristics sections of this document is not warranted. Constant or repeated exposure to limiting values will permanently and irreversibly affect the quality and reliability of the device.

Terms and conditions of commercial sale - Nexperia products are sold subject to the general terms and conditions of commercial sale, as published at http://www.nexperia.com/profile/terms, unless otherwise agreed in a valid written individual agreement. In case an individual agreement is concluded only the terms and conditions of the respective agreement shall apply. Nexperia hereby expressly objects to applying the customer's general terms and conditions with regard to the purchase of Nexperia products by customer

No offer to sell or license - Nothing in this document may be interpreted or construed as an offer to sell products that is open for acceptance or the grant, conveyance or implication of any license under any copyrights, patents or other industrial or intellectual property rights.

Export control — This document as well as the item(s) described herein may be subject to export control regulations. Export might require a prior authorization from competent authorities.

# 74LV17A Hex buffer Schmitt trigger

Non-automotive qualified products — Unless this data sheet expressly states that this specific Nexperia product is automotive qualified, the product is not suitable for automotive use. It is neither qualified nor tested in accordance with automotive testing or application requirements. Nexperia accepts no liability for inclusion and/or use of non-automotive qualified products in automotive equipment or applications. In the event that customer uses the product for design-in and use in automotive applications to automotive specifications and standards, customer (a) shall use the product without Nexperia's warranty of the product for such automotive applications, use and specifications beyond Nexperia's specifications such use shall be solely at customer's own risk, and (c) customer fully indemnifies Nexperia for any liability, damages or failed product claims resulting from customer

design and use of the product for automotive applications beyond Nexperia's standard warranty and Nexperia's product specifications.

**Translations** — A non-English (translated) version of a document is for reference only. The English version shall prevail in case of any discrepancy between the translated and English versions.

### 14.4 Trademarks

Notice: All referenced brands, product names, service names and trademarks are the property of their respective owners.

# 74LV17A Hex buffer Schmitt trigger

### Contents

1	General description	1
2	Features and benefits	1
3	Ordering information	1
4	Functional diagram	2
5	Pinning information	2
5.1	Pinning	2
5.2	Pin description	2
6	Functional description	3
7	Limiting values	3
8	Recommended operating conditions	4
9	Static characteristics	4
9.1	Transfer characteristics waveforms	5
10	Dynamic characteristics	7
10.1	Waveforms and test circuit	8
11	Package outline	10
12	Abbreviations	11
13	Revision history	11
14	Legal information	12

Please be aware that important notices concerning this document and the product(s) described herein, have been included in section 'Legal information'.

© Nexperia B.V. 2017.

All rights reserved.

For more information, please visit: http://www.nexperia.com For sales office addresses, please send an email to: salesaddresses@nexperia.com

Date of release: 18 May 2017 Document identifier: 74LV17A