



BT15T120 CNR

General Description:

Using HUAJING's proprietary trench design, advanced FS(field stop) technology and integrated with Free Wheeling Diode, the 1200V Trench FS IGBT offers superior conduction and switching performances, high avalanche ruggedness.

Features:

- l Trench FS Technology, Positive temperature coefficient
- l Low saturation voltage: $V_{CE(sat)}$, typ =1.95V @ $I_C=15A$
- l Extremely enhanced avalanche capability

Applications:



Power switch circuit of induction cooker(IH).

Absolute Maximum Ratings

($T_J=25^\circ C$ unless otherwise specified):

| Symbol | Parameter | Rating | Units |
|----------------|--|------------------|------------|
| V_{CES} | Collector-Emitter Voltage | 1200 | V |
| V_{GES} | Gate- Emitter Voltage | ± 20 | V |
| I_C | Collector Current@ $T_C = 25^\circ C$ | 30 | A |
| | Collector Current @ $T_C = 100^\circ C$ | 15 | A |
| I_{CM}^{al} | Pulsed Collector Current@ $T_C = 25^\circ C$ | 45 | A |
| I_F | Diode Continuous Forward Current @ $T_C = 100^\circ C$ | 15 | A |
| I_{FM} | Diode Maximum Forward Current@ $T_C = 25^\circ C$ | 45 | A |
| P_D | Power Dissipation @ $T_C = 25^\circ C$ | 156 | W |
| | Power Dissipation @ $T_C = 100^\circ C$ | 62 | W |
| T_J, T_{stg} | Operating Junction and Storage Temperature Range | 150, -55 to +150 | $^\circ C$ |
| T_L | Maximum Temperature for Soldering | 270 | $^\circ C$ |

| | | |
|---------------------------|------|---|
| V_{CES} | 1200 | V |
| I_C | 15 | A |
| $P_{tot}(T_C=25^\circ C)$ | 156 | W |
| $V_{CE(SAT)}$ | 1.95 | V |



Thermal Characteristics

| Symbol | Parameter | Typ. | Max. | Units |
|-----------------|---|------|------|--------------|
| $R_{\theta JC}$ | Thermal Resistance, Junction to case for IGBT | 0.55 | 0.8 | $^\circ C/W$ |
| $R_{\theta JA}$ | Thermal Resistance, Junction to Ambient | 35 | 40 | $^\circ C/W$ |

Electrical Characteristics of the IGBT ($T_j = 25^\circ\text{C}$ unless otherwise specified):

| OFF Characteristics | | | | | | |
|----------------------------|-------------------------------------|-----------------------------|--------|------|------|-------|
| Symbol | Parameter | Test Conditions | Rating | | | Units |
| | | | Min. | Typ. | Max. | |
| V_{CES} | Collector-Emitter Breakdown Voltage | $V_{GE}=0V, I_{CE}=1mA$ | 1200 | -- | -- | V |
| I_{CES} | Collector-Emitter Leakage Current | $V_{GE}=0V, V_{CE}=V_{CES}$ | -- | -- | 1.0 | mA |
| $I_{GES(F)}$ | Gate to Emitter Forward Leakage | $V_{GE}=+20V$ | -- | -- | +250 | nA |
| $I_{GES(R)}$ | Gate to Source Reverse Leakage | $V_{GE}=-20V$ | -- | -- | -250 | nA |

| ON Characteristics | | | | | | |
|---|--------------------------------------|-------------------------------|--------|------|------|-------|
| Symbol | Parameter | Test Conditions | Rating | | | Units |
| | | | Min. | Typ. | Max. | |
| $V_{CE(sat)}$ | Collector-Emitter Saturation Voltage | $I_C=15A, V_{GE}=15V$ | -- | 1.95 | 2.5 | V |
| V_{FM} | Diode Forward Voltage | $I_F=15A$ | -- | 2.7 | 3.2 | V |
| $V_{GE(TH)}$ | Gate Threshold Voltage | $I_C=250\mu A, V_{CE}=V_{GE}$ | 4.5 | 5.8 | 7.5 | V |
| Pulse width $tp \leq 300\mu s, \delta \leq 2\%$ | | | | | | |

| Dynamic Characteristics | | | | | | |
|--------------------------------|------------------------------|-------------------------------------|--------|------|------|-------|
| Symbol | Parameter | Test Conditions | Rating | | | Units |
| | | | Min. | Typ. | Max. | |
| C_{ies} | Input Capacitance | $V_{CE}=25V, V_{GE}=0V$ $f=1MHz$ | -- | 1513 | -- | pF |
| C_{oes} | Output Capacitance | | -- | 35 | -- | |
| C_{res} | Reverse Transfer Capacitance | | -- | 25 | -- | |

| Resistive Switching Characteristics | | | | | | |
|--|--------------------------|---|--------|------|------|-------|
| Symbol | Parameter | Test Conditions | Rating | | | Units |
| | | | Min. | Typ. | Max. | |
| $t_{d(ON)}$ | Turn-on Delay Time | $T_j = 25^\circ\text{C}$ $V_{CE}=600V, I_C=15A$ $V_{GE}=0/15V,$ $R_g=10\Omega$ Inductive Load | -- | 14 | -- | ns |
| t_r | Rise Time | | -- | 32 | -- | |
| $t_{d(OFF)}$ | Turn-Off Delay Time | | -- | 107 | -- | |
| t_f | Fall Time | | -- | 131 | -- | mJ |
| E_{on} | Turn-On Switching Loss | | -- | 0.43 | -- | |
| E_{off} | Turn-Off Switching Loss | | -- | 0.7 | -- | |
| E_{ts} | Total Switching Loss | | -- | 1.13 | -- | |
| Q_g | Total Gate Charge | $V_{CE}=960V, I_C=15A$ $V_{GE}=15V$ | -- | 81.5 | -- | nC |
| Q_{ge} | Gate to Emitter Charge | | -- | 7.5 | -- | |
| Q_{gc} | Gate to Collector Charge | | -- | 51.5 | -- | |

Characteristics Cure




Figure 1. Typical Output Characteristics




Figure 2. Typical Output Characteristics




Figure 3. Typical Saturation Voltage vs. Junction Temperature




Figure 4. Typical Saturation Voltage vs. Gate-Emitter Voltage




Figure 5. Typical Saturation Voltage vs. Gate-Emitter Voltage




Figure 6. Typical Capacitance Characteristics




Figure 7. Typical Turn-On Characteristics vs. Gate Resistance




Figure 8. Typical Turn-Off Characteristics vs. Gate




Figure 9. Typical Switching Losses vs. Gate Resistance




Figure 10. Typical Turn-On Characteristics vs. Collector Current




Figure 11. Typical Turn-Off Characteristics vs. Collector Current




Figure 12. Typical Switching Losses vs. Collector Current




Figure 13. Typical Diode Forward Characteristics




Figure 14. Typical Gate Charge





Figure 15. Transient Thermal Impedance of IGBT

Package Information


| Items | Values(mm) | |
|-------|------------|-------|
| | MIN | MAX |
| A | 15.00 | 16.00 |
| B | 19.20 | 20.60 |
| C | 4.60 | 5.00 |
| D | 1.40 | 1.60 |
| E | 0.90 | 1.10 |
| F | 0.50 | 0.70 |
| G1 | 2.00 | 2.20 |
| G2 | 3.00 | 3.20 |
| H | 3.00 | 3.70 |
| I | 1.20 | 1.70 |
| | 2.70 | 2.90 |
| L* | 19.00 | 21.00 |
| N | 5.25 | 5.65 |
| Φ P | 3.10 | 3.30 |

*: adjustable

TO-3P(N) Package



The name and content of poisonous and harmful material in products

| Part's Name | Hazardous Substance | | | | | | | | | |
|--------------|--|-----------|------------|--------|-------|-------|-------|-------|-------|-------|
| | Pb | Hg | Cd | Cr(VI) | PBB | PBDE | DIBP | DEHP | DBP | BBP |
| Limit | ≤ 0.1% | ≤ 0.1% | ≤ 0.01% | ≤0.1% | ≤0.1% | ≤0.1% | ≤0.1% | ≤0.1% | ≤0.1% | ≤0.1% |
| Lead Frame | ○ | ○ | ○ | ○ | ○ | ○ | ○ | ○ | ○ | ○ |
| Molding | ○ | ○ | ○ | ○ | ○ | ○ | ○ | ○ | ○ | ○ |
| Chip | ○ | ○ | ○ | ○ | ○ | ○ | ○ | ○ | ○ | ○ |
| Wire Bonding | ○ | ○ | ○ | ○ | ○ | ○ | ○ | ○ | ○ | ○ |
| Solder | × | ○ | ○ | ○ | ○ | ○ | ○ | ○ | ○ | ○ |
| Note | <p>○: Means the hazardous material is under the criterion of 2011/65/EU. ×: Means the hazardous material exceeds the criterion of 2011/65/EU. The plumbum element of solder exist in products presently, but within the allowed range of Eurogroup's RoHS.</p> | | | | | | | | | |

Warnings

1. Exceeding the maximum ratings of the device in performance may cause damage to the device, even the permanent failure, which may affect the dependability of the machine. It is suggested to be used under 80 percent of the maximum ratings of the device.
2. When installing the heat sink, please pay attention to the torsional moment and the smoothness of the heat sink.
3. IGBTs is the device which is sensitive to the static electricity, it is necessary to protect the device from being damaged by the static electricity when using it.
4. This publication is made by Huajing Microelectronics and subject to regular change without notice.

WUXI CHINA RESOURCES HUAJING MICROELECTRONICS CO., LTD.

Add: No.14 Liangxi RD. Wuxi, Jiangsu, China **Mail:** 214061 <http://www.crhj.com.cn>
Tel: 0510-85807228 **Fax:** 0510-85800864

Marketing Part: **Post:** 214061 **Tel / Fax:** 0510-85807228-3663/5508
0510-85800360 (Fax)

Application and Service: **Post:** 214061 **Tel / Fax:** 0510-85807228-3399 / 2227