





1 2 3 4 5 6 7 8



Specifications :

- Voltage rating: 250V AC / DC
- Current rating: 3A AC / DC
- Withstanding voltage: 800V AC/minute
- Temperature range: -25°C~+85°C
- Insulation resistance: ≥1000MΩ
- Contact resistance: ≤10mΩ
- After environmental testing: ≤20mΩ

X2015 H X-2*XX -N0 XX

① ② ③ ④ ⑤ ⑥

- ① Series No.
- ② Category: H-HSG
- ③ Appearance type: Blank-Ordinary
- ④ Row No.-Pin No.: 2*XX-2*02P-2*20P
- ⑤ Material: N0-PA66 94V-0
- ⑥ Color: Blank-Natural Color

Poles	Dimensions (mm)		Poles	Dimensions (mm)	
	A	B		A	B
2*02	2.00	5.90	2*13	24.00	27.90
2*03	4.00	7.90	2*14	26.00	29.90
2*04	6.00	9.90	2*15	28.00	31.90
2*05	8.00	11.90	2*16	30.00	33.90
2*06	10.00	13.90	2*17	32.00	35.90
2*07	12.00	15.90	2*18	34.00	37.90
2*08	14.00	17.90	2*19	36.00	39.90
2*09	16.00	19.90	2*20	38.00	41.90
2*10	18.00	21.90			
2*11	20.00	23.90			
2*12	22.00	25.90			

X2015H-2*XX-N0	Nylon 66 UL 94V-0	X2026T	X2026W
PART NO	Material	Suitable XKB Terminal	Suitable XKB Terminal

For and on behalf of
XKB INDUSTRIAL PRECISION CO., LIMITED
 香港星坤工業精密有限公司

△ X					ANGULAR	±5°	
△ X					L ≤ 4	±0.2	
△ X					4 < L ≤ 16	±0.3	
MARK					16 < L ≤ 63	±0.4	
					L > 63	±0.5	
	DESCRIPTION	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES		
	REVISIONS					Authorized Signature(s)	

DSND		DATE		SCALE: N/A	MODEL	X2015H-2*XX-N0		
DWN		DATE		VIEW:	PART NO.:	2.00mm Crimp Style Connectors		
CHKD		DATE		UNIT: mm	DWG NO.:			
APPD		DATE		SIZE: A4				
					WEIGHT	SHEET	REVISION	
					1.0g	1/1	A0	

XKB INDUSTRIAL PRECISION CO., LIMITED

1 2 3 4 5 6 7 8