

- Highly reliable capacitors that withstand under high ripple current.
- Two or three dimensions with same ratings.
- Aluminum case designed explosion-proof vent.
- Best for switching power supplies.
- Load life: 3,000 hours.
- AEC-Q200 compliant. Please contact sales department for automotive specific PN.



SPECIFICATIONS

[illegible]

RIPPLE CURRENT MULTIPLIER

Frequency Coefficient

Coefficient \ Freq. (Hz)	60	120	1k	10k~50k
Rated Voltage				
10~100V	0.90	1.00	1.15	1.25
160~250V	0.80	1.00	1.25	1.47
315~450V	0.80	1.00	1.30	1.47
500~600V	0.80	1.00	1.28	1.41

PART NUMBER SYSTEM (EXAMPLE : 400V 100μF)

1	2 3	4 5 6	7	8 9	10	11 12	13 14
E	KP	107	M	2G	O	25	SW

Type (Terminal Code)

Case Length (25mm)

Diameter (25mm)

Voltage (400V)

Tolerance ($\pm 20\%$)

Capacitance (100μF)

Series

E-CAP

STANDARD RATINGS

Voltage (Code)		10V (1A)		16V (1C)		25V (1E)		35V (1V)	
Cap. (μF)	Code	Case Size	Ripple Current	Case Size	Ripple Current	Case Size	Ripple Current	Case Size	Ripple Current
2700	278							20 x 25	1.62
3300	338							20 x 30	1.94
								22 x 25	1.90
3900	398					20 x 25	1.72	20 x 35	2.02
								22 x 30	2.00
4700	478					20 x 30	2.04	20 x 40	2.21
						22 x 25	2.00	22 x 35	2.20
5600	568							25 x 25	2.20
				20 x 25	1.89	20 x 35	2.23	22 x 35	2.40
6800	688	20 x 25	1.41	20 x 30	2.25	22 x 30	2.20	25 x 30	2.40
				22 x 25	2.20	20 x 40	2.72	22 x 40	2.60
8200	828					22 x 30	2.40	25 x 35	2.60
						25 x 25	2.40	30 x 25	2.78
10000	109			20 x 35	2.43	22 x 35	2.70	22 x 50	2.90
						25 x 30	2.70	25 x 40	2.90
12000	129	20 x 30	1.67	22 x 30	2.40	30 x 25	2.70	30 x 30	2.90
15000	159	20 x 30	1.88	20 x 40	2.79	22 x 40	3.00	25 x 45	3.20
		22 x 25	1.80	22 x 30	2.60	25 x 35	3.00	30 x 35	3.20
18000	189	20 x 35	2.23	25 x 25	2.60	30 x 30	3.00		
		22 x 30	2.20						
22000	229	25 x 25	2.20	22 x 35	2.90	22 x 50	3.20	25 x 50	3.50
		20 x 40	2.31	25 x 30	2.90	25 x 40	3.20	30 x 40	3.50
27000	279	22 x 40	2.52	30 x 30	3.50	30 x 30	3.20	35 x 30	3.50
		25 x 30	2.40	22 x 40	3.20	25 x 45	3.60	30 x 45	3.90
33000	339	30 x 25	2.49	30 x 25	3.11	30 x 35	3.60	35 x 35	3.90
		22 x 45	2.60	25 x 35	3.20	35 x 30	3.60		
39000	399	25 x 40	2.60	22 x 45	3.50	30 x 40	3.90	35 x 40	4.51
		30 x 30	2.60	30 x 30	3.50	35 x 35	3.90		
47000	479	35 x 30	2.60	25 x 45	3.80	30 x 45	4.30	35 x 45	5.24
		22 x 45	3.19	30 x 30	3.80	35 x 35	4.30		
56000	569	25 x 50	4.20	35 x 30	3.80				
		30 x 35	4.20	25 x 40	4.20	35 x 45	4.80		
68000	689	30 x 40	4.70	35 x 35	4.70				
		35 x 35	4.70	30 x 45	4.90				
82000	829	30 x 45	5.10	30 x 50	5.27				
		35 x 40	5.10	35 x 45	5.50				
100000	1009	35 x 45	5.50						

Maximum Allowable Ripple Current (Arms) at 105°C 120Hz

Case Size $\Phi D \times L$ (mm)

KP

Large Can Aluminum Electrolytic Capacitors

Specifications are subject to change without notice. Should a safety or technical concern arise regarding the product, please be sure to contact our sales offices or agents immediately.

STANDARD RATINGS

Voltage (Code)		50V (1H)		63V (1J)		80V (1K)		100V (2A)	
Cap. (μF)	Code	Case Size	Ripple Current	Case Size	Ripple Current	Case Size	Ripple Current	Case Size	Ripple Current
560	567							20 x 25	0.95
680	687							20 x 30	1.15
								22 x 25	1.09
820	827					20 x 25	1.04	20 x 35	1.31
								22 x 30	1.40
1000	108			20 x 25	1.21	20 x 30	1.24	20 x 35	1.43
						22 x 25	1.19	22 x 30	1.47
								25 x 25	1.45
1200	128			20 x 30	1.43	20 x 35	1.43	20 x 40	1.61
				22 x 25	1.40	22 x 30	1.50	22 x 35	1.69
								25 x 30	1.68
1500	158	20 x 25	1.29	20 x 35	1.52	20 x 35	1.57	22 x 40	1.97
				22 x 30	1.50	22 x 30	1.59	25 x 35	1.98
						25 x 25	1.59	30 x 25	1.95
1800	188	20 x 30	1.53	20 x 35	1.72	20 x 40	1.77	22 x 45	2.23
				22 x 30	1.70	22 x 35	1.79	25 x 40	2.20
		22 x 25	1.50	25 x 25	1.70	25 x 30	1.71	30 x 30	2.20
2200	228	20 x 35	1.72	20 x 40	2.01	22 x 40	2.03	25 x 45	2.53
				22 x 35	2.00	25 x 35	2.10	30 x 35	2.55
		22 x 30	1.70	25 x 30	2.00	30 x 25	1.98	35 x 30	2.60
2700	278	20 x 35	1.82	22 x 40	2.20	22 x 45	2.39	25 x 50	2.82
		22 x 30	1.80	25 x 35	2.20	25 x 40	2.35	30 x 40	2.86
		25 x 25	1.80	30 x 25	2.20	30 x 30	2.35	35 x 35	2.90
3300	338	20 x 40	2.01	22 x 45	2.60	25 x 45	2.64	30 x 45	3.30
		22 x 35	2.00	25 x 35	2.39	30 x 35	2.61		
		25 x 30	2.00	30 x 30	2.50	35 x 30	2.60	35 x 35	3.25
3900	398	22 x 40	2.23	25 x 40	2.57	25 x 50	2.92	30 x 50	3.60
		25 x 30	2.20			30 x 40	2.82		
		30 x 25	2.20	30 x 35	2.70	35 x 30	2.97	35 x 40	3.67
4700	478	22 x 45	2.50	25 x 50	3.00	30 x 45	3.34		
		25 x 35	2.43	30 x 40	3.00			35 x 45	3.80
		30 x 30	2.50	35 x 30	3.00	35 x 35	3.38		
5600	568	22 x 50	2.80	30 x 40	3.22	30 x 50	3.80	35 x 50	4.05
		25 x 40	2.80			35 x 40	3.80		
		30 x 30	2.76	35 x 35	3.30				
6800	688	25 x 45	3.30	30 x 50	3.86	35 x 45	3.90		
		30 x 35	3.30						
		35 x 30	3.30	35 x 40	3.84				
8200	828	30 x 40	3.71	35 x 45	4.43	35 x 50	4.20		
		35 x 35	3.85						
10000	109	30 x 50	4.51	35 x 50	5.11				
		35 x 40	4.49						
12000	129	35 x 45	4.56						
15000	159	35 x 50	4.80						

Maximum Allowable Ripple Current (Arms) at 105°C 120Hz

Case Size ΦD x L (mm)

Specifications are subject to change without notice. Should a safety or technical concern arise regarding the product, please be sure to contact our sales offices or agents immediately.

STANDARD RATINGS

Voltage (Code)		160V (2C)		180V (2P)		200V (2D)		220V (2N)	
Cap. (μF)	Code	Case Size	Ripple Current	Case Size	Ripple Current	Case Size	Ripple Current	Case Size	Ripple Current
180	187							20 x 25	0.90
220	227			20 x 25	1.00	20 x 25	1.00	20 x 30	1.00
								22 x 25	1.00
270	277	20 x 25	1.10	20 x 30	1.10	20 x 30	1.10	20 x 35	1.15
				22 x 25	1.00	22 x 25	1.10	22 x 30	1.15
330	337	20 x 30	1.20	20 x 35	1.20	20 x 35	1.20	20 x 40	1.25
		22 x 25	1.20	22 x 30	1.20	22 x 30	1.25	22 x 35	1.25
						25 x 25	1.25	25 x 25	1.25
390	397	20 x 35	1.42	20 x 35	1.30	20 x 40	1.31	20 x 45	1.40
				22 x 30	1.35	22 x 35	1.35	22 x 35	1.40
		22 x 30	1.30	25 x 25	1.35	25 x 30	1.35	25 x 25	1.40
470	477	20 x 40	1.34	20 x 40	1.40	22 x 40	1.50	22 x 40	1.51
		22 x 30	1.55	22 x 35	1.50	25 x 30	1.50	25 x 30	1.44
		25 x 25	1.55	25 x 30	1.50	30 x 25	1.50	30 x 25	1.50
560	567	22 x 35	1.67	22 x 40	1.67	22 x 45	1.67	25 x 35	1.64
				25 x 30	1.67	25 x 35	1.70	30 x 30	1.70
		25 x 30	1.67	30 x 25	1.67	30 x 25	1.67	35 x 25	1.71
680	687	22 x 40	1.82	22 x 45	1.78	22 x 50	1.78	25 x 40	1.84
		25 x 35	1.85	25 x 35	1.78	25 x 40	1.82	30 x 35	1.93
		30 x 25	1.82	30 x 30	1.78	30 x 30	1.78	35 x 30	1.89
820	827	22 x 45	2.04	22 x 50	2.04	25 x 45	2.10	25 x 45	2.08
		25 x 40	2.04	25 x 40	2.04	30 x 35	2.04	30 x 40	2.19
		30 x 30	2.04	30 x 30	2.04	35 x 30	2.04	35 x 30	2.16
1000	108	25 x 45	2.40	25 x 45	2.30	25 x 50	2.42	30 x 45	2.50
		30 x 35	2.25	30 x 35	2.30	30 x 40	2.30	35 x 35	2.44
				35 x 30	2.30	35 x 35	2.30		
1200	128	25 x 50	2.62	30 x 40	2.55	30 x 45	2.65	35 x 40	2.79
		30 x 40	2.49						
		35 x 30	2.49	35 x 35	2.55	35 x 35	2.65		
1500	158	30 x 45	2.84	30 x 45	2.90	35 x 40	3.08	35 x 45	3.22
		35 x 35	2.84	35 x 40	2.90				
1800	188	30 x 50	3.32	35 x 45	3.30	35 x 45	3.48		
		35 x 40	3.00						
2200	228	35 x 45	3.50	35 x 50	3.65				

Maximum Allowable Ripple Current (Arms) at 105°C 120Hz

Case Size ΦD x L (mm)

STANDARD RATINGS

Voltage (Code)		250V (2E)		315V (2F)		350V (2V)		385V (2Y)	
Cap. (μF)	Code	Case Size	Ripple Current	Case Size	Ripple Current	Case Size	Ripple Current	Case Size	Ripple Current
56	566							20 x 25	0.37
68	686					20 x 25	0.47	20 x 30	0.44
								22 x 25	0.45
82	826			20 x 25	0.64	20 x 30	0.54	20 x 30	0.50
								22 x 30	0.52
100	107			20 x 30	0.69	20 x 30	0.60	20 x 35	0.56
						22 x 25	0.69	22 x 30	0.58
								25 x 25	0.57
120	127			20 x 30	0.75	20 x 35	0.68	20 x 40	0.66
						22 x 30	0.75	22 x 35	0.68
				22 x 25	0.75	25 x 25	0.75	25 x 30	0.68
150	157	20 x 25	0.79	20 x 35	0.82	20 x 40	0.78	22 x 40	0.79
				22 x 30	0.82	22 x 35	0.82	25 x 30	0.78
				25 x 25	0.82	25 x 30	0.83	30 x 25	0.75
180	187	20 x 30	0.90	20 x 40	0.90	22 x 40	0.92	22 x 45	0.89
				22 x 35	0.92	25 x 30	0.92	25 x 35	0.86
		22 x 25	0.88	25 x 30	0.93	30 x 25	0.90	30 x 30	0.88
220	227	20 x 35	1.00	22 x 40	1.04	22 x 50	1.05	22 x 50	1.01
		22 x 30	1.00	25 x 30	1.04	25 x 35	1.04	25 x 40	1.00
		25 x 25	1.08	30 x 25	1.04	30 x 30	1.02	30 x 30	1.00
270	277	20 x 40	1.10	22 x 45	1.16	22 x 50	1.16	25 x 45	1.13
		22 x 35	1.18	25 x 35	1.16	25 x 40	1.18	30 x 40	1.14
		25 x 30	1.27	30 x 25	1.16	30 x 30	1.17	35 x 30	1.10
330	337	22 x 40	1.30	22 x 50	1.33	25 x 45	1.29	30 x 45	1.31
		25 x 30	1.30	25 x 40	1.33	30 x 35	1.34		
		30 x 25	1.35	30 x 30	1.33	35 x 30	1.22	35 x 35	1.32
390	397	22 x 45	1.49	25 x 45	1.47	25 x 50	1.51	30 x 50	1.48
		25 x 35	1.49	30 x 35	1.47	30 x 40	1.51		
		30 x 30	1.49	35 x 30	1.47	35 x 35	1.47	35 x 40	1.48
470	477	22 x 50	1.65	30 x 40	1.70	30 x 45	1.65	35 x 45	1.76
		25 x 40	1.65						
		30 x 30	1.65	35 x 30	1.70	35 x 35	1.69		
560	567	25 x 45	1.80	30 x 45	2.05	30 x 50	1.85	35 x 50	1.95
		30 x 35	1.80	35 x 35	2.05	35 x 40	1.90		
680	687	25 x 50	2.03						
		30 x 40	2.00	35 x 40	2.17	35 x 45	2.20		
		35 x 30	2.00						
820	827	30 x 45	2.30	35 x 45	2.20				
		35 x 35	2.30						
1000	108	30 x 50	2.70						
		35 x 40	2.69						
1200	128	35 x 45	3.09						

Maximum Allowable Ripple Current (Arms) at 105°C 120Hz

Case Size Φ D x L (mm)

Specifications are subject to change without notice. Should a safety or technical concern arise regarding the product, please be sure to contact our sales offices or agents immediately.

STANDARD RATINGS

Voltage (Code)		400V (2G)		420V (2M)		450V (2W)	
Cap. (μF)	Code	Case Size	Ripple Current	Case Size	Ripple Current	Case Size	Ripple Current
47	476					20 x 25	0.39
56	566	20 x 25	0.51	20 x 25	0.51	20 x 30	0.51
						22 x 25	0.50
68	686	20 x 30	0.56	20 x 30	0.56	20 x 35	0.56
		22 x 25	0.50	22 x 25	0.55	22 x 30	0.53
						25 x 25	0.53
82	826	20 x 30	0.64	20 x 35	0.64	20 x 35	0.64
		22 x 25	0.64	22 x 25	0.64	22 x 30	0.64
				25 x 25	0.58	25 x 25	0.64
100	107	20 x 35	0.70	20 x 35	0.70	22 x 35	0.69
		22 x 30	0.70	22 x 30	0.70	25 x 25	0.65
		25 x 25	0.70	25 x 25	0.70	30 x 25	0.72
120	127	20 x 40	0.75	20 x 40	0.75	22 x 40	0.80
		22 x 35	0.75	22 x 35	0.75	25 x 30	0.80
		25 x 30	0.76	25 x 30	0.75		
				30 x 25	0.78	30 x 25	0.80
150	157	22 x 40	0.88	22 x 40	0.88	22 x 45	0.88
		25 x 30	0.83	25 x 35	0.88	25 x 35	0.88
		30 x 25	0.88	30 x 25	0.88	30 x 30	0.88
180	187	22 x 45	0.98	22 x 45	0.95	25 x 40	1.00
		25 x 35	0.98	25 x 40	0.97		
		30 x 30	0.98	30 x 30	0.96	30 x 30	1.00
				35 x 25	0.94		
220	227	22 x 50	1.10	25 x 45	1.13	25 x 45	1.12
		25 x 40	1.10	30 x 35	1.10	30 x 35	1.12
		30 x 30	1.10	35 x 25	1.10	35 x 30	1.12
270	277	25 x 50	1.29	25 x 50	1.37	30 x 40	1.28
		30 x 35	1.22	30 x 40	1.25		
		35 x 30	1.22	35 x 30	1.22	35 x 35	1.28
330	337	30 x 45	1.55	30 x 45	1.49	30 x 50	1.45
		35 x 30	1.44	35 x 35	1.45	35 x 40	1.45
390	397	30 x 45	1.60	30 x 50	1.67	35 x 40	1.55
		35 x 35	1.60	35 x 40	1.66		
470	477	35 x 40	1.90	35 x 45	1.90	35 x 50	1.85
560	567	35 x 45	2.12				

Maximum Allowable Ripple Current (Arms) at 105°C 120Hz

Case Size Φ D x L (mm)

KP

Large Can Aluminum Electrolytic Capacitors

Specifications are subject to change without notice. Should a safety or technical concern arise regarding the product, please be sure to contact our sales offices or agents immediately.

STANDARD RATINGS

Voltage (Code)		500V (2H)		550V (25)		600V (26)		
Cap. (μF)	Code	Case Size	Ripple Current	Case Size	Ripple Current	Case Size	Ripple Current	
150	157	25 x 45	0.86	25 x 50	0.86	30 x 50	0.78	
		30 x 40	0.90	30 x 45	0.90	35 x 45	0.82	
		35 x 35	0.90	35 x 40	0.92	35 x 50	0.86	
180	187	25 x 50	1.00	30 x 50	1.06	30 x 60	0.92	
		30 x 40	1.02	35 x 40	1.04	35 x 45	0.90	
220	227	30 x 45	1.18	30 x 60	1.34	35 x 50	1.12	
		35 x 35	1.12	35 x 40	1.26			
270	277	30 x 50	1.34	30 x 60	1.48	35 x 50	1.30	
		35 x 40	1.34	35 x 50	1.50			
330	337	30 x 60	1.61	30 x 60	1.64	35 x 60	1.58	
		35 x 40	1.50	35 x 50	1.68	40 x 50	1.58	
390	397	30 x 60	1.75	35 x 60	1.83	35 x 65	1.78	
		35 x 50	1.76	40 x 50	1.83	40 x 50	1.72	
470	477	35 x 50	1.93	35 x 60	2.00	35 x 70	2.02	
		40 x 40	1.90	40 x 50	2.00	40 x 60	2.04	
560	567	35 x 60	2.28	35 x 70	2.34	40 x 70	2.26	
		40 x 50	2.27	40 x 60	2.36			
680	687	35 x 70	2.68	40 x 70	2.78	45 x 70	2.60	
		40 x 60	2.70	45 x 60	2.78			
820	827	40 x 70	3.18	45 x 70	3.26	50 x 70	2.85	
		45 x 60	3.18	50 x 60	3.25			
1000	108	40 x 80	3.72	45 x 90	4.02	50 x 80	3.15	
		45 x 70	3.75	50 x 80	4.05			
1200	128	40 x 90	4.30	45 x 80	4.18	50 x 90	3.62	
		45 x 80	4.35	50 x 80	4.44			
		50 x 70	4.36					
1500	158	45 x 90	4.90	50 x 90	5.23	50 x 100	4.40	
		50 x 90	5.20	50 x 100	5.48			
1800	188	50 x 105	5.90	50 x 105	5.80	50 x 110	4.85	

Maximum Allowable Ripple Current (Arms) at 85°C 120Hz

Case Size Φ D x L (mm)

Specifications are subject to change without notice. Should a safety or technical concern arise regarding the product, please be sure to contact our sales offices or agents immediately.