





Stack-up Top Mount Double Sided Module
for 1.20 max top-side component height

Stack-up Top Mount Double Sided Module
for 1.35 max top-side component height

Stack-up Top Mount Double Sided Module
for 1.35 max top-side component height




HOW TO MATE AND EXTRACT

MATE: ① → ④

EXTRACT: ⑤






NOTE: Mating force will generate from step 3 to step 4.



RECOMMENDED PCB LAYOUT(TOP VIEW)

DEFAULT TOLERANCE $\pm 0.05\text{MM}$

GENERAL TOLERANCES UNLESS SPECIFIED		PART NO.		LOTES			
.X ± 0.35	X.° ± 3°	SEE TABLE					
.XX ± 0.25	.X.° ± 2°	APPROVED BY Barney		TITLE 0.5 PITCH M.2 8.5H TOP MOUNT-DOUBLE SIDED			
.XXX ± 0.15	.XX.° ± 1°						
CUSTOMER DRAWING		CHECKED BY Vito		DWG NO. AP-APCI0164-X			
SIZE	UNITS	DRAWN BY Sam			SHEET	SCALE	REV
A4	MM [INCH]				2 / 4	4 : 1	1C



GENERAL TOLERANCES UNLESS SPECIFIED		PART NO. SEE TABLE	LOTES			
.X± 0.35	X°± 3°		TITLE 0.5 PITCH M.2 8.5H TOP MOUNT-DOUBLE SIDED			
.XX± 0.25	X°± 2°	APPROVED BY Barney	DWG NO. AP-APCI0164-X			
.XXX±0.15	.XX°±1°					
CUSTOMER DRAWING		CHECKED BY Vito				
SIZE A4	UNITS MM[INCH]	DRAWN BY Sam				
			SHEET 3 / 4	SCALE 4 : 1	REV 1C	

