


Features

- Input Voltage up to 35V
- Output Voltage: 5V
- Output Current: 0.5A (Max)
- Overload Protection and Short-Circuit Limiting.

3-Terminal Voltage Regulator

TO-252




1、IN 2、GND 3、OUT

Absolute Maximum Ratings

Ratings at $T_A = 25^\circ\text{C}$ unless otherwise specified.

Parameter	Symbol	Value	Unit
Input Voltage	V_I	35	V
Thermal Resistance Junction-Ambient	$R_{\theta JA}$	100	$^\circ\text{C}/\text{W}$
Thermal Resistance Junction-Case	$R_{\theta JC}$	8.0	$^\circ\text{C}/\text{W}$
Operating Temperature Range	T_{OPR}	-40~125	$^\circ\text{C}$
Junction Temperature	T_J	150	$^\circ\text{C}$
Storage Temperature Range	T_{STG}	-55~150	$^\circ\text{C}$

Application Circuit









Electrical Characteristics

Ratings at $T_A = 25^\circ\text{C}$ unless otherwise specified.


Parameter	Symbol	Test Conditions	Min	Typ	Max	Unit
Output Voltage	V_O	$T_J=25^\circ\text{C}$	4.9	5	5.1	V
		$V_i=7V\text{-}20V \quad I_o=5\text{mA}\text{-}350\text{mA}$	4.8	5	5.2	V
Load Regulation	ΔV_O	$I_o=5\text{mA}\text{-}500\text{mA} \quad T_J=25^\circ\text{C}$	-	-	100	mV
		$I_o=5\text{mA}\text{-}200\text{mA} \quad T_J=25^\circ\text{C}$	-	-	50	mV
Line Regulation	ΔV_O	$V_i=7V\text{-}25V \quad T_J=25^\circ\text{C}$	-	-	100	mV
		$V_i=8V\text{-}25V \quad T_J=25^\circ\text{C}$	-	-	50	mV
Output Noise Voltage	e_N	$B=10\text{Hz}\text{-}100\text{KHz} \quad T_J=25^\circ\text{C}$	-	40	-	μV
Ripple Rejection	RR	$V_i=8V\text{-}18V \quad f=120\text{Hz}$	62	-	-	dB
Short Circuit Current	I_{sc}	$V_i=35V \quad T_J=25^\circ\text{C}$	-	300	-	mA
Quiescent Current	I_Q	$T_J=25^\circ\text{C}$	-	-	6	mA
Quiescent Current Change	ΔI_Q	$V_i=8V\text{-}25V$	-	-	0.8	mA
		$I_o=5\text{mA}\text{-}350\text{mA}$	-	-	0.5	mA
Output Voltage Drift	$\Delta V_O/\Delta T$	$I_o=5\text{mA}$	-	-0.5	-	$\text{mV}/^\circ\text{C}$
Dropout Voltage	V_D	$T_J=25^\circ\text{C}$	-	2	-	V
Short Circuit Peak Current	I_{scp}	$T_J=25^\circ\text{C}$	-	700	-	mA

Electrical Characteristics Curves



Package Outline

TO-252



Recommended Soldering Footprint

