华润微电子(重庆)有限公司

CRTM105N06L

Trench N-MOSFET 60V, 8mΩ, 56A

Features

- Uses CRM(CQ) advanced Trench MOS technology
- Extremely low on-resistance $R_{DS(on)}$
- Excellent Q_gx$R_{DS(on)}$ product(FOM)
- Qualified according to JEDEC criteria

Applications

- Motor control and drive
- Battery management
- UPS (Uninterrupible Power Supplies)

Product Summary

V_{DS}	60V
$R_{DS(on)}$ typ.	8mΩ
I_D	56A

100% DVDS Tested

100% Avalanche Tested

RoHS HF





Package Marking and Ordering Information

Part #	Marking	Package	Packing	Reel Size	Tape Width	Qty
CRTM105N06L	TM105N06L	DFN5X6	Reel	N/A	N/A	5000pcs

Absolute Maximum Ratings

Parameter	Symbol	Value	Unit
Drain-source voltage	V_{DS}	60	V
Continuous drain current T_C = 25°C (Silicon limit) T_C = 25°C (Package limit) T_C = 100°C (Silicon limit)	I_D	 56 124 36	A
Pulsed drain current (T_C = 25°C, t_p limited by T_{jmax})	$I_{D\ pulse}$	224	A
Avalanche energy, single pulse (L=0.5mH, Rg=25Ω)	E_{AS}	60	mJ
Gate-Source voltage	V_{GS}	±20	V
Power dissipation (T_C = 25°C)	P_{tot}	61	W
Operating junction and storage temperature	T_j , T_{stg}	-55...+150	°C
Soldering temperature, wave soldering only allowed at leads (1.6mm from case for 10s)	T_{sold}	260	°C

Thermal Resistance

Parameter	Symbol	Max	Unit
Thermal resistance, junction – case.	R_{thJC}	2.05	°C/W
Thermal resistance, junction – ambient(min. footprint)	R_{thJA}*	47	

Electrical Characteristic (at Tj = 25 °C, unless otherwise specified)

Parameter	Symbol	Value			Unit	Test Condition
		min.	typ.	max.		
Static Characteristic						
Drain-source breakdown voltage	BV_{DSS}	60	-	-	V	V_{GS}=0V, I_D=250uA
Gate threshold voltage	$V_{GS(th)}$	1.3	1.8	2.3	V	V_{DS}=V_{GS},I_D=250uA
Zero gate voltage drain current	I_{DSS}	- -	0.03 -	1 100	μA	V_{DS}=60V,V_{GS}=0V T_j=25°C T_j=150°C
Gate-source leakage current	I_{GSS}	-	±5	±100	nA	V_{GS}=±20V,V_{DS}=0V
Drain-source on-state resistance	$R_{DS(on)}$	- - 	8 15.5 10	10.5 19 12.5	mΩ	V_{GS}=10V, I_D=30A, T_j=25°C T_j=150°C V_{GS}=4.5V, I_D=25A
Transconductance	g_{fs}	-	77	-	S	V_{DS}=5V,I_D=30A
Dynamic Characteristic						
Input Capacitance	C_{iss}	-	1902	-	pF	V_{GS}=0V, V_{DS}=30V, f=1MHz
Output Capacitance	C_{oss}	-	201	-		
Reverse Transfer Capacitance	C_{rss}	-	142	-		
Gate Total Charge	Q_G	-	46	-	nC	V_{GS}=10V, V_{DS}=30V, I_D=30A, f=1MHz
Gate-Source charge	Q_{gs}	-	8.3	-		
Gate-Drain charge	Q_{gd}	-	13	-		
Turn-on delay time	$t_{d(on)}$	-	11	-	ns	V_{GS}=10V, V_{DD}=30V, R_{G_ext}=2.7Ω, I_D=30A
Rise time	t_r	-	61	-		
Turn-off delay time	$t_{d(off)}$	-	34	-		
Fall time	t_f	-	90	-		
Gate resistance	R_G	-	1.2	-	Ω	V_{GS}=0V, V_{DS}=0V, f=1MHz

Body Diode Characteristic

Parameter	Symbol	Value			Unit	Test Condition
		min.	typ.	max.		
Body Diode Forward Voltage	V_{SD}	-	0.8	1.3	V	V_{GS}=0V,I_{SD}=30A
Body Diode Continuous Forward Current	I_S			56	A	T_C = 25°C
Body Diode Reverse Recovery Time	t_{rr}	-	23	-	ns	I_F=30A, dI/dt=100A/μs
Body Diode Reverse Recovery Charge	Q_{rr}	-	19	-	nC	

*Weld the device to a PCB board with the size of 32mm*36mm and then place it in an one-cubic-foot air static box.

Typical Performance Characteristics

Fig 1: Output Characteristics



Fig 2: Transfer Characteristics



Fig 3: Rds(on) vs Drain Current and Gate Voltage



Fig 4: Rds(on) vs Gate Voltage



Fig 5: Rds(on) vs. Temperature



Fig 6: Capacitance Characteristics



Fig 7: Gate Charge Characteristics



Fig 8: Body-diode Forward Characteristics



Fig 9: Power Dissipation



Fig 10: Drain Current Derating



Fig 11: Safe Operating Area



Fig 12: Max. Transient Thermal Impedance



Test Circuit & Waveform

Gate Charge Test Circuit & Waveform





Resistive Switching Test Circuit & Waveforms





Unclamped Inductive Switching (UIS) Test Circuit & Waveforms





Diode Recovery Test Circuit & Waveforms





Package Outline: DFN5X6



Symbol	Dimensions In Millimeters		Dimensions In Inches	
	Min.	Max.	Min.	Max.
A	0.80	1.20	0.031	0.047
A1	0.00	0.05	0.000	0.002
b	0.30	0.51	0.012	0.020
c	0.15	0.35	0.006	0.014
D	4.80	5.40	0.189	0.213
e	1.27 BSC		0.050 BSC	
E	5.66	6.06	0.223	0.239
G	0.30	0.71	0.012	0.028
H	5.90	6.35	0.232	0.250
J	3.32	3.92	0.131	0.154
K	3.61	4.25	0.142	0.167
L1	0.05	0.25	0.002	0.010
L2	0.00	0.15	0.000	0.006
R	0.25 REF		0.010 REF	
θ	0°	12°	0°	12°

Revision History

Revison	Date	Major changes
1.0	2018/4/24	Release of formal version
2.0	2019/8/6	Increase the environmental labeling, I_S, T_{sold}, I_{DSS} test value at T_j=150°C and I_{GSS} test value at V_{GS}=-20V;Update $R_{DS(on)}$, g_{fs},V_{SD},$t_{d(on)}$/t_r/$t_{d(off)}$/t_f,Q_G/Q_{gs}/Q_{gd} and t_{rr}/Q_{rr} test current from 20A/40A to 30A;Update Fig2/Fig3/Fig4/Fig7 of Typical Performance Characteristics;Update Package Outline.

Disclaimer

Unless otherwise specified in the datasheet, the product is designed and qulified as a standard commercial product and is not intended for use in applications that require extraordinary levels of quality and reliability, such as automotive, aviation/aerospace and life-support devices or systems.

Any and all semicondutor products have certain probability to fail or malfunction, which may result in personal injury, death or property damage. Customer are solely responsible for providing adequate safe measures when design their systems.

CRM(CQ) reserves the right to improve product design, function and reliability without notice.