

## 8CH DARLINGTON SOURCE DRIVER


**IK62783**

The IK62783 are eight current drivers with common power supply and ground.

The IK62783 are purposed to use different devices: relays, lamps, displays (LED & gas discharge cells), in fluorescent indicators, telecommunication lines and logic devices.

### FEATURES


- High output voltage up to 50V
- One channel output current up to minus - 500 mA
- Output clamp diodes
- Single supply voltage 50V




**Table 1 – ELECTRIC CIRCUITRY DIFFERENCE OF ICS**

IC Marking	Quantity of Serially Connected Diodes	Applicable with ICs
IK62783N/D/DH	3	TTL, 5 V CMOS

Pin Connection (top view)



Schematics (each driver)



**Table 2 – PIN DESCRIPTION (DIP-18, SOP-18)**

<b>Pin Number</b>	<b>Symbol</b>	<b>Description</b>
01	IN 1	Input
02	IN 2	Input
03	IN 3	Input
04	IN 4	Input
05	IN 5	Input
06	IN 6	Input
07	IN 7	Input
08	IN 8	Input
09	Vcc	Supply voltage pin
10	GND	Common pin (ground)
11	OUT 8	Output
12	OUT 7	Output
13	OUT 6	Output
14	OUT 5	Output
15	OUT 4	Output
16	OUT 3	Output
17	OUT 2	Output
18	OUT 1	Output

**Table 3 – PIN DESCRIPTION (SOP-20)**

<b>Pin Number</b>	<b>Symbol</b>	<b>Description</b>
01	IN 1	Input
02	IN 2	Input
03	IN 3	Input
04	IN 4	Input
05	IN 5	Input
06	IN 6	Input
07	IN 7	Input
08	IN 8	Input
09	Vcc	Supply voltage pin
10	NC	NC
11	NC	NC
12	GND	Common pin (ground)
13	OUT 8	Output
14	OUT 7	Output
15	OUT 6	Output
16	OUT 5	Output
17	OUT 4	Output
18	OUT 3	Output
19	OUT 2	Output
20	OUT 1	Output

## ABSOLUTE MAXIMUM RATINGS

Symbol	Parameter		Min	Max	Unit
$V_{CC}$	Supply voltage		-	50	V
$I_{OUT}$	Output Current (One Channel)		-	-500	mA/ch
$V_{IN}$	Input voltage		-0.5	15	V
$V_R$	Clamp diode reverse voltage		-	50	V
$I_F$	Clamp diode forward current		-	500	mA
$T_{STG}$	Storage temperature		-60	150	°C
$P_D$	Power Dissipation	DIP	1.47		W
		SOP	0.96		W

\* Stresses beyond those listed under "absolute maximum ratings" may cause permanent damage to the device. These are stress ratings only and functional operation of the device at these or any other conditions beyond those indicated under "recommended operating conditions" is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

## RECOMMENDED OPERATION MODES

Symbol	Parameter		Test Condition		Min	Max	Unit	
$V_{CC}$	Supply voltage		-		-	50	V	
$I_{OUT}$	Output current	DIP	Ta=85 °C Tj=120 °C Tpw=25mS	Duty=10% 8 Circuits	-	-260	mA/ch	
				Duty=50% 8 Circuits		-59		
		SOP		Duty=10% 8 Circuits		-180		
				Duty=50% 8 Circuits		-38		
$V_R$	Clamp diode reverse voltage		-		-	50	V	
$I_F$	Clamp diode forward current		-		-	400	mA	

## ELECTRICAL CHARACTERISTICS


Parameter	Symbol	Test CIRCUIT	Measurement mode	Norm		Ta (°C)	Unit
				Min	Max		
Output leakage current at close (OFF) state of output	I <sub>CEX</sub>	1	V <sub>CC</sub> = 50 V V <sub>IN</sub> = 0.4 V	-	100	25±10	µA
Collector-emitter saturation voltage	V <sub>CE(sat)</sub>	2	I <sub>OUT</sub> = -100 mA V <sub>IN</sub> = 2 V	-	<u>1.8</u> 2.16	<u>25±10</u> -40 to 85	V
			I <sub>OUT</sub> = -225 mA V <sub>IN</sub> = 2 V	-	<u>1.9</u> 2.28		
			I <sub>OUT</sub> = -350 mA V <sub>IN</sub> = 2 V	-	<u>2.0</u> 2.4		
			I <sub>OUT</sub> = -225 mA V <sub>IN</sub> = 4.5 V	-	<u>1.9</u> 2.28		
			I <sub>OUT</sub> = -350 mA V <sub>IN</sub> = 4.5 V	-	<u>2.0</u> 2.4		
Input current	I <sub>IN(ON)</sub>	3	V <sub>IN</sub> = 2.4 V	-	<u>0.052</u> 0.082	<u>25±10</u> -40 to 85	mA
			V <sub>IN</sub> = 3.85 V	-	<u>0.26</u> 0.31		
			V <sub>IN</sub> = 12 V	-	<u>1.13</u> 1.356		
Input voltage at open (ON) state of output	V <sub>IN(ON)</sub>	4	I <sub>OUT</sub> = -350 mA V <sub>CE</sub> = 2 V	-	<u>2.0</u> 2.4	<u>25±10</u> -40 to 85	V
Input voltage at close (OFF) state of output,	V <sub>IN(OFF)</sub>		I <sub>OUT</sub> = -500 µA	<u>0.8</u> 0.64	-		
Consumption current	I <sub>CC(ON)</sub>	3	V <sub>IN</sub> = 2 V V <sub>CC</sub> = 50 V	-	<u>2.5</u> 3.0	<u>25±10</u> -40 to 85	mA
Reverse current of clamp diode	I <sub>R</sub>	5	V <sub>R</sub> = 50 V	-	<u>50</u> 60		
Forward DC voltage of clamp diode	V <sub>F</sub>	6	I <sub>F</sub> = 350 mA	-	<u>2.0</u> 2.4	<u>25±10</u> -40 to 85	V

## TYPICAL ELECTRIC PARAMETERS at Ta = 25 °C


Parameter	Symbol	Test CIRCUIT	Measurement mode	Typical	Max	Unit
Switch -ON delay	t <sub>ON</sub>	7	R <sub>L</sub> = 125 Ω, V <sub>CC</sub> = 50 V C <sub>L</sub> = 15 pF	0.15	0.3	µs
Switch-OFF delay	t <sub>OFF</sub>			3.0	5.0	µs

## Test Circuit


### 1. I<sub>CEx</sub>




### 2. V<sub>CE(sat)</sub>




### 3. I<sub>IN</sub> (ON), I<sub>CC</sub>




### 4. V<sub>IN</sub> (ON), V<sub>IN</sub> (OFF)




### 5. I<sub>R</sub>




### 6. V<sub>F</sub>




### 7. t<sub>ON</sub>, t<sub>OFF</sub>





Pulse width 50  $\mu\text{s}$ , ratio (duty cycle) 100% •  $t_W / T = 10\%$  (  $t_W$  – pulse width,  $\mu\text{s}$ ;  $T$  – period ,  $\mu\text{s}$ )


**Fig. 4 – Time diagram of IK62783 at measurement of signal delay at switching -ON  $t_{ON}$  and switching -OFF  $t_{OFF}$**



## PACKAGE DIMENSIONS


DIP-18

Unit: mm




SYMBOL	Dimension (mm)		
	Min	Typ	Max
BL	22.800		23.200
BW	6.200		6.600
FT	0.246		0.262
TL	7.900		8.800
LP	2.515		2.565
LW	0.432		0.482
A			4.310
A1	0.550		0.750
A2	3.300		3.500
b2		1.524	
LL	3.200		3.500
SW		7.620	
Z		0.570	

## SOP-18



SYMBOL	Dimension (mm)		
	Min	Typ	Max
BL	11.250		11.650
BW	7.400		7.800
FT	0.204		0.304
TL	10.300		10.500
LP	1.245		1.295
LW	0.381		0.431
A			2.700
A <sub>1</sub>	0.050		0.250
A <sub>2</sub>	2.250		2.450
A <sub>3</sub>	1.048BSC		
LL	1.40BSC		
FL	0.670		1.070
Θ	0		8
Z		0.440	

## SOP-20



SYMBOL	MILLIMETER		
	MIN	NOM	MAX
A	—	—	2.70
A1	0.10	0.20	0.30
A2	2.10	2.30	2.50
A3	0.92	1.02	1.12
b	0.35	—	0.44
b1	0.34	0.37	0.39
c	0.26	—	0.31
c1	0.24	0.25	0.26
D	12.60	12.80	13.00
E	10.10	10.30	10.50
E1	7.30	7.50	7.70
e	1.27BSC		
L	0.70	0.85	1.00
L1	1.40BSC		
θ	0	—	8°
L/F载体尺寸 (mil)	140*160		
	160*250		