MOSFET – Power, N-Channel, Logic Level, SOT-223 3.0 A, 60 V

Designed for low voltage, high speed switching applications in power supplies, converters and power motor controls and bridge circuits.

Features

- NVF Prefix for Automotive and Other Applications Requiring Unique Site and Control Change Requirements; AEC-Q101 Qualified and PPAP Capable
- These Devices are Pb-Free and are RoHS Compliant

Applications

- Power Supplies
- Converters
- Power Motor Controls
- Bridge Circuits

MAXIMUM RATINGS (T_C = 25°C unless otherwise noted)

Rating	Symbol	Value	Unit
Drain-to-Source Voltage	V _{DSS}	60	Vdc
Drain-to-Gate Voltage (R_{GS} = 1.0 M Ω)	V _{DGR}	60	Vdc
Gate–to–Source Voltage – Continuous – Non–repetitive (t _p ≤ 10 ms)	V _{GS}	± 15 ± 20	Vdc Vpk
$ \begin{array}{l} \text{Drain Current} \\ - \text{ Continuous @ } T_{A} = 25^{\circ}\text{C} \text{ (Note 1)} \\ - \text{ Continuous @ } T_{A} = 100^{\circ}\text{C} \text{ (Note 2)} \\ - \text{ Single Pulse (} t_{p} \leq 10 \ \mu\text{s}\text{)} \end{array} $	I _D I _D I _{DM}	3.0 1.4 9.0	Adc Apk
Total Power Dissipation @ $T_A = 25^{\circ}C$ (Note 1) Total Power Dissipation @ $T_A = 25^{\circ}C$ (Note 2) Derate above $25^{\circ}C$	P _D	2.1 1.3 0.014	Watts Watts W/°C
Operating and Storage Temperature Range	T _J , T _{stg}	-55 to 175	°C
$ Single Pulse Drain-to-Source Avalanche \\ Energy - Starting T_J = 25^\circ C \\ (V_{DD} = 25 Vdc, V_{GS} = 5.0 Vdc, \\ I_{L(pk)} = 7.0 Apk, L = 3.0 mH, V_{DS} = 60 Vdc) $	E _{AS}	74	mJ
Thermal Resistance –Junction-to-Ambient (Note 1) –Junction-to-Ambient (Note 2)	$R_{ heta JA}$ $R_{ heta JA}$	72.3 114	°C/W
Maximum Lead Temperature for Soldering Purposes, 1/8" from case for 10 seconds	ΤL	260	°C

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.



ON Semiconductor®

www.onsemi.com

3.0 A, 60 V R_{DS(on)} = 120 m Ω





MARKING DIAGRAM



PIN ASSIGNMENT



ORDERING INFORMATION

See detailed ordering and shipping information in the package dimensions section on page 6 of this data sheet.

- When surface mounted to an FR4 board using 1" pad size, 1 oz. (Cu. Area 1 in²).
 When surface mounted to an FR4 board using minimum recommended pad size, 2 oz. (Cu. Area 0.272 in²).

ELECTRICAL CHARACTERISTICS (T_A = 25°C unless otherwise noted)

Charac	Symbol	Min	Тур	Max	Unit	
OFF CHARACTERISTICS						
Drain-to-Source Breakdown Voltage (Note 3) $(V_{GS} = 0 \text{ Vdc}, I_D = 250 \ \mu\text{Adc})$ Temperature Coefficient (Positive)			60 -	68 68	-	Vdc mV/°C
Zero Gate Voltage Drain Current ($V_{DS} = 60 \text{ Vdc}, V_{GS} = 0 \text{ Vdc}$) ($V_{DS} = 60 \text{ Vdc}, V_{GS} = 0 \text{ Vdc}, T_J = 150^{\circ}\text{C}$)					1.0 10	μAdc
Gate-Body Leakage Current ($V_{GS} = \pm 15 \text{ Vdc}, V_{DS} = 0 \text{ Vdc}$)			-	-	± 100	nAdc
ON CHARACTERISTICS (Note 3)						
Gate Threshold Voltage (Note 3) ($V_{DS} = V_{GS}$, $I_D = 250 \ \mu Adc$) Threshold Temperature Coefficient (Negative)			1.0 -	1.68 4.6	2.0 - mV/°C	
Static Drain-to-Source On-Resistance (Note 3) (V _{GS} = 5.0 Vdc, I _D = 1.5 Adc)			_	92	120	mΩ
$ \begin{array}{l} Static \ Drain-to-Source \ On-Resistan \\ (V_{GS}=5.0 \ Vdc, \ I_D=3.0 \ Adc) \\ (V_{GS}=5.0 \ Vdc, \ I_D=1.5 \ Adc, \ T_J=0.0 \end{array} $	V _{DS(on)}	-	0.290 0.250	0.43 -	Vdc	
Forward Transconductance (Note 3)	9 _{fs}	-	5.7	-	Mhos	
DYNAMIC CHARACTERISTICS				-		
Input Capacitance		C _{iss}	-	313	440	pF
Output Capacitance	(V _{DS} = 25 Vdc, V _{GS} = 0 V, f = 1.0 MHz)	C _{oss}	-	112	160	
Transfer Capacitance	,	C _{rss}	-	40	60	
SWITCHING CHARACTERISTICS (No	ote 4)					
Turn-On Delay Time		t _{d(on)}	-	11	25	ns
Rise Time	$(V_{DD} = 30 \text{ Vdc}, I_D = 3.0 \text{ Adc},$	t _r	-	35	70	
Turn-Off Delay Time	V_{GS} = 5.0 Vdc, R _G = 9.1 Ω) (Note 3)	t _{d(off)}	-	22	45	
Fall Time		t _f	-	27	60	
Gate Charge		Q _T	-	7.6	15	nC
	(V _{DS} = 48 Vdc, I _D = 3.0 Adc, V _{GS} = 5.0 Vdc) (Note 3)	Q ₁	-	1.4	-	
		Q ₂	-	4.0	-	
SOURCE-DRAIN DIODE CHARACTE	RISTICS		-			•
Forward On-Voltage		V _{SD}		0.87 0.72	1.0 -	Vdc
Reverse Recovery Time		t _{rr}	-	35	-	ns
	(I _S = 3.0 Adc, V _{GS} = 0 Vdc,	ta	-	21	-]
	$dI_S/dt = 100 \text{ A}/\mu \text{s}$) (Note 3)	t _b	-	14	-	
Reverse Recovery Stored Charge	Q _{RR}	-	0.044	_	μC	

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

Pulse Test: Pulse Width ≤ 300 μs, Duty Cycle ≤ 2.0%.
 Switching characteristics are independent of operating junction temperatures.

TYPICAL ELECTRICAL CHARACTERISTICS



TYPICAL ELECTRICAL CHARACTERISTICS



TYPICAL ELECTRICAL CHARACTERISTICS



Figure 13. Thermal Response

ORDERING INFORMATION

Device	Package	Shipping [†]
NTF3055L108T1G	SOT-223 (TO-261) (Pb-Free)	1000 / Tape & Reel
NVF3055L108T1G	SOT-223 (TO-261) (Pb-Free)	1000 / Tape & Reel

+For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.

PACKAGE DIMENSIONS

SOT-223 (TO-261) CASE 318E-04 ISSUE N



NOTES: 1. DIMENSIONING AND TOLERANCING PER ASME Y14.5M, 1994. 2. CONTROLLING DIMENSION: INCH.

	MILLIMETERS			INCHES		
DIM	MIN	NOM	MAX	MIN	NOM	MAX
Α	1.50	1.63	1.75	0.060	0.064	0.068
A1	0.02	0.06	0.10	0.001	0.002	0.004
b	0.60	0.75	0.89	0.024	0.030	0.035
b1	2.90	3.06	3.20	0.115	0.121	0.126
С	0.24	0.29	0.35	0.009	0.012	0.014
D	6.30	6.50	6.70	0.249	0.256	0.263
E	3.30	3.50	3.70	0.130	0.138	0.145
е	2.20	2.30	2.40	0.087	0.091	0.094
e1	0.85	0.94	1.05	0.033	0.037	0.041
L	0.20			0.008		
L1	1.50	1.75	2.00	0.060	0.069	0.078
HE	6.70	7.00	7.30	0.264	0.276	0.287
θ	0°	-	10°	0°	-	10°
STYLE 3:						

SOLDERING FOOTPRINT*

PIN 1. GATE 2. DRAIN 3. SOURCE 4. DRAIN



*For additional information on our Pb–Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

ON Semiconductor and are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent_Marking.pdf. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor roducts, "typical" parameters which may be provided in ON Semiconductor dates the sets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typical" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor products reading, explained applications, Buyer shall indemnify and hold ON Semiconductor and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associa

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor 19521 E. 32nd Pkwy, Aurora, Colorado 80011 USA Phone: 303–675–2175 or 800–344–3860 Toll Free USA/Canada Fax: 303–675–2176 or 800–344–3867 Toll Free USA/Canada Email: orderlit@onsemi.com N. American Technical Support: 800–282–9855 Toll Free USA/Canada Europe, Middle East and Africa Technical Support:

Phone: 421 33 790 2910 Japan Customer Focus Center Phone: 81-3-5817-1050 ON Semiconductor Website: www.onsemi.com

Order Literature: http://www.onsemi.com/orderlit

For additional information, please contact your local Sales Representative