

ESD9N18BA

1-Line, Bi-directional, Transient Voltage Suppressors

<http://www.sh-willsemi.com>

Descriptions


The ESD9N18BA is a TVS (Transient Voltage Suppressor) designed to protect sensitive electronic components which are connected to data and transmission lines from over-stress caused by ESD (Electrostatic Discharge), EFT (Electrical Fast Transients) and lightning.

The ESD9N18BA may be used to provide ESD protection up to $\pm 30\text{kV}$ (contact discharge) according to IEC61000-4-2, and withstand peak pulse current up to 6.5A (8/20 μs) according to IEC61000-4-5.

The ESD9N18BA is available in DFN1006-2L package. Standard products are Pb-free and Halogen-free.




DFN1006-2L (Bottom View)



Circuit diagram

Features

- Stand-off voltage: $\pm 18\text{V}$ Max.
- Transient protection for each line according to IEC61000-4-2 (ESD): $\pm 30\text{kV}$ (contact discharge)
IEC61000-4-5 (surge): 6.5A (8/20 μs)
- Capacitance: $C_J = 8\text{pF}$ typ.
- Ultra-low leakage current: $I_R = 0.5\text{nA}$ typ.
- Low clamping voltage: $V_{CL} = 21\text{V}$ typ. @ $I_{PP} = 16\text{A}$ (TLP)
- Solid-state silicon technology



I = Device code

* = Month code (A~Z)

Marking (Top View)

Applications

- Computers and peripherals
- Cellular handsets
- Portable Electronics
- Notebooks


Order information

Device	Package	Shipping
ESD9N18BA-2/TR	DFN1006-2L	10000/Tape&Reel

Absolute maximum ratings

Parameter	Symbol	Rating	Unit
Peak pulse power ($t_p = 8/20\mu s$)	P_{pk}	150	W
Peak pulse current ($t_p = 8/20\mu s$)	I_{PP}	6.5	A
ESD according to IEC61000-4-2 air discharge	V_{ESD}	± 30	kV
ESD according to IEC61000-4-2 contact discharge		± 30	
Junction temperature	T_J	125	$^{\circ}C$
Operating temperature	T_{OP}	-40~85	$^{\circ}C$
Lead temperature	T_L	260	$^{\circ}C$
Storage temperature	T_{STG}	-55~150	$^{\circ}C$

Electrical characteristics ($T_A=25^{\circ}C$, unless otherwise noted)









Electrical characteristics ($T_A=25^\circ\text{C}$, unless otherwise noted)


Parameter	Symbol	Condition	Min.	Typ.	Max.	Unit
Stand-off voltage	V_{RWM}				± 18	V
Reverse leakage current	I_R	$V_{RWM} = 18\text{V}$		0.5	50	nA
Reverse breakdown voltage	V_{BR}	$I_T = 1\text{mA}$	19	21	23	V
Clamping voltage ¹⁾	V_{CL}	$I_{PP} = 16\text{A}$, $t_p = 100\text{ns}$		21		V
Dynamic resistance ¹⁾	R_{DYN}			0.3		Ω
Clamping voltage ²⁾	V_{CL}	$I_{PP} = 1\text{A}$, $t_p = 8/20\mu\text{s}$			21	V
		$I_{PP} = 6.5\text{A}$, $t_p = 8/20\mu\text{s}$			24	V
Junction capacitance	C_J	$V_R = 0\text{V}$, $f = 1\text{MHz}$		8	10	pF

1) TLP parameter: $Z_0 = 50\Omega$, $t_p = 100\text{ns}$, $t_r = 2\text{ns}$, averaging window from 60ns to 80ns. R_{DYN} is calculated from 20A to 80A.


2) Non-repetitive current pulse, according to IEC61000-4-5.

Typical characteristics ($T_A=25^\circ\text{C}$, unless otherwise noted)

8/20 μs waveform per IEC61000-4-5

Contact discharge current waveform per IEC61000-4-2

Clamping voltage vs. Peak pulse current

Capacitance vs. Reverse voltage

Non-repetitive peak pulse power vs. Pulse time

Power derating vs. Ambient temperature


Typical characteristics (TA=25°C, unless otherwise noted)




ESD clamping
(+8kV contact discharge per IEC61000-4-2)




ESD clamping
(-8kV contact discharge per IEC61000-4-2)






TLP Measurement

PACKAGE OUTLINE DIMENSIONS
DFN1006-2L


Symbol	Dimensions in Millimeters		
	Min.	Typ.	Max.
A	0.340	0.450	0.530
A1	0.000	0.020	0.050
A3	0.125 Ref.		
D	0.950	1.000	1.075
E	0.550	0.600	0.675
b	0.200	0.250	0.300
L	0.450	0.500	0.550
e	0.650 BSC		

Recommend PCB Layout (Unit: mm)

Notes:

This recommended land pattern is for reference purposes only. Please consult your manufacturing group to ensure your PCB design guidelines are met.

TAPE AND REEL INFORMATION
Reel Dimensions

Tape Dimensions

Quadrant Assignments For PIN1 Orientation In Tape



 User Direction of Feed

RD	Reel Dimension	☒ 7inch	☐ 13inch		
W	Overall width of the carrier tape	☒ 8mm	☐ 12mm		
P	Pitch between successive cavity centers	☒ 2mm	☐ 4mm	☐ 8mm	
Pin1	Pin1 Quadrant	☒ Q1	☒ Q2	☐ Q3	☐ Q4