

HSF

NOTES:
 Rated Current: 3.0AMP
 Contact Resistance: 20mΩ max
 Withstand Voltage: 1000V AC/DC
 Insulation Resistance: 1000MΩ min
 Operation Temperature: -25℃ to +85℃


Contact Material: Phosphor bronze
 Contact Plating: Au Or Sn Over Ni

Ordering Information

WF2548-T P XX 01

Material
 P=Phosphor Bronze

Contact Plating
 S0=Gold Flash/Tin
 S3=10u"Gold/Tin
 S4=15u"Gold/Tin
 S5=30u"Gold/Tin
 SN=Tin
 G0=Gold Flash
 G3=10u"Gold
 G4=15u"Gold
 G5=30u"Gold



Dimensional & Ordering Information

Part No.	Thickness	Finish	Material	Wire Range	Insulation O.D
WF2548-TPXX01	0.20	Tin	Phosphor Bronze	AWG#26	1.55mm(Max)

REV	DATE	MODIFICATION DESCRIPTION	CHANGE	OPERATION	DRAW	DATE	SCALE	FIT	PART NO.	TITLE:	Customer NO.
A4	2018/08/14	Modify	—	X.X	OPERATION	2018/08/14	UNIT	mm	SEE TAB	2.54mm TERMINAL FEMALE	WCON-Dongguan Tel: +86 769 85358920 Fax: +86 769 85358915 E-mail: sales@wcon.com
A3	2018/04/20	Modify	—	±0.40	Ding	DATE	inch	A4			
A2	2017/05/27	Modify	—	±0.25	CHECK	DATE	SIZE	1/1			
A0	2012/09/08	NEW	—	±0.15	APPROVE	DATE	SHEET	1/1			
				Angle			PROJ.				
				DIM	TOL						

WCON

Http: www.wcon.com

WCON-Dongguan
 Tel: +86 769 85358920
 Fax: +86 769 85358915
 E-mail: sales@wcon.com

WCON-Kunshan
 Tel: +86 512 57468408
 Fax: +86 512 57468468
 E-mail: salesks@wcon.com