


NOTES:
Rated Current:3.0AMP
Contact Resistance:20mΩ max
Withstand Voltage:1000V AC/DC
Insulation Resistance:1000MΩ min
Operation Temperature:−25℃ to +85℃

Contact Material:Phosphor bronze
Contact Plating:Au or Sn Over Ni

Ordering Information

WF2549 - T P XX 0 2

Contact Plating
G0=Gold Flash
G3=10u"Gold
G4=15u"Gold
G5=30u"Gold
S0=Gold Flash/Tin
S3=10u"Gold/Tin
S4=15u"Gold/Tin
S5=30u"Gold/Tin
SN=Tin



Specification & Ordering Information:

Part No.	Thickness	Finish	Material	Wire Range	Insulation O.D
WF2549-TPS002	0.25	Gold/Tin	Phosphor bronze	AWG#20~#24	1.55mm(Max)
WF2549-TPSN02	0.25	Tin-Plated	Phosphor bronze	AWG#20~#24	1.55mm(Max)

				OPERATION		DRAW Ding	DATE 2019/04/01	SCALE UNIT	FIT mm inch	PART NO. WF2549-TPXX02	WCON Http: www.wcon.com	
A2	2019/04/01	Modify the drawing	—	X.X	±0.40							
A1	2015/01/29	1.37±0.05 → 1.37±0.10	—	X.XX	±0.25	CHECK	DATE	SIZE	A4	TITLE: 2.54mm TERMINAL	WCON-Dongguan Tel: +86 769 85358920 Fax: +86 769 85358915 E-mail: sales@wcon.com	
AO	2012/09/08	NEW	—	X.XXX	±0.15	APPROVE	DATE	SHEET	1/1			
REV	DATE	MODIFICATION DESCRIPTION	CHANGE	Angle DIM	± 3° TOL			PROJ.	⌀	Customer NO.	WCON-Kunshan Tel: +86 512 57468408 Fax: +86 512 57468468 E-mail: salesks@wcon.com	