


# 產品製作規格書

產品料號	<b>306-76970</b>	VER: 2	產品名稱:	<b>CD32N-6R8M</b>			
圖面說明(單位:mm)			使用材料		注意事項		
			A	DRT3.5x2.1(ST)		(無鉛)	
			B	Ø0.15mm(2UEW-H)		180°C(原色)	
			C				
			D				
			E				
			F				
			G				
			A	3.5 ± 0.5		E	
			B	3.0 ± 0.5		F	
			C	2.1 ± 0.5		G	
D	1.0 (REF)		H				
測試儀器		L (µH)	DCR Ω (Max)	IDC A(Max)	測試條件		
TH2816B		6.8±20%	0.210	1.2	200KHz,0.25V		
客戶編碼	產品料號	送樣編號	修改項目	修改參數			
	306-76970	M8-06127					
				包裝方式			
A	3000	PCS/卷	D				
B	4	卷/盒	E				
C	2	盒/箱	F				
作業內容				修改記錄			
1.用DRT3.5x2.1(ST)的無鉛CORE生產(B=1.5mm,F=1.0mm).				時間	料號	修改內容	
2.用2UEW-H Ø0.15mm 180°C的原色高溫銅線,繞19Ts(REF).				1	2008.11.24	306-76970	更改為180°C的銅線制作.
3.采用新制程繞線,起線從CORE頂引入.				2	2015.4.7	306-76970	更改包裝方式.
4.CORE頂印1號白色Arial字體"6R8",要求印字要清晰.				3			
5.產品以無鉛制程制作.				4			
				5			
				6			
				7			
				8			
注意事項				9			
1.以感值為主;圈數為輔.				備 注			
2.可用同等功能的儀器測試電性.				A	1PCS產品單重: 0.082g		
3.保護帶的起點不能在包裝帶的收點處開始卷.				B			
4.產品L值按100%全測, DCR值按10%抽測.				C			
				D			
核準: _____		審核: _____		製表: 張小萍		發文日期: 2015.4.7	