

8V Input , 300mA , Low power , CMOS LDO**>Description**

AF6206N series are a highly precise, lower consumption, 3 terminal, positive voltage regulators manufactured using CMOS and laser trimming technologies.

The AF6206N consists of a current limiter circuit, a driver transistor, a precision reference voltage and an error correction circuit. The current limiter is fold-back circuit operates as a short circuit protection as well as the output current limiter for the output pin. Output voltages are internally by laser trimming technologies.

Applications

- Portable consumer equipment
- Wireless handsets, Smart Phones
- Bluetooth, Digital cameras and Digital audio
- PDAs and other handheld products

Device Information


AF 6206N – XX N/M/P R/G



① ② ③ ④ ⑤

| | |
|---|----------------------------------|
| ① | Standard |
| ② | Product Name |
| ③ | Output Voltage e.g. 12 = 1.2V |
| ④ | N: SOT23 Package |
| ④ | M: SOT23-3 Package |
| ④ | P: SOT89 Package |
| ⑤ | R: RoHS/Pb Free |
| ⑤ | G: Halogen Free |

Features

- Input Voltage Range: up to 8V
- Output Voltage Range: 1.2V~5V
- Output Current: 300mA
- Quiescent Current: 3uA
- Fixed Voltage Accuracy: $\pm 2\%$ (Typ.)
- PSRR: 50dB at 1kHz
- Low voltage drop
- Low temperature coefficient
- Compatible with low ESR ceramic capacitors
- Available in SOT-23/SOT23-3 and SOT-89 packages

Typical Application**Pin Configuration**

| Symbol | Package Pin | |
|--|-------------|-------|
| | SOT23 | SOT89 |
| GND | 1 | 1 |
| OUT | 2 | 3 |
| VIN | 3 | 2 |
|  SOT23(23-3) | | |
|  SOT89 | | |

**✚ Absolute Maximum Ratings⁽¹⁾**

(Unless otherwise specified, all voltage are with respect to GND, TA=25°C)

| PARAMETER | SYMBOL | RATINGS | UNITS | |
|--------------------------------------|------------------|----------------------|-------|---|
| Input Voltage | V _{IN} | -0.3~10 | V | |
| Output Voltage | V _{OUT} | -0.3~V _{IN} | V | |
| Output Current | I _{OUT} | 350 | mA | |
| Power Dissipation | SOT23 | P _D | 0.25 | W |
| | SOT23-3 | | 0.3 | W |
| | SOT89 | | 0.5 | W |
| Operating Junction Temperature Range | T _J | -40~125 | °C | |
| Maximum Ambient Temperature | T _A | 100 | °C | |
| Storage Temperature | T _{STG} | -40~125 | °C | |
| Lead Temperature(Soldering, 10 sec) | T _L | 260 | °C | |

(1). Stresses beyond those listed under absolute maximum ratings may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under recommended operating conditions is not implied. Exposure to absolute-maximum-rated conditions for extended periods my affect device reliability.

✚ Thermal Resistance Ratings(T_A=25°C unless otherwise noted)

| Parameter | Package | Symbol | Rating | Unit |
|----------------------------|---------|------------------|--------|-------|
| Package Thermal Resistance | SOT23 | R _{θJA} | 300 | °C/ W |
| | SOT23-3 | | 250 | |
| | SOT89 | | 150 | |







**AF6206N Series****Electronics Characteristics**


(Unless otherwise specified, VIN=VOUT+1V, CIN=COUT=1uF, TA=25°C)

| PARAMETER | SYMBOL | CONDITIONS | MIN | TYP | MAX | UNIT |
|------------------------------|--------------------|---|---------------------------|------------------|--------------------------|-------------------|
| Input Voltage | V _{IN} | | | | 8 | V |
| Output Voltage | V _{OUT} | | 0.98 V _{OUT} | V _{OUT} | 1.02 V _{OUT} | V |
| Dropout Voltage | V _{DIF} | I _{OUT} =100 mA | V _{OUT} ≤1.5V | 0.35 | | V |
| | | | 1.8V≤V _{OUT} ≤2V | 0.28 | | |
| | | | 2.8V≤V _{OUT} ≤5V | 0.19 | | |
| Quiescent Current | I _Q | I _{OUT} =0 | | 3 | 5 | uA |
| Line Regulation | ΔV _{LINE} | I _{OUT} =40mA V _{OUT} +1V≤V _{IN} ≤8V | | 0.05 | 0.2 | %/V |
| Load Regulation | ΔV _{LOAD} | V _{IN} =V _{OUT} +1V 1mA≤I _{OUT} ≤80mA | | 12 | 30 | mV |
| Temperature Coefficient | TC | I _{OUT} =30mA 0°C<T _A <75°C | | 100 | | ppm |
| Power Supply Rejection Ratio | PSRR | I _{OUT} =50mA 1kHz | | 50 | | dB |
| Output Noise | | 10Hz~100kHz | | 30 | | uV _{RMS} |


✚ Typical Characteristics

(Unless otherwise specified, $V_{IN}=V_{OUT}+1V$, $C_{IN}=C_{OUT}=1\mu F$, $TA=25^{\circ}C$)




 **Package Information****SOT23**

| Symbol | Dimensions In Millimeters | | Dimensions In Inches | |
|--------|---------------------------|-------|----------------------|-------|
| | Min. | Max. | Min. | Max. |
| A | 0.900 | 1.150 | 0.035 | 0.045 |
| A1 | 0.000 | 0.100 | 0.000 | 0.004 |
| A2 | 0.900 | 1.050 | 0.035 | 0.041 |
| b | 0.300 | 0.500 | 0.012 | 0.020 |
| c | 0.080 | 0.150 | 0.003 | 0.006 |
| D | 2.800 | 3.000 | 0.110 | 0.118 |
| E | 1.200 | 1.400 | 0.047 | 0.055 |
| E1 | 2.250 | 2.550 | 0.089 | 0.100 |
| e | 0.950 TYP. | | 0.037 TYP. | |
| e1 | 1.800 | 2.000 | 0.071 | 0.079 |
| L | 0.550 REF. | | 0.022 REF. | |
| L1 | 0.300 | 0.500 | 0.012 | 0.020 |
| θ | 0° | 8° | 0° | 8° |

SOT23-3


| Symbol | Dimensions In Millimeters | | Dimensions In Inches | |
|--------|---------------------------|-------|----------------------|-------|
| | Min | Max | Min | Max |
| A | 1.050 | 1.250 | 0.041 | 0.049 |
| A1 | 0.000 | 0.100 | 0.000 | 0.004 |
| A2 | 1.050 | 1.150 | 0.041 | 0.045 |
| b | 0.300 | 0.500 | 0.012 | 0.020 |
| c | 0.100 | 0.200 | 0.004 | 0.008 |
| D | 2.820 | 3.020 | 0.111 | 0.119 |
| E | 1.500 | 1.700 | 0.059 | 0.067 |
| E1 | 2.650 | 2.950 | 0.104 | 0.116 |
| e | 0.950(BSC) | | 0.037(BSC) | |
| e1 | 1.800 | 2.000 | 0.071 | 0.079 |
| L | 0.300 | 0.600 | 0.012 | 0.024 |
| θ | 0° | 8° | 0° | 8° |

SOT89

| Symbol | Dimensions In Millimeters | | Dimensions In Inches | |
|--------|---------------------------|-------|----------------------|-------|
| | Min | Max | Min | Max |
| A | 1.400 | 1.600 | 0.055 | 0.063 |
| b | 0.350 | 0.520 | 0.013 | 0.197 |
| b1 | 0.400 | 0.580 | 0.016 | 0.023 |
| c | 0.350 | 0.440 | 0.014 | 0.017 |
| D | 4.400 | 4.600 | 0.173 | 0.181 |
| D1 | 1.550 REF | | 0.061 REF | |
| E | 2.350 | 2.550 | 0.091 | 0.102 |
| E1 | 3.940 | 4.250 | 0.155 | 0.167 |
| e | 1.500 TYP | | 0.060TYP | |
| e1 | 3.000 TYP | | 0.118TYP | |
| L | 0.900 | 1.100 | 0.035 | 0.047 |

**Marking Rule**

- ① Represents product number

Mark: 6

- ② Represents 3 pins regulator

Mark: 5(Voltage=0.1V~3V)

6(Voltage=3.1V~6V)

- ③ Represents output voltage

| Mark | Voltage(V) | | Mark | Voltage(V) | |
|------|------------|-----|------|------------|-----|
| 0 | | 3.1 | F | 1.6 | 4.6 |
| 1 | | 3.2 | H | 1.7 | 4.7 |
| 2 | | 3.3 | K | 1.8 | 4.8 |
| 3 | | 3.4 | L | 1.9 | 4.9 |
| 4 | | 3.5 | M | 2.0 | 5.0 |
| 5 | | 3.6 | N | 2.1 | |
| 6 | | 3.7 | P | 2.2 | |
| 7 | | 3.8 | R | 2.3 | |
| 8 | | 3.9 | S | 2.4 | |
| 9 | | 4.0 | T | 2.5 | |
| A | | 4.1 | U | 2.6 | |
| B | 1.2 | 4.2 | V | 2.7 | |
| C | 1.3 | 4.3 | X | 2.8 | |
| D | 1.4 | 4.4 | Y | 2.9 | |
| E | 1.5 | 4.5 | Z | 3.0 | |

- ④ X

Packing Information

| Package | Packing | Shipping |
|---------|---------------|----------|
| SOT23 | | 3K/Reel |
| SOT23-3 | Tape and Reel | 3K/Reel |
| SOT89-3 | | 1K/Reel |

**History Version**

| | | |
|------|--|------------|
| V1.0 | Produce datasheet | 2019-09-09 |
| V2.0 | Add ambient temperature and thermal resistance | 2020-09-15 |

DISCLAIMER

AFSEMI RESERVES THE RIGHT TO MAKE CHANGES WITHOUT FURTHER NOTICE TO ANY PRODUCTS HEREIN TO IMPROVE RELIABILITY, FUNCTION OR DESIGN. AFSEMI DOES NOT ASSUME ANY LIABILITY ARISING OUT OF THE APPLICATION OR USE OF ANY PRODUCT OR CIRCUIT DESCRIBED HEREIN; NEITHER DOES IT CONVEY ANY LICENCE UNDER ITS PATENT RIGHTS, NOR THE RIGHTS OF OTHERS.

THE GRAPHS PROVIDED IN THIS DOCUMENT ARE STATISTICAL SUMMARIES BASED ON A LIMITED NUMBER OF SAMPLES AND ARE PROVIDED FOR INFORMATIONAL PURPOSE ONLY. THE PERFORMANCE CHARACTERISTICS LISTED IN THEM ARE NOT TESTED OR GUARANTEED. IN SOME GRAPHS, THE DATA PRESENTED MAY BE OUTSIDE THE SPECIFIED OPERATING RANGE (E.G. OUTSIDE SPECIFIED POWER SUPPLY RANGE) AND THEREFORE OUTSIDE THE WARRANTED RANGE.