

# Multilayer Chip Ferrite Bead – HPZ Series

Operating Temp. : -55℃~+125℃



## FEATURES

- Internal silver printed layers and magnetic shielded structures to minimize crosstalk
- Perfect effect for EMI suppression at high frequency ( $\geq 1\text{GHz}$ )
- Low DC resistance suitable for large current signals
- Four types material and wide range of impedance values for various applications


## APPLICATIONS

- High frequency noise suppression in electric equipments such as computers and peripheral devices, DVD, cameras, LCD TVs, communication equipments, OA equipments, etc.

## PRODUCT IDENTIFICATION

| ①<br><b>HPZ</b>                                              | ②<br><b>1608</b> | ③<br><b>D</b> | ④<br><b>221</b>                | ⑤<br><b>-R60</b> | ⑥<br><b>T</b>                        | ⑦<br><b>F</b> |
|--------------------------------------------------------------|------------------|---------------|--------------------------------|------------------|--------------------------------------|---------------|
| ①                                                            | ②                |               | ③                              |                  | ④                                    |               |
| Type                                                         | HPZ              |               | External Dimensions (L×W) (mm) |                  | Material Code                        |               |
|                                                              |                  |               |                                |                  | G, D, E, U                           |               |
| Chip Ferrite Bead<br>For High Frequency<br>and Large Current |                  | 1005 [0402]   |                                | 1.0×0.5          | ⑥                                    |               |
|                                                              |                  | 1608 [0603]   |                                | 1.6×0.8          |                                      |               |
|                                                              |                  |               |                                |                  | Packing                              |               |
|                                                              |                  |               |                                |                  | T Tape & Reel                        |               |
|                                                              |                  |               |                                |                  | ⑦                                    |               |
|                                                              |                  |               |                                |                  | Hazardous Substance<br>Free Products |               |
|                                                              |                  |               |                                |                  | F                                    |               |

## SHAPE AND DIMENSIONS



| Unit: mm [inch]   |                         |                         |                         |                         |
|-------------------|-------------------------|-------------------------|-------------------------|-------------------------|
| Type              | L                       | W                       | T                       | a                       |
| HPZ1005<br>[0402] | 1.0±0.15<br>[.039±.006] | 0.5±0.15<br>[.020±.006] | 0.5±0.15<br>[.020±.006] | 0.25±0.1<br>[.010±.004] |
| HPZ1608<br>[0603] | 1.6±0.15<br>[.063±.006] | 0.8±0.15<br>[.031±.006] | 0.8±0.15<br>[.031±.006] | 0.3±0.2<br>[.012±.008]  |

## SPECIFICATIONS

### HPZ1005 TYPE

| Part Number       | Impedance |            | Max. DC Resistance | Max. Rated Current | Thickness               |
|-------------------|-----------|------------|--------------------|--------------------|-------------------------|
|                   | @100MHz   | @1GHz Min. |                    |                    |                         |
| Units 单位          | $\Omega$  |            | $\Omega$           | mA                 | mm [inch]               |
| Symbol 符号         | Z         |            | DCR                | Ir                 | T                       |
| HPZ1005D121-R60TF | 120±25%   | 100        | 0.25               | 600                | 0.5±0.15<br>[.020±.006] |
| HPZ1005D221-R50TF | 220±25%   | 300        | 0.38               | 500                |                         |
| HPZ1005U121-R60TF | 120±25%   | 100        | 0.25               | 600                |                         |
| HPZ1005U121-1R1TF | 120±25%   | 100        | 0.13               | 1100               |                         |
| HPZ1005U221-R50TF | 220±25%   | 200        | 0.38               | 500                |                         |
| HPZ1005U221-R70TF | 220±25%   | 250        | 0.25               | 700                |                         |


### HPZ1608 TYPE

| Part Number       | Impedance |            | Max. DC Resistance | Max. Rated Current | Thickness               |
|-------------------|-----------|------------|--------------------|--------------------|-------------------------|
|                   | @100MHz   | @1GHz Min. |                    |                    |                         |
| Units             | $\Omega$  |            | $\Omega$           | mA                 | mm [inch]               |
| Symbol            | Z         |            | DCR                | Ir                 | T                       |
| HPZ1608G121-R90TF | 120±25%   | 700        | 0.13               | 900                | 0.8±0.15<br>[.031±.006] |
| HPZ1608D121-1R5TF | 120±25%   | 200        | 0.07               | 1500               |                         |
| HPZ1608D151-R80TF | 150±25%   | 200        | 0.2                | 800                |                         |
| HPZ1608D151-1R5TF | 150±25%   | 200        | 0.07               | 1500               |                         |
| HPZ1608D221-R60TF | 220±25%   | 300        | 0.25               | 600                |                         |
| HPZ1608D221-1R2TF | 220±25%   | 300        | 0.12               | 1200               |                         |
| HPZ1608D331-R50TF | 330±25%   | 500        | 0.3                | 500                |                         |
| HPZ1608D331-R90TF | 330±25%   | 500        | 0.15               | 900                |                         |
| HPZ1608D391-R70TF | 390±25%   | 600        | 0.18               | 700                |                         |
| HPZ1608D471-R50TF | 470±25%   | 700        | 0.32               | 500                |                         |
| HPZ1608D471-R70TF | 470±25%   | 700        | 0.22               | 700                |                         |
| HPZ1608D601-R50TF | 600±25%   | 1000       | 0.35               | 500                |                         |
| HPZ1608D601-R70TF | 600±25%   | 1000       | 0.24               | 700                |                         |
| HPZ1608D102-R15TF | 1000±25%  | 1300       | 0.9                | 150                |                         |
| HPZ1608D102-R60TF | 1000±25%  | 1000       | 0.35               | 600                |                         |
| HPZ1608E601-R80TF | 600±25%   | 500        | 0.25               | 800                |                         |
| HPZ1608E102-R60TF | 1000±25%  | 600        | 0.35               | 600                |                         |
| HPZ1608E152-R50TF | 1500±25%  | 1000       | 0.5                | 500                |                         |
| HPZ1608U101-R80TF | 100±25%   | 100        | 0.2                | 800                |                         |
| HPZ1608U101-2R0TF | 100±25%   | 100        | 0.055              | 2000               |                         |
| HPZ1608U121-2R0TF | 120±25%   | 110        | 0.055              | 2000               |                         |
| HPZ1608U221-R60TF | 220±25%   | 220        | 0.25               | 600                |                         |
| HPZ1608U331-R50TF | 330±25%   | 300        | 0.3                | 500                |                         |
| HPZ1608U471-R50TF | 470±25%   | 400        | 0.32               | 500                |                         |
| HPZ1608U601-R50TF | 600±25%   | 450        | 0.35               | 500                |                         |
| HPZ1608U102-R15TF | 1000±25%  | 750        | 0.9                | 150                |                         |

※: Products with other electrical characteristics can be provided upon customer's request. Please contact your local sales.


## TYPICAL ELECTRICAL CHARACTERISTICS

### D, E, U Material Comparison









### Rated Current

When operating temperatures exceed +85°C, derating of current is necessary for chip ferrite beads for which rated current is 800mA and over. Please apply the derating curve shown in chart according to the operating temperature.









## DETAIL ELECTRICAL CHARACTERISTICS

### HPZ1005 TYPE



### HPZ1608 TYPE



**Sunlord**


Specifications subject to change without notice. Please check our website for latest information.

Revised: 2012/05/10

Sunlord Industrial Park, Dafuyuan Industrial Zone, Guanlan, Shenzhen, China 518110 Tel: 0086-755-29832660 Fax: 0086-755-82269029 E-Mail: sunlord@sunlordinc.com

# DETAIL ELECTRICAL CHARACTERISTICS

## HPZ1608 TYPE



DETAIL ELECTRICAL CHARACTERISTICS

HPZ1608 TYPE

