




ST3407SRG 
P Channel Enhancement Mode MOSFET

-3.6A

DESCRIPTION


ST3407SRG is the P-Channel logic enhancement mode power field effect transistor which is produced using high cell density, DMOS trench technology. This high density process is especially tailored to minimize on-state resistance. These devices are particularly suited for low voltage application such as cellular phone and notebook computer power management, other battery powered circuits, and low in-line power loss are required. The product is in a very small outline surface mount package.

PIN CONFIGURATION SOT-23



1.Gate 2.Source 3.Drain


PART MARKING SOT-23



Y: Year Code A: Process Code

FEATURE

- -30V/-4.0A, $R_{DS(ON)} = 54m\Omega$ (Typ.)
@ $V_{GS} = -10V$
- -30V/-3.2A, $R_{DS(ON)} = 72m\Omega$
@ $V_{GS} = -4.5V$
- Super high density cell design for extremely low $R_{DS(ON)}$
- Exceptional on-resistance and maximum DC current capability
- SOT-23 package design





ST3407SRG

P Channel Enhancement Mode MOSFET

-3.6A

ABSOLUTE MAXIMUM RATINGS (Ta = 25°C Unless otherwise noted)

| Parameter | Symbol | Typical | Unit |
|--|------------------|--------------|------|
| Drain-Source Voltage | V _{DSS} | -30 | V |
| Gate-Source Voltage | V _{GSS} | ±20 | V |
| Continuous Drain Current TJ=150°C) | I _D | -3.6 -3.0 | A |
| Pulsed Drain Current | I _{DM} | -15 | A |
| Continuous Source Current (Diode Conduction) | I _S | -1.0 | A |
| Power Dissipation | P _D | 1.20 0.8 | W |
| Operation Junction Temperature | T _J | 150 | °C |
| Storage Temperature Range | T _{STG} | -55/150 | °C |
| Thermal Resistance-Junction to Ambient | R _{θJA} | 120 | °C/W |



ST3407SRG



P Channel Enhancement Mode MOSFET

-3.6A

ELECTRICAL CHARACTERISTICS (Ta = 25°C Unless otherwise noted)

| Parameter | Symbol | Condition | Min | Typ | Max | Unit |
|---------------------------------|---------------------------|---|------|----------|------|------|
| Static | | | | | | |
| Drain-Source Breakdown Voltage | V _{(BR)DSS} | V _{GS} =0V, I _D =-250uA | -30 | | | V |
| Gate Threshold Voltage | V _{GS(th)} | V _{DS} =V _{GS} , I _D =-250uA | -1.0 | | -3.0 | V |
| Gate Leakage Current | I _{GSS} | V _{DS} =0V, V _{GS} =±20V | | | ±100 | Na |
| Zero Gate Voltage Drain Current | I _{DSS} | V _{DS} =-24V, V _{GS} =0V | | | -1 | UA |
| | | V _{DS} =-24V, V _{GS} =0V T _J =55°C | | | -9.5 | |
| Drain-source On-Resistance | R _{DS(on)} | V _{GS} =-10.0V, I _D =-4.0A V _{GS} =-4.5V, I _D =-3.2A | | 54 72 | | mΩ |
| Forward Transconductance | g _{fs} | V _{DS} =-5.0V, I _D =-4.0A | | 10 | | S |
| Diode Forward Voltage | V _{SD} | I _S =-1.0A, V _{GS} =0V | | -0.8 | -1.2 | V |
| Dynamic | | | | | | |
| Total Gate Charge | Q _g | V _{DS} =-15V V _{GS} =-10V I _D =-4.0A | | 14 | 21 | nC |
| Gate-Source Charge | Q _{gs} | | | 1.9 | | |
| Gate-Drain Charge | Q _{gd} | | | 3.7 | | |
| Input Capacitance | C _{iss} | V _{DS} =-15V V _{GS} =0V F=1MHz | | 540 | | pF |
| Output Capacitance | C _{oss} | | | 131 | | |
| Reverse Transfer Capacitance | C _{rss} | | | 105 | | |
| Turn-On Time | t _{d(on)} tr | V _{DD} =-15V R _L =15Ω I _D =-1.0A V _{GEN} =-10V R _G =6Ω | | 10 | 16 | nS |
| Turn-Off Time | t _{d(off)} tf | | | 16 | 25 | |
| | | | | 32 | 50 | |
| | | | | 21 | 32 | |









ST3407SRG



P Channel Enhancement Mode MOSFET

-3.6A

TYPICAL CHARACTERISTICS (25°C unless otherwise noted)



STANSON TECHNOLOGY
120 Bentley Square, Mountain View, Ca 94040 USA
www.stansontech.com








ST3407SRG



P Channel Enhancement Mode MOSFET

-3.6A

TYPICAL CHARACTERISTICS (25°C unless otherwise noted)



STANSON TECHNOLOGY
120 Bentley Square, Mountain View, Ca 94040 USA
www.stansontech.com


ST3407SRG 2006. V1



ST3407SRG P Channel Enhancement Mode MOSFET

-3.6A

SOT-23 PACKAGE OUTLINE



| Symbol | Dimensions In Millimeters | | Dimensions In Inches | |
|--------|---------------------------|-------|----------------------|-------|
| | Min | Max | Min | Max |
| A | 0.900 | 1.100 | 0.035 | 0.043 |
| A1 | 0.000 | 0.100 | 0.000 | 0.004 |
| A2 | 0.900 | 1.000 | 0.035 | 0.039 |
| b | 0.300 | 0.500 | 0.012 | 0.020 |
| c | 0.080 | 0.150 | 0.003 | 0.006 |
| D | 2.800 | 3.000 | 0.110 | 0.118 |
| E | 1.200 | 1.400 | 0.047 | 0.055 |
| E1 | 2.250 | 2.550 | 0.089 | 0.100 |
| e | 0.950TYP | | 0.037TYP | |
| e1 | 1.800 | 2.000 | 0.071 | 0.079 |
| L | 0.550REF | | 0.022REF | |
| L1 | 0.300 | 0.500 | 0.012 | 0.020 |
| θ | 0° | 8° | 0° | 8° |

STANSON TECHNOLOGY
120 Bentley Square, Mountain View, Ca 94040 USA
www.stansontech.com

ST3407SRG 2006. V1