




ST2304SRG 
N Channel Enhancement Mode MOSFET

3.2A

DESCRIPTION

ST2304SRG is the N-Channel logic enhancement mode power field effect transistor which is produced using high cell density, DMOS trench technology. This high density process is especially tailored to minimize on-state resistance. These devices are particularly suited for low voltage application such as cellular phone and notebook computer power management, other battery powered circuits, and low in-line power loss are required. The product is in a very small outline surface mount package.

PIN CONFIGURATION SOT-23




1.Gate 2.Source 3.Drain


FEATURE

- 30V/3.2A, $R_{DS(ON)} = 44\text{m-ohm}$ (Typ.) @ $VGS = 10.0\text{V}$
- 30V/2.0A, $R_{DS(ON)} = 60\text{m-ohm}$ @ $VGS = 4.5\text{V}$
- Super high density cell design for extremely low $R_{DS(ON)}$
- Exceptional on-resistance and maximum DC current capability
- SOT-23 package design

PART MARKING SOT-23



Y: Year Code A: Process Code





ST2304SRG 

N Channel Enhancement Mode MOSFET

3.2A

ABSOULTE MAXIMUM RATINGS (Ta = 25°C Unless otherwise noted)

| Parameter | | Symbol | Typical | Unit |
|--|--|------------------|----------------|-------------|
| Drain-Source Voltage | | V _{DSS} | 30 | V |
| Gate-Source Voltage | | V _{GSS} | ±20 | V |
| Continuous Drain Current TJ=150°C) | T _A =25°C T _A =70°C | I _D | 3.2 2.6 | A |
| Pulsed Drain Current | | I _{DM} | 10 | A |
| Continuous Source Current (Diode Conduction) | | I _S | 1.20 | A |
| Power Dissipation | T _A =25°C T _A =70°C | P _D | 1.20 0.8 | W |
| Operation Junction Temperature | | T _J | 150 | °C |
| Storage Temperature Range | | T _{STG} | -55/150 | °C |
| Thermal Resistance-Junction to Ambient | | R _{θJA} | 100 | °C/W |



ST2304SRG







N Channel Enhancement Mode MOSFET

3.2A






ELECTRICAL CHARACTERISTICS (Ta = 25°C Unless otherwise noted)

| Parameter | Symbol | Condition | Min | Typ | Max | Unit |
|---------------------------------|---------------------------|--|-----|----------------|----------------|------|
| Static | | | | | | |
| Drain-Source Breakdown Voltage | V _{(BR)DSS} | V _{GS} =0V, I _D =250μA | 30 | | | V |
| Gate Threshold Voltage | V _{GS(th)} | V _{DS} =V _{GS} , I _D =250μA | 1.0 | | 2.0 | V |
| Gate Leakage Current | I _{GSS} | V _{DS} =0V, V _{GS} =±20V | | | ±100 | nA |
| Zero Gate Voltage Drain Current | I _{DSS} | V _{DS} =30V, V _{GS} =1.0V | | | 1 | uA |
| | | V _{DS} =30V, V _{GS} =0V T _J =55°C | | | 10 | |
| Drain-source On-Resistance | R _{D(on)} | V _{GS} =10V, I _D =3.2A V _{GS} =4.5V, I _D =2.0A | | 0.044 0.060 | 0.052 0.067 | Ω |
| Forward Transconductance | g _f | V _{DS} =4.5V, I _D =2.5V | | 4.6 | | S |
| Diode Forward Voltage | V _{SD} | I _S =1.25A, V _{GS} =0V | | | 1.2 | V |
| Dynamic | | | | | | |
| Total Gate Charge | Q _g | V _{DS} =15V V _{GS} =10V I _D =2.5A | | 4.5 | 10 | nC |
| Gate-Source Charge | Q _{gs} | | | 0.8 | | |
| Gate-Drain Charge | Q _{gd} | | | 1.0 | | |
| Input Capacitance | C _{iss} | V _{DS} =15V V _{GS} =0V F=1MHz | | 240 | | pF |
| Output Capacitance | C _{oss} | | | 110 | | |
| Reverse Transfer Capacitance | C _{rss} | | | 17 | | |
| Turn-On Time | t _{d(on)} tr | V _{DD} =15V R _L =15Ω I _D =1.0A V _{GEN} =10V R _G =6Ω | | 8.0 | 20 | nS |
| Turn-Off Time | t _{d(off)} tf | | | 12 | 30 | |
| | | | | 17 | 35 | |
| | | | | 8.0 | 20 | |


TYPICAL CHARACTERISTICS (25°C Unless noted)



TYPICAL CHARACTERISTICS (25°C Unless noted)



SOT-23 PACKAGE OUTLINE



| Symbol | Dimensions In Millimeters | | Dimensions In Inches | |
|--------|---------------------------|-------|----------------------|-------|
| | Min | Max | Min | Max |
| A | 0.900 | 1.100 | 0.035 | 0.043 |
| A1 | 0.000 | 0.100 | 0.000 | 0.004 |
| A2 | 0.900 | 1.000 | 0.035 | 0.039 |
| b | 0.300 | 0.500 | 0.012 | 0.020 |
| c | 0.080 | 0.150 | 0.003 | 0.006 |
| D | 2.800 | 3.000 | 0.110 | 0.118 |
| E | 1.200 | 1.400 | 0.047 | 0.055 |
| E1 | 2.250 | 2.550 | 0.089 | 0.100 |
| e | 0.950TYP | | 0.037TYP | |
| e1 | 1.800 | 2.000 | 0.071 | 0.079 |
| L | 0.550REF | | 0.022REF | |
| L1 | 0.300 | 0.500 | 0.012 | 0.020 |
| θ | 0° | 8° | 0° | 8° |