



**ST3400SRG**   
N Channel Enhancement Mode MOSFET

5.8A


## DESCRIPTION

The ST3400SRG is the N-Channel logic enhancement mode power field effect transistor is produced using high cell density, DMOS trench technology.

This high-density process is especially tailored to minimize on-state resistance. These devices are particularly suited for low voltage application such as cellular phone and notebook computer power management and other battery powered circuits where high side switching.

## PIN CONFIGURATION

SOT-23




## FEATURE


- 30V/5.8A,  $R_{DS(ON)} = 25m\Omega$  (Typ.)  
@ $V_{GS} = 10V$
- 30V/4.8A,  $R_{DS(ON)} = 30m\Omega$   
@ $V_{GS} = 4.5V$
- 30V/4.0A,  $R_{DS(ON)} = 40m\Omega$   
@ $V_{GS} = 2.5V$
- Super high density cell design for extremely low  $R_{DS(ON)}$
- Exceptional on-resistance and maximum DC current capability
- SOT-23 package design

## PART MARKING

SOT-23



Y: Year Code    A: Week Code





**ST3400SRG**   
N Channel Enhancement Mode MOSFET

5.8A

**ABSOLUTE MAXIMUM RATINGS** (Ta = 25°C Unless otherwise noted )

Parameter	Symbol	Typical	Unit
Drain-Source Voltage	V <sub>DSS</sub>	30	V
Gate-Source Voltage	V <sub>GSS</sub>	±12	V
Continuous Drain Current(T <sub>J</sub> =150°C)	I <sub>D</sub>	5.8 3.5	A
Pulsed Drain Current	I <sub>DM</sub>	25	A
Continuous Source Current (Diode Conduction)	I <sub>S</sub>	1.7	A
Power Dissipation	P <sub>D</sub>	2.0 1.3	W
Operation Junction Temperature	T <sub>J</sub>	150	°C
Storage Temperature Range	T <sub>STG</sub>	-55/150	°C
Thermal Resistance-Junction to Ambient	R <sub>θJA</sub>	90	°C/W



**ST3400SRG**



N Channel Enhancement Mode MOSFET

5.8A

**ELECTRICAL CHARACTERISTICS ( Ta = 25°C Unless otherwise noted )**

Parameter	Symbol	Condition	Min	Typ	Max	Unit
<b>Static</b>						
Drain-Source Breakdown Voltage	V <sub>(BR)DSS</sub>	V <sub>GS</sub> =0V, I <sub>D</sub> =250uA	30			V
Gate Threshold Voltage	V <sub>GS(th)</sub>	V <sub>DS</sub> =V <sub>GS</sub> , I <sub>D</sub> =250uA	0.5		1.5	V
Gate Leakage Current	I <sub>GSS</sub>	V <sub>DS</sub> =0V, V <sub>GS</sub> =±12V			±100	nA
Zero Gate Voltage Drain Current	I <sub>DSS</sub>	V <sub>DS</sub> =24V, V <sub>GS</sub> =0V			1	uA
		V <sub>DS</sub> =24V, V <sub>GS</sub> =0V T <sub>J</sub> =55°C			10	
Drain-source On-Resistance	R <sub>DS(on)</sub>	V <sub>GS</sub> =10V, I <sub>D</sub> =5.8A V <sub>GS</sub> =4.5V, I <sub>D</sub> =4.8A V <sub>GS</sub> =2.5V, I <sub>D</sub> =4.0A		25 30 40		mΩ
Forward Transconductance	g <sub>fs</sub>	V <sub>DS</sub> =4.5V, I <sub>D</sub> =5.8A		12		S
Diode Forward Voltage	V <sub>SD</sub>	I <sub>S</sub> =1.7A, V <sub>GS</sub> =0V			1.2	V
<b>Dynamic</b>						
Total Gate Charge	Q <sub>g</sub>	V <sub>DS</sub> =15V V <sub>GS</sub> =10V I <sub>D</sub> ≡6.7A		9.7	18	nC
Gate-Source Charge	Q <sub>gs</sub>			1.6		
Gate-Drain Charge	Q <sub>gd</sub>			3.1		
Input Capacitance	C <sub>iss</sub>	V <sub>DS</sub> =15V V <sub>GS</sub> =0V F=1MHz		450		pF
Output Capacitance	C <sub>oss</sub>			240		
Reverse Transfer Capacitance	C <sub>rss</sub>			38		
Turn-On Time	t <sub>d(on)</sub> tr	V <sub>DD</sub> =15V R <sub>L</sub> =15Ω I <sub>D</sub> =1.0A V <sub>GEN</sub> =10V R <sub>G</sub> =6Ω		7	15	nS
Turn-Off Time	t <sub>d(off)</sub> tf			10	20	
				20	40	
				11	20	



**ST3400SRG** N Channel Enhancement Mode MOSFET

5.8A

**TYPICAL CHARACTERISTICS (25°C Unless noted)**




Fig 1: On-Region Characteristics




Figure 2: Transfer Characteristics




Figure 3: On-Resistance vs. Drain Current and Gate Voltage




Figure 4: On-Resistance vs. Junction Temperature




Figure 5: On-Resistance vs. Gate-Source Voltage




Figure 6: Body-Diode Characteristics








**ST3400SRG**



N Channel Enhancement Mode MOSFET

5.8A

**TYPICAL CHARACTERISTICS (25°C Unless noted)**






**ST3400SRG**   
N Channel Enhancement Mode MOSFET

5.8A

### SOT-23 PACKAGE OUTLINE



Symbol	Dimensions In Millimeters		Dimensions In Inches	
	Min	Max	Min	Max
A	0.900	1.100	0.035	0.043
A1	0.000	0.100	0.000	0.004
A2	0.900	1.000	0.035	0.039
b	0.300	0.500	0.012	0.020
c	0.080	0.150	0.003	0.006
D	2.800	3.000	0.110	0.118
E	1.200	1.400	0.047	0.055
E1	2.250	2.550	0.089	0.100
e	0.950TYP		0.037TYP	
e1	1.800	2.000	0.071	0.079
L	0.550REF		0.022REF	
L1	0.300	0.500	0.012	0.020
theta	0°	8°	0°	8°