


# BR1220

## ■ Dimensions(mm)




## ■ Specification


<b>Nominal voltage(V)</b>	3
<b>Nominal capacity(mAh)</b>	35
<b>Continuous drain(mA)</b>	0.03
<b>Operating temperature(°C)</b>	-30 to +85

\*Please consult Panasonic when anticipating usage in operating temperature of 80°C or above.


## ■ Discharge temperature characteristics



## ■ Operating voltage vs. load resistance(voltage at 50% discharge depth)




## ■ Capacity vs. load resistance



# BR1225

## ■ Dimensions(mm)




## ■ Specification


<b>Nominal voltage(V)</b>	3
<b>Nominal capacity(mAh)</b>	48
<b>Continuous drain(mA)</b>	0.03
<b>Operating temperature(°C)</b>	-30 to +85

\*Please consult Panasonic when anticipating usage in operating temperature of 80°C or above.


## ■ Discharge temperature characteristics



## ■ Operating voltage vs. load resistance(voltage at 50% discharge depth)



## ■ Capacity vs. load resistance



\* The data in this document are for descriptive purposes only and are not intended to make or imply any guarantee or warranty.