



P.C.B LAYOUT

Specifications :

- Voltage rating: 250VAC / DC
- Current rating: 2A AC / DC
- Withstanding voltage: 500V AC/minute
- Temperature range: -40 to +105
- Insulation resistance: ≥1000M Min
- Contact resistance: ≤20M Max
- Material: PA6T 94V-0
- Planting Category: 1U"Gold
- Wave soldering temperature: 255 ± 5°C, 10s

X4621 W R-2*XX I- C40 D28

① ② ③ ④ ⑤ ⑥ ⑦

- ① Series No.
- ② Category: W-wafer
- ③ Welding Board Angle: R-Straight 90 °
- ④ Row No -Pin No : 2*XX-2*01P-40P
- ⑤ Plastic height: l=2.0mm
- ⑥ Pin length:C=4.0mm
- ⑦ Pin length:D=2.8mm

X4621WR-2*XXI-C40D28	PA6T 94V-0	Brass	1U"Gold	X4621F
PART NO	Material	Material(Pin)	Finsh(Pin)	Suitable XKB Terminal

For and on behalf of
XKB INDUSTRIAL PRECISION CO., LIMITED
 香港星坤工業精密有限公司

△ X
 △ X
 △ X

MARK

DESCRIPTION

DATE

REVISED

APPROVED

REVISIONS

Authorized Signature(s)

UNSPECIFIED TOLERANCES

DSND	DATE	SCALE: N/A	MODEL TYPE: X4621WR-2*XXI-C40D28
DWN	DATE	VIEW:	PART NO.:
CHKD	DATE	UNIT: mm	2.0 mm Crimp Style Connectors
APPD	DATE	SIZE: A4	DWG NO.:
			WEIGHT
			1.0g
			SHEET
			1/1
			REVISION
			A0

XKB INDUSTRIAL PRECISION CO., LIMITED