

Features

- ESD Protection for 1 Line with Bi-directional
- Provide ESD protection for the protected line to IEC 61000-4-2 (ESD) ±15kV (air / contact) IEC 61000-4-4 (EFT) 40A (5/50ns) Cable Discharged Event (CDE)
- Suitable for, **33V and below**, operating voltage applications
- 0402 small DFN package saves board space
- Protect one I/O line or one power line
- Fast turn-on and low clamping voltage
- Solid-state silicon-avalanche and active circuit triggering technology
- Green part

Applications

- Cellular Handsets and Accessories
- Small Panel Modules
- Control Signal Line Protection
- Power Line Protection
- Portable Devices
- Touch Panels
- Notebooks and Handhelds
- Peripherals

Description

AZ4233-01F is a design which includes one bi-directional ESD rated clamping cell to protect one power line, or one control line, or one low speed data line in an electronic system. The AZ4233-01F has been specifically designed to protect sensitive components which are connected to data and transmission lines from over-voltage damage caused by Electrostatic Discharging (ESD), Electrical Fast Transients (EFT), and Cable Discharge Event (CDE).

AZ4233-01F is a unique design which includes proprietary clamping cell in a single package. During transient conditions, the proprietary clamping cell prevents over-voltage on the power line or control/data lines, protecting any downstream components.

AZ4233-01F is bi-directional and may be used on lines where the signal swings above and below ground.

AZ4233-01F may be used to meet the ESD immunity requirements of IEC 61000-4-2, Level 4 (\pm 15kV air, \pm 8kV contact discharge).

Circuit Diagram / Pin Configuration



1



SPECIFICATIONS

ABSOLUTE MAXIMUM RATINGS				
PARAMETER	SYMBOL	RATING	UNITS	
Operating Supply Voltage (pin-1 to pin-2)	V _{DC}	34	V	
Pin-1 to pin-2 ESD per IEC 61000-4-2 (Air)	V _{ESD-1}	±15	kV	
Pin-1 to pin-2 ESD per IEC 61000-4-2 (Contact)	V_{ESD-2}	±15		
Lead Soldering Temperature	T _{SOL}	260 (10 sec.)	°C	
Operating Temperature	T _{OP}	-55 to +85	°C	
Storage Temperature	T _{STO}	-55 to +150	°C	

ELECTRICAL CHARACTERISTICS						
PARAMETER	SYMBOL	CONDITIONS	MINI	ТҮР	МАХ	UNITS
Reverse						
Stand-Off	V_{RWM}	T=25 °C.	-33		33	V
Voltage						
Reverse					4	
Leakage Current	Leak	V _{RWM} = ±33V, T=25 °C.			1	μA
Reverse			35			
Breakdown	V_{BV}	I _{BV} = 1mA, T=25 °C.			42	V
Voltage						
ESD Clamping	M	IEC 61000-4-2 +8kV (I _{TLP} = 16A),		70		v
Voltage (Note 1)	V _{clamp}	Contact mode, T=25 °C.		70		v
Channel Input	<u> </u>			13	20	ъĘ
Capacitance	C _{IN}	V _R = 0V, f = 1MHz, T=25 °C.		13	20	pF

Note 1: ESD Clamping Voltage was measured by Transmission Line Pulsing (TLP) System.

TLP conditions: $Z_0=50\Omega$, $t_p=100$ ns, $t_r=1$ ns.



Typical Characteristics



Typical Variation of C_{IN} vs. V_{IN} 1MHz, T = 25°C f = Input Capacitance (pF) -35 -30 -25 -20 -15 -10 -5 Input Voltage (V)



Applications Information

The AZ4233-01F is designed to protect one line against system ESD/EFT/CDE pulse by clamping it to an acceptable reference. It provides bi-directional protection.

The usage of the AZ4233-01F is shown in Fig. 1. Protected line, such as data line, control line, or power line, is connected at pin 1. The pin 2 is connected to a ground plane on the board. In order to minimize parasitic inductance in the board traces, all path lengths connected to the pins of AZ4233-01F should be kept as short as possible. In order to obtain enough suppression of ESD induced transient, good circuit board is critical. Thus, the following guidelines are recommended:

- Minimize the path length between the protected lines and the AZ4233-01F.
- Place the AZ4233-01F near the input terminals or connectors to restrict transient coupling.
- The ESD current return path to ground should be kept as short as possible.
- Use ground planes whenever possible.
- NEVER route critical signals near board edges and near the lines which the ESD transient easily injects to.



Fig. 1



Fig. 2 shows another simplified example of using AZ4233-01F to protect the control line, low speed

data line, and power line from ESD transient stress.



Fig. 2 ESD protection scheme by using AZ4233-01F.



Mechanical Details





Symbol	Millimeters		Inches		
Symbol	min	max	min	max	
Α	0.95	1.05	0.037	0.041	
В	0.55	0.65	0.022	0.026	
С	0.40	0.55	0.016	0.022	
D	0.45		0.0	18	
E	0.20	0.30	0.008	0.012	
F	0.45	0.55	0.018	0.022	



(Unit: mm)

Notes: This LAND LAYOUT is for reference purposes only. Please consult your manufacturing partners to ensure your company's PCB design guidelines are met.

MARKING CODE



Top View

U = Device Code

Part Number	Marking Code	
AZ4233-01F.R7GR (Green Part)	U	

Note. Green means Pb-free, RoHS, and Halogen free compliant.



Ordering Information

PN#	Material	Туре	Reel size	MOQ	MOQ/internal box	MOQ/carton
AZ4233-01F.R7GR	Green	T/R	7 inch	12,000/reel	4 reels = 48,000/box	6 boxes = 288,000/carton

Revision History

Revision	Modification Description		
Revision 2014/01/20	Preliminary Release.		
Revision 2015/07/24	1. Update ABSOLUTE MAXIMUM RATINGS of ESD.		
	2. Add the Typical Characterization.		
	3. Add the Ordering information.		
Revision 2017/05/16	Formal Release.		
Revision 2019/05/31	Update the ordering information.		