

FEATURES

- Provide ultra-fast response to surge voltage from slow-rising of 100V/s to rapid-rising surge of 1KV/ μ s.
- Small : 5.5*6mm
- Stable breakdown voltage.
- High insulation resistance.
- Low capacitance and insertion loss.
- Reliable to protect electrostatic surge.



APPLICATION

- Repeaters, Modems.
- Telephone interface, line cards.
- Data communication equipment.
- Line test equipment.


ELECTRICAL CHARACTERISTIC

Part Number	DC Breakdown Voltage 100V/s(V)	Tolerance of Vs	Impulse spark-over voltage 1kV/ μ s(V)	Insulation Resistance		Impulse Discharge Current 8/20 μ s(A)	C
	V	%	V	GΩ	DC(V)	KA	pF
5-2R350L	350	± 20	≤ 750	≥ 1	100	5	≤ 1

1. The parameters of all tested by ITU-T K12.
2. Total Impulse discharge current 1000A@ 8/20 μ s by IEC 61000-4-5, 10 shots.
3. The capacitance are tested by 1MHz @DC=0.3V.
4. The V-T waveform of DCBV and IPBV must lie between the shades.

PACKAGE DIMENSIONS

(unit: mm)



PART NUMBER CODE

5 2R 350 L 6

(1) (2) (3) (4) (5)

- ① Brand name;
- ② Sembo 2-Electrod DIP Gas Discharge Tube;
- ③ DC breakdown Voltage.,
- ④ Tolerance is DC breakdown voltage, L=±15%, M=±20%, N=±30%
- ⑤ Gas discharge tube in 5.5*6.0 (mm)

PACKAGING

Part Number	Component Package	Quantity
5-2R350L	5.5*6	500