


## Description

The FSRV05-4 is an ultra low capacitance TVS array, utilizing leading monolithic silicon technology to provide fast response time and low ESD clamping voltage, making this device an ideal solution for protecting voltage sensitive high-speed data lines. The FSRV05-4 has an ultra -low capacitance with a typical value at 0. 6 pF, and complies with the IEC 61000-4-2 (ESD) standard with  $\pm 15\text{kV}$  air and  $\pm 8\text{kV}$  contact discharge. It is assembled into a 6-pin lead-free SOT-23-6L package. The combination of small size, ultra low capacitance, and high ESD surge capability make it ideal for use in applications such as multimedia, and other high speed ports.


## Features

- \* Ultra low capacitance: 0. 6pF typical
- \* Ultra low leakage: nA level
- \* Low operating voltage: 5.0V
- \* Up to 4 data lines and one power line protects
- \* Low clamping voltage
- \* Complies with following standards:
  - IEC 61000-4-2 (ESD) immunity test  
Air :  $\pm 20\text{kV}$ ; discharge:  $\pm 15\text{kV}$
  - IEC61000-4-5 (Lightning) 4A (8/20 $\mu\text{s}$ )
- \* SOT-23-6L Package
- \* RoHS Compliant

## Circuit Diagram



## Marking Diagram



Transparent top view

## Applications

- \* Monitors and flat panel displays
- \* Set-top box and Digital TV
- \* Video graphics cards
- \* Digital Video Interface (DVI)
- \* Notebook Computers
- \* PCI Express and Serial SATA Ports

## Ordering Information

Part Number	Packaging	Reel Size
FSRV05-4	3000/Tape & Reel	7 inch


**Absolute Maximum Ratings ( $T_A=25^\circ\text{C}$  unless otherwise specified)**

Parameter	Symbol	Value	Unit
Peak Pulse Power (8/20μs,I/O-GND)	Ppk	50	W
Peak Pulse Power (8/20μs,Vcc-GND)	Ppk	300	W
Peak Pulse Current (8/20μs,I/O-GND)	IPP	4.0	A
Peak Pulse Current (8/20μs,Vcc-GND)	IPP	17	A
ESD per IEC 61000-4-2 (Air)	$V_{\text{ESD},\text{VDD}}$	±20	kV
ESD per IEC 61000-4-2 (Contact)	$V_{\text{ESD},\text{I/O}}$	±15	
Operating Temperature Range	$T_J$	-55 to +125	°C
Storage Temperature Range	$T_{\text{stg}}$	-55 to +150	°C


**Electrical Characteristics ( $T_A=25^\circ\text{C}$  unless otherwise specified)**

Parameter	Symbol	Test Condition	Min	Typ	Max	Unit
Reverse Working Voltage	$V_{\text{RWM}}$	Pin 5 to GND,I/O-GND			5.0	V
Breakdown Voltage	$V_{\text{BR}}$	$I_T = 1\text{mA}(\text{Pin 5 to GND,I/O-GND})$	6.0	7.5	8.5	V
Reverse Leakage Current	$I_R$	$V_{\text{RWM}} = 5.0\text{V}$			0.5	μA
Forward Breakdown Voltage	$V_F$	$I_F = 15\text{mA,GND to Pin 5/IO}$		0.9	1.2	V
Clamping Voltage	$V_C$	$\text{IPP} = 4\text{A (8 x 20μs pulse, I/O to GND)}$		14.0	15.0	V
Clamping Voltage	$V_C$	$\text{IPP} = 17\text{A (8 x 20μs pulse,Pin 5 to GND)}$		16.0	18.0	V
Junction Capacitance	$C_J$	$V_{\text{pin5}} = 5\text{V, I/O=0V, f = 1MHz, I/O-GND}$		0.6	0.8	pF
Junction Capacitance	$C_J$	$V_{\text{pin5}} = 5\text{V, I/O=0V, f = 1MHz, I/O-I/O pins}$		0.3	0.4	pF


**Typical Performance Characteristics ( $T_A=25^\circ\text{C}$  unless otherwise Specified)**




Junction Capacitance vs. Reverse Voltage




Clamping Voltage vs. Peak Pulse Current




Peak Pulse Power vs. Pulse Time



IEC61000-4-2 Pulse Waveform




Power Derating Curve



8 X 20us Pulse Waveform


## Package Outline Drawing



SOT-23-6L Package

SYM	DIMENSIONS					
	MILLIMETERS			INCHES		
	MIN	NOM	MAX	MIN	NOM	MAX
A	0.90		1.45	0.035		0.057
A1	0.00		0.15	0.000		0.006
A2	0.90	1.15	1.30	0.035	0.045	0.051
b	0.25		0.50	0.010		0.020
c	0.08		0.22	0.003		0.009
D	2.80	2.90	3.10	0.110	0.114	0.122
E1	1.50	1.60	1.75	0.060	0.063	0.069
E	2.80 BSC			0.110 BSC		
e	0.95 BSC			0.037 BSC		
e1	1.90 BSC			0.075 BSC		
N	6			6		
aaa	0.10			0.004		
ccc	0.20			0.008		

## Suggested Land Pattern



SYM	DIMENSIONS	
	MILLIMETERS	INCHES
C	2.50	0.098
G	1.40	0.055
P	0.95	0.037
X	0.60	0.024
Y	1.10	0.043
Z	3.60	0.141