



ASCENDSEMI

ASDM30P11TD

-30V P-Channel MOSFET



Features


- Low FOM $R_{DS(on)} \times Q_{gd}$
- 100% avalanche tested
- Easy to use/drive
- RoHS compliant

Application



- Power Switch Circuit of Adaptor and Charger
- Battery Protection Charge/Discharge
- Notebook AC-in Load Switch

Product Summary

V_{DS}	-30	V
$R_{DS(on),TYP} @ V_{GS}=10\text{ V}$	6.4	$\text{m}\Omega$
I_D	-55	A



PDFN3*3-8



Absolute Maximum Ratings $T_A = 25^\circ\text{C}$, unless otherwise noted

Parameter	Symbol	Values	Unit
Drain-Source voltage($V_{GS}=0\text{V}$)	V_{DS}	-30	V
Continuous Drain Current ²⁾	I_D	-55	A
$T_C = 100^\circ\text{C}$	I_D	-34.6	
Pulsed Drain Current ³⁾	$I_{D,pulse}$	-220	A
Gate-Source Voltage	V_{GSS}	± 25	V
Single Pulse Avalanche Energy	E_{AS}	200	mJ
Power Dissipation	P_D	31.2	W
Operating Junction and Storage Temperature Range	T_J, T_{stg}	-55~+150	$^\circ\text{C}$

Thermal Resistance

Parameter	Symbol	Max.	Unit
Thermal Resistance, Junction-to-Case	R_{thJC}	4	$^\circ\text{C/W}$
Thermal Resistance, Junction-to-Ambient	R_{thJA}	35	$^\circ\text{C/W}$

Notes

- 1) $L=0.5\text{mH}, VDD=-15\text{V}, \text{Start } T_J=25^\circ\text{C}$
- 2) Limited by maximum junction temperature.
- 3) Repetitive Rating: Pulse width limited by maximum junction temperature.








ASCENDSEMI







ASDM30P11TD

-30V P-Channel MOSFET

Electrical Characteristics $T_J = 25^\circ\text{C}$, unless otherwise noted

Parameter	Symbol	Test Conditions	Value			Unit
			Min.	Typ.	Max.	
Static Characteristics						
Drain-Source Breakdown Voltage	$V_{(\text{BR})\text{DSS}}$	$V_{\text{GS}} = 0\text{V}, I_D = -250\mu\text{A}$	-30	--	--	V
Zero Gate Voltage Drain Current	I_{DSS}	$V_{\text{DS}} = -30\text{V}$ $V_{\text{GS}} = 0\text{V}, T_J = 25^\circ\text{C}$	--	--	-1	μA
		$V_{\text{DS}} = -24\text{V}$, $V_{\text{GS}} = 0\text{V}, T_J = 125^\circ\text{C}$	--	--	-100	
Gate-Source Leakage Current	I_{GSS}	$V_{\text{GS}} = \pm 25\text{V}$	--	--	± 100	nA
Gate-Source Threshold Voltage	$V_{\text{GS}(\text{th})}$	$V_{\text{DS}} = V_{\text{GS}}, I_D = -250\mu\text{A}$	-1.2	-1.8	-2.5	V
Drain-Source On-State-Resistance	$R_{\text{DS}(\text{on})}$	$V_{\text{GS}} = -10\text{V}, I_D = -20\text{A}$	--	6.4	8	$\text{m}\Omega$
		$V_{\text{GS}} = -4.5\text{V}, I_D = -10\text{A}$	--	10.5	13	$\text{m}\Omega$
Dynamic Characteristics						
Input Capacitance	C_{iss}	$V_{\text{GS}} = 0\text{V},$ $V_{\text{DS}} = -15\text{V}$ $f = 1.0\text{MHz}$	--	3482	--	pF
Output Capacitance	C_{oss}		--	400	--	
Reverse Transfer Capacitance	C_{rss}		--	309	--	
Total Gate Charge	Q_g	$V_{\text{DS}} = -15\text{V}, I_D = -10\text{A}$ $V_{\text{GS}} = -10\text{V}$	--	61	--	nC
Gate-Source Charge	Q_{gs}		--	12	--	
Gate-Drain Charge	Q_{gd}		--	10	--	
Gate Plateau Voltage	V_{Plateau}		--	3.1	--	V
Turn-on Delay Time	$t_{\text{d}(\text{on})}$	$V_{\text{DS}} = -15\text{V}, V_{\text{GS}} = -10\text{V}$ $R_G = 3\Omega, I_D = -10\text{A}$	--	19	--	ns
Turn-on Rise Time	t_r		--	33	--	
Turn-off Delay Time	$t_{\text{d}(\text{off})}$		--	38	--	
Turn-off Fall Time	t_f		--	15	--	
Drain-Source Body Diode Characteristics						
Body Diode Forward Voltage	V_{SD}	$T_J = 25^\circ\text{C}, I_{\text{SD}} = -10\text{A},$ $V_{\text{GS}} = 0\text{V}$	--	--	-1.2	V
Continuous Diode Forward Current	I_s	$I_F = -10\text{A}, \frac{di_F}{dt} = -100\text{A}/\mu\text{s}$	--	--	-55	A
Reverse Recovery Time	t_{rr}		--	45	--	ns
Reverse Recovery Charge	Q_{rr}		--	29	--	nC

Typical Characteristics $T_J = 25^{\circ}\text{C}$, unless otherwise noted

Figure 1. Maximum Safe Operating Area

Figure 2. Maximum Power Dissipation vs Case Temperature

Figure 3. Maximum Continuous Drain Current vs Case Temperature

Figure 4. Typical output Characteristics

Figure 5 Maximum Effective Thermal Impedance , Junction to Case

Typical Characteristics $T_j = 25^\circ\text{C}$, unless otherwise noted

Figure 6 Typical Transfer Characteristics

Figure 7 Typical Body Diode Transfer Characteristics

Figure 8. Drain-to-Source On Resistance vs Drain Current

Figure 9. Normalized On Resistance vs Junction Temperature

Figure10. Normalized Threshold Voltage vs Junction Temperature

Figure 11. Normalized Breakdown Voltage vs Junction Temperature

Typical Characteristics $T_J = 25^{\circ}\text{C}$, unless otherwise noted




Figure 12. Capacitance Characteristics





Figure 13 Typical Gate Charge vs Gate to Source Voltage

Ordering and Marking Information

Ordering Device No.	Marking	Package	Packing	Quantity
ASDM30P11TD-R	30P11J	PDFN3*3-8	Tape&Reel	5000

PACKAGE	MARKING
PDFN3*3-8	





ASCENDSEMI

ASDM30P11TD

-30V P-Channel MOSFET

PDFN3*3_8 Package



SYMBOL	COMMON		
	MM		
	MIN	NOM	MAX
A	0.70	0.75	0.85
A1	/	/	0.05
b	0.20	0.30	0.40
c	0.10	0.152	0.25
D	3.15	3.30	3.45
D1	3.00	3.15	3.25
D2	2.29	2.45	2.65
E	3.15	3.30	3.45
E1	2.90	3.05	3.20
E2	1.54	1.74	1.94
E3	0.28	0.48	0.65
E4	0.37	0.57	0.77
E5	0.10	0.20	0.30
e	0.60	0.65	0.70
K	0.59	0.69	0.89
L	0.30	0.40	0.50
L1	0.06	0.125	0.20
t	0	0.075	0.13
θ	10°	12°	14°



ASCENDSEMI

ASDM30P11TD

-30V P-Channel MOSFET

IMPORTANT NOTICE

Xi'an Ascend Semiconductor incorporated MAKES NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).

Xi'an Ascend Semiconductor Incorporated and its subsidiaries reserve the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. Xi'an Ascend Semiconductor Incorporated does not assume any liability arising out of the application or use of this document or any product described herein; neither does Xi'an Ascend Semiconductor Incorporated convey any license under its patent or trademark rights, nor the rights of others. Any Customer or user of this document or products described herein in such applications shall assume .

all risks of such use and will agree to hold Ascendsemi Incorporated and all the companies whose products are represented on Xi'an Ascend Semiconductor Incorporated website, harmless against all damages.

Xi'an Ascend Semiconductor Incorporated does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel. Should Customers purchase or use Xi'an Ascend Semiconductor Incorporated products for any unintended or unauthorized application, Customers shall indemnify and hold Xi'an Ascend Semiconductor Incorporated and its representatives harmless against all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized application.

www.ascendsemi.com